

CAT#	A
621	2.250
622	3.600
623	6.340
624	8.500
621A	2.250
622A	3.600
623A	6.340
624A	8.500
621B	2.0250
622B	3.600
623B	6.340
624B	8.500

GROUND CLAMPS WITH THREADED HUBS FOR CONDUIT PIPE


					BRASS
TOPAZ CAT #	UPC#	SIZE	UNIT CTN	SHIP CASE	WT/ CASE
WITH 1/2" HUBS					
621	16120	1/2" TO 1"	10	100	26
622	16130	1 1/4" TO 2"	5	50	35
623	16140	2 1/2" TO 4"	—	10	15
624	16150	5" TO 6"	—	10	20

WITH 3/4" HUBS

621A	16160	1/2" TO 1"	5	50	20
622A	16170	1 1/4" TO 2"	5	50	37
623A	16180	2 1/2" TO 4"	—	10	12
624A	16190	5" TO 6"	—	10	21

WITH 1" HUBS

621B	16200	1/2" TO 1"	—	10	9
622B	16210	1 1/4" TO 2"	—	10	10
623B	16220	2 1/2" TO 4"	—	10	21
624B	16230	5" TO 6"	—	10	28



CAT#	A	B	WIRE SIZE MIN MAX
411	1.22	.75	10 SOL 2STR
412	1.41	.90	10 SOL 2STR
413	1.47	1.00	10 SOL 2STR

GROUND ROD CLAMPS FOR DIRECT BURIAL W/BRONZE OR STAINLESS SCREWS

TOPAZ CAT #	UPC#	SIZE	UNIT CTN	SHIP CASE	BRONZE WT/ CASE
411	13820	1/2"	—	100	9
412	13830	5/8"	—	100	18
413	13840	3/4"	—	50	12

