

### CAST BRONZE CLAMPS FOR CONDUIT

Pressure bar type conduit hub adjusts for 1/2", 3/4" EMT or 1/2" rigid conduit. Hub swings 360° for easy alignment. Zinc plated hardware.



CATALOG NUMBER	ACCOMMODATES CONDUCTOR RANGE			REFERENCE DIMENSIONS			RECOMMENDED SCREW TORQUE "INCH POUNDS"	
	WATER PIPE	GROUND	HUB SIZE	H	L	W	PIPE CLAMP	WIRE CLAMP
C-11JPT	1/2 - 1 [13 - 25]	10 - 6 Sol.	1/2 [13]	2.07 [53]	3.19 [81]	2.70 [69]	50 in.-lb.	50 in.-lb.
C-22JPT	1-1/4 - 2 [32 - 51]			2.70 [69]	3.83 [97]			
C-4JPT	2-1/2 - 4 [64 - 102]			4.39 [112]	5.15 [131]			

D-34

### CAST BRONZE GROUND CLAMPS

For connecting grounding conductor to water pipe or copper tube. "D" indicates UL467 Listed for direct burial in earth and concrete and are supplied with silicon bronze hardware. "B" indicates brass hardware.



CATALOG NUMBER	ACCOMMODATES CONDUCTOR RANGE			REFERENCE DIMENSIONS				RECOMMENDED SCREW TORQUE "INCH POUNDS"	
	WATER PIPE	REBAR	GROUND	H	L	W	C	PIPE CLAMP	WIRE CLAMP
C-11N	1/2 - 1 [13 - 25]	—	10 - 2 Str.	1.81 [46]	2.25 [56]	.63 [16]	.63 [16]	50 in.-lb.	50 in.-lb.
C-11D		#4 - #6							
C-11B		—							
C-22	1-1/4 - 2 [32 - 51]	—	10 - 2 Str.	2.38 [60]	3.63 [92]	.75 [19]	1.00 [25]		
C-22D									
C-4	2-1/2 - 4 [64 - 114]	—	10 - 2 Str.	4.13 [105]	6.25 [159]	.96 [24]	1.88 [48]		
C-8	4-1/2 - 6 [114 - 165]	—	10 - 2 Str.	4.29 [109]	8.34 [212]	1.25 [32]	1.88 [48]		

### BUDGET PRICE CAST BRONZE GROUND CLAMP

Similar to above but lighter duty.



CATALOG NUMBER	ACCOMMODATES CONDUCTOR RANGE			REFERENCE DIMENSIONS				RECOMMENDED SCREW TORQUE "INCH POUNDS"	
	WATER PIPE	REBAR	GROUND	H	L	W	C	PIPE CLAMP	WIRE CLAMP
C-5 (JUNIOR)	1/2 - 1 [13 - 25]	—	10 - 2 Str.	1.56 [40]	2.25 [56]	.56 [14]	.50 [13]	50 in.-lb.	50 in.-lb.