



Key Features

Design Lights Consortium Certified

- Long Life LED chips
- Uniform and consistent color
- Excellent thermal design
- Motion Sensor
- 15-30 foot height performance
- Shatter- resistant glass
- Universal Voltage 120-277V
- Power Factor >0.99
- Operating Temp: -30°F~130°F
- 50,000 Hours rated average life

Dimension

	Width	Depth	Height	Weight (lbs)
40W	14.5 / 363	7.5 / 188	9 / 230	9.5
60W	18.5 / 463	9.25 / 239	9 / 230	16.00
90W	18.5 / 463	9.25 / 239	9 / 230	18.60



*Inch/mm

Applications

- Area Lighting
- Security Lighting
- Pathway Lighting
- Perimeter Lighting
- Entryway Lighting

SHIELD INCLUDED

Requires shield for
DLC qualification



Specifications

Item Code	Description	Color Temp	Wattage	Output Lumen	Equiv. Wattage	CRI	Beam Type	DLC QPL LISTED
7086	LED-FXTWP40/40K/DB	4000K	40W	3,025	100W MH	80	Forward Throw	●
7087	LED-FXTWP40/50K/DB	5000K	40W	3,043	100W MH	80	Forward Throw	●
7088	LED-FXTWP60/40K/DB	4000K	60W	4,593	150W MH	80	Forward Throw	●
7089	LED-FXTWP60/50K/DB	5000K	60W	4,596	150W MH	80	Forward Throw	●
7138	LED-FXTWP90/40K/DB	4000K	90W	6,125	250W MH	80	Forward Throw	●
7139	LED-FXTWP90/50K/DB	5000K	90W	6,550	250W MH	80	Forward Throw	●

