


## JAP6

60/240-260/3BB

MULTICRYSTALLINE SILICON MODULE




### JA Solar Holdings Co., Ltd.

JA Solar Holdings Co., Ltd. is a world-leading manufacturer of high-performance photovoltaic products that convert sunlight into electricity for residential, commercial, and utility-scale power generation. The company was founded on May 18, 2005, and was publicly listed on NASDAQ on February 7, 2007. JA Solar is one of the world's largest producers of solar cells and modules. Its standard and high-efficiency product offerings are among the most powerful and cost-effective in the industry.

**A d d :** NO.36, Jiang Chang San Road, Zhabei, Shanghai 200436, China  
**T e l :** +86 21 6095 5888 / +86 21 6095 5999  
**F a x :** +86 21 6095 5858 / +86 21 6095 5959  
**Email:** sales@jasolar.com market@jasolar.com

### Superior Warranty

- 10-year product warranty
- 25-year linear power output warranty



### Key Features



Multicrystalline modules designed for residential commercial and utility applications, rooftop or ground mount



High output, 15.90% highest conversion efficiency



Designed for UL 600V or ETL 1000V, IEC 1000V applications



Anti-reflective and self-cleaning surface reduces power loss from dirt and dust



Outstanding performance in low-light irradiance environments



Excellent mechanical load resistance: Certified to withstand high wind loads (2400Pa) and snow loads (5400Pa)



High salt and ammonia resistance certified by TÜV NORD

### Reliable Quality

- Positive power tolerance: 0~+5W
- 100% EL double-inspection ensures modules are defects free
- Modules binned by current to improve system performance
- Potential Induced Degradation (PID) Resistant



### Comprehensive Certificates

- IEC 61215, IEC 61730, UL1703, CEC Listed, MCS and CE
- ISO 9001: 2008: Quality management systems
- ISO 14001: 2004: Environmental management systems
- BS OHSAS 18001: 2007: Occupational health and safety management systems
- Environmental policy: The first solar company in China to complete Intertek's carbon footprint evaluation program and receive green leaf mark verification for our products



Specifications subject to technical changes and tests. JA Solar reserves the right of final interpretation.

## Engineering Drawings



■ customized cable length available upon request

### MECHANICAL PARAMETERS

Cell (mm)	Poly 156x156
Weight (kg)	18.5 (approx)
Dimensions (LxWxH) (mm)	1650x991x40
Cable Cross Section Size (mm <sup>2</sup> )	4
No. of Cells and Connections	60 (6x10)
Junction Box	IP67, 3 diodes
Connector	MC4 Compatible
Packaging Configuration	26/26+2 Per Pallet




### WORKING CONDITIONS

Maximum System Voltage	DC 1000V (TÜV) / 600V (UL) / 1000V (ETL)
Operating Temperature	-40°C ~ +85°C
Maximum Series Fuse	15A
Maximum Static Load, Front (e.g., snow and wind) Maximum Static Load, Back (e.g., wind)	5400Pa (112 lb/ft <sup>2</sup> ) 2400Pa (50 lb/ft <sup>2</sup> )
NOCT	47±2°C
Application Class	Class A

### ELECTRICAL PARAMETERS

TYPE	JAP6 60-240/3BB	JAP6 60-245/3BB	JAP6 60-250/3BB	JAP6 60-255/3BB	JAP6 60-260/3BB
Rated Maximum Power at STC (W)	240	245	250	255	260
Open Circuit Voltage (Voc/V)	37.30	37.45	37.54	37.62	37.73
Maximum Power Voltage (Vmp/V)	29.38	29.63	29.98	30.36	30.77
Short Circuit Current (Isc/A)	8.65	8.78	8.84	8.88	8.91
Maximum Power Current (Imp/A)	8.17	8.27	8.34	8.40	8.45
Module Efficiency [%]	14.68	14.98	15.29	15.59	15.90
Power Tolerance (W)	-0~+5W				
Temperature Coefficient of Isc (αIsc)	+0.062%/°C				
Temperature Coefficient of Voc (βVoc)	-0.330%/°C				
Temperature Coefficient of Pmax (γPmp)	-0.450%/°C				
STC	Irradiance 1000W/m <sup>2</sup> , Module Temperature 25°C, Air Mass 1.5				

### I-V CURVE



### NOCT

TYPE	JAP6 60-240/3BB	JAP6 60-245/3BB	JAP6 60-250/3BB	JAP6 60-255/3BB	JAP6 60-260/3BB
Max Power at STC (Pmax) [W]	172.67	176.27	179.87	183.47	187.06
Open Circuit Voltage (Voc) [V]	33.97	34.10	34.19	34.26	34.36
Max Power Voltage (Vmp) [V]	26.43	26.66	26.97	27.32	27.68
Short Circuit Current (Isc) [A]	7.01	7.11	7.16	7.19	7.22
Max Power Current (Imp) [A]	6.53	6.61	6.67	6.72	6.76
Condition	Under Normal Operating Cell Temperature, Irradiance of 800 W/m <sup>2</sup> , spectrum AM 1.5, ambient temperature 20°C, wind speed 1 m/s				

Electrical data in this catalog do not refer to a single module and they are not part of the offer. They only serve for comparison among different module types.