

simplicity



Application Illustration only, subject lamps not used in photo.

Plug into a new kind of energy savings.

LED replacement for CFL plug-in downlights

GE's LED plug-in lamps allow you to replace inefficient CFL 4 pin G24q/GX24 without tools or costly upgrades. Simply plug the replacement lamp into the existing ballast.

LOW-COST OPERATION

- Uses 50% less energy than CFL
- 12W LED saves over \$71 in energy vs 26 watt CFL
- 18.5W LED saves over \$129 in energy vs 42 watt CFL
- Energy savings based on \$0.11 per kWh over the rated life of the lamp
- Advanced optics eliminate wasted light to deliver a more targeted beam with fewer lumens (950 vs. 1800)
- Energy efficiency and long life mean fewer lamp replacements versus CFL light sources

COLOR RENDERING

- Available with a CRI of 80

COLOR TEMPERATURE

- Available in 2700K, 3000K, 3500K and 4000K

LONG LIFE

- Lasts 2.5X longer than CFL
- 50,000 hours rated life (L70)

ENVIRONMENTALLY CONSCIOUS

- These lamps are energy efficient, contain no lead or mercury, and meet the material restriction requirements of RoHS

GE QUALITY AND RELIABILITY

- 5-year limited warranty

To learn more about saving money and energy, go to: gelighting.com/ThinkLED

When you Think LED lighting, Think GE.

ecomaginationSM



imagination at work

Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.


LED replacement for CFL Plug-in lamps

Bulb Shape	Base Type	Watts	Grainger Item Number	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)	Dimmable	#Location Rating	Additional Information	
Vertical																		
	G24q/GX24	12	39UR94	96801	LED12G24Q-V/827	##	6	5.31	950		2700	80		50000	-	Damp	Requires Electronic Ballast, White	
			39UR96	96775	LED12G24Q-V/830	##	6	5.31	950		3000	80		50000	-	Damp	Requires Electronic Ballast, White	
			39UR92	96689	LED12G24Q-V/835	##	6	5.31	1000		3500	80		50000	-	Damp	Requires Electronic Ballast, White	
			39UR97	96771	LED12G24Q-V/840	##	6	5.31	1000		4000	80		50000	-	Damp	Requires Electronic Ballast, White	
			18.5	39288	LED19GX24Q-V/827	##	6	6.42	1800		2700	80		50000	-	Damp	Requires Electronic Ballast, White	
				39277	LED19GX24Q-V/830	##	6	6.42	1850		3000	80		50000	-	Damp	Requires Electronic Ballast, White	
				39275	LED19GX24Q-V/835	##	6	6.42	1950		3500	80		50000	-	Damp	Requires Electronic Ballast, White	
39279	LED19GX24Q-V/840	##	6	6.42	1950		4000	80		50000	-	Damp	Requires Electronic Ballast, White					
Horizontal																		
	G24q/GX24	12	39UR91	96799	LED12G24Q-H/827	##	6	5.31	950		2700	80		50000	-	Damp	Requires Electronic Ballast, White	
			39UR93	96798	LED12G24Q-H/830	##	6	5.31	950		3000	80		50000	-	Damp	Requires Electronic Ballast, White	
			39UR95	96761	LED12G24Q-H/835	##	6	5.31	1000		3500	80		50000	-	Damp	Requires Electronic Ballast, White	
			39UR98	96769	LED12G24Q-H/840	##	6	5.31	1000		4000	80		50000	-	Damp	Requires Electronic Ballast, White	
			18.5	39289	LED19GX24q-H/827	##	6	6.70	1800		2700	80		50000	-	Damp	Requires Electronic Ballast, White	
				39282	LED19GX24q-H/830	##	6	6.70	1850		3000	80		50000	-	Damp	Requires Electronic Ballast, White	
				39276	LED19GX24q-H/835	##	6	6.70	1950		3500	80		50000	-	Damp	Requires Electronic Ballast, White	
39279	LED19GX24q-H/840	##	6	6.70	1950		4000	80		50000	-	Damp	Requires Electronic Ballast, White					

Check compatibility at: GELighting.com/LED4pin-compatibility

Approximate performance when replacing listed CFL Plug-In lamps with a 12W GE LED Plug-In

Original 4-Pin CFL Plug-In (DBX, TBX) Performance		Subsequent performance when replaced with a 12W 4-Pin LED Plug-In (DBX, TBX)		Subsequent performance when replaced with a 18.5W 4-Pin LED Plug-In (DBX, TBX)	
Watts	Approximate Lumens	Watts	Approximate Lumens	Watts	Approximate Lumens
13	900	7	500	-	-
18	1200	10	750	-	-
26	1800	12	950	-	-
32	2400	12	950	16	1700
42	3200	-	-	18.5	1800



Compatible with 1 or 2 lamp configuration

HORIZONTAL CONFIGURATION



12 Watt



18.5 Watt

4-PIN REPLACEMENT

12 Watt Replacement Bases



18.5 Watt Replacement Bases



VERTICAL CONFIGURATION



12 Watt



18.5 Watt

Check compatibility at GELighting.com/LED4pin-compatibility

Get more information at GELighting.com/ThinkLED

Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

* The life rating is based on the hours of operation the lamp will provide before reaching 70% of its original rating (L70)

** Minimum order quantity = 6

UL 1993 Environmental Requirements for LED LAMPS

Location, damp - Exterior or interior location that is normally or periodically subject to condensation of moisture in, on, or adjacent to, electrical equipment, and includes partially protected locations.

Location, dry - Location not normally subject to dampness, may include a location subject to temporary dampness, i.e., building under construction, provided ventilation is adequate to prevent an accumulation of moisture.

Location, wet - Location in which water or other liquid can drip, splash, or flow on or against electrical equipment.

Check ballast compatibility at: GELighting.com/LED4Pin-Compatibility

ecomaginationSM

Product is compliant with material restriction requirements of RoHS



www.gelighting.com

GE and the GE Monogram are trademarks of the General Electric Company. All other trademarks are the property of their respective owners. Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions. GE Lighting and GE Lighting Solutions, LLC are businesses of the General Electric Company. © 2016 GE.

LEDL007-G (Rev 4/11/16)

Distributor:

AVAILABLE THROUGH

GRAINGER
FOR THE ONES WHO GET IT DONE