

sleek



Application illustration only, subject lamps not used in photo.



GE LED Bright Stik™

GE's LED Bright Stik™ illuminates spaces instantly. Its sleek cylindrical shape fits in place of a 40-100 watt incandescent, halogen, and CFL. Use as a longer life, lower energy alternative to CFL.

LOW-COST OPERATION

- Uses 80% less energy than incandescent and 20% less energy than CFL
- For example, using only 10 watts of energy, saves over \$82 in energy costs over the rated life of a lamp versus a standard 60 watt incandescent lamp based on \$0.11 per kWh. Provides similar light output (760 vs 840 lumens).
- Instant full brightness
- Energy efficiency and long life mean fewer lamp replacements versus standard incandescent and halogen light sources

COLOR RENDERING

- Available with a CRI of 80 and 88

COLOR TEMPERATURE

- Available in 2700K, 2850K and 5000K

LONG LIFE

- 15,000 hour rated life (L70)
- Lasts 50% longer than CFL (10,000 hrs)
- Lasts 15X longer than incandescent/halogen (1,000 hrs)

ENVIRONMENTALLY CONSCIOUS

- These lamps are energy efficient, contain no lead or mercury, and are compliant with material restriction requirements of RoHS
- Worry-free use and disposal

GE QUALITY AND RELIABILITY

- 3-year limited warranty

To learn more about saving money and energy, go to: gelighting.com/ThinkLED

When you Think LED lighting, Think GE.


ecomaginationSM



imagination at work

Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

GE LED Bright Stik™

Bulb Shape	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information
LED Bright Stik™																	
	MED	5.5	66256	LED5.5LS3/827	120	48	4.45	450		2700	80	40W	15,000	-	★	Damp	Case = 16 3-packs, ES 2.0, Avail. Oct. 2016
			75177	LED5.5LS3/850	120	48	4.45	450		5000	80	40W	15,000	-	★	Damp	Case = 16 3-packs, ES 2.0, Avail. Oct. 2016
	MED	6	35517	LED6LS3/828	120	48	4.45	450		2850	80	40W	15,000	-		Indoor	Case = 16 3-packs
			35519	LED6LS3/850	120	48	4.45	450		5000	80	40W	15,000	-		Indoor	Case = 16 3-packs
	MED	9	75184	LED9LS3/827	120	48	4.45	760		2700	80	60W	15,000	-	★	Damp	Case = 16 3-packs, ES 2.0, Avail. Oct. 2016
			75588	LED9LS3/850	120	48	4.45	760		5000	80	60W	15,000	-	★	Damp	Case = 16 3-packs, ES 2.0, Avail. Oct. 2016
	MED	10	28089	LED10LS3/828	120	48	4.45	760		2850	80	60W	15,000	-		Indoor	Case = 16 3-packs
			32273	LED10LS3/850	120	48	4.45	760		5000	80	60W	15,000	-		Indoor	Case = 16 3-packs
	MED	14	35520	LED14LS2/828	120	32	5.24	1060		2850	80	75W	15,000	-		Indoor	Case = 16 2-packs
			35522	LED14LS2/850	120	32	5.24	1060		5000	80	75W	15,000	-		Indoor	Case = 16 2-packs
	MED	16	35523	LED16LS2/828	120	32	5.24	1520		2850	88	100W	15,000	-		Indoor	Case = 16 2-packs
			35524	LED16LS2/850	120	32	5.24	1520		5000	88	100W	15,000	-		Indoor	Case = 16 2-packs

Get more information at GELighting.com/ThinkLED

Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

* The life rating is based on the hours of operation the lamp will provide before reaching 70% of its original rating (L70)

** Minimum order quantity = 3

UL 1993 Environmental Requirements for LED LAMPS

Location, damp – Exterior or interior location that is normally or periodically subject to condensation of moisture in, on, or adjacent to, electrical equipment, and includes partially protected locations.

Location, dry – Location not normally subject to dampness, may include a location subject to temporary dampness, i.e., building under construction, provided ventilation is adequate to prevent an accumulation of moisture.

Location, wet – Location in which water or other liquid can drip, splash, or flow on or against electrical equipment.

Notes: 1) Product descriptions ending in "TIP" indicate a carded blister or clamshell package nested in a tray for shelf display. Cards also designed for hook display.

2) LED A19 Locking device works on PC: 85791, 85792, 89898, 62182, 89899 and 89900



ecomaginationSM

Product is compliant with material restriction requirements of RoHS



www.gelighting.com

GE and the GE Monogram are trademarks of the General Electric Company. All other trademarks are the property of their respective owners. Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions. GE Lighting and GE Lighting Solutions, LLC are businesses of the General Electric Company. © 2016 GE.

LEDL019 (Rev 10/5/16)