

GE
Lighting

awaken



LED replacement lamps

ecomaginationSM



imagination at work

exceeding expectations

Why choose GE'S LED Lamps?

Innovation leadership

A GE scientist invented the first visible LED in 1962, pioneering a technology that is revolutionizing the lighting industry. That was our start and now we are dedicated to constantly improving LED performance. We continually invest in new products and the latest upgrades to make sure our best LED solutions are available.

Trust

We've been here. We'll be here. Built into each of GE's LED replacement lamps is 125 years of experience, reliability and innovation. Every performance claim we make is supported by stringent, comprehensive testing—ensuring that your lighting investment pays off today and in the future.

Long life

GE's LED replacement lamps are sturdy, dependable and long lasting. Depending on the lamp, you can expect up to 50,000 hours of rated life. That's 12 hours a day, every day of the year, for over a decade.

Short payback period

Decreased energy and maintenance costs, combined with utility rebates, deliver results that often exceed your expectations.

Family of solutions

Directional. Omni-directional. Decorative. Dimming. Tight optical control. Accent. Task. Display. Indoor. Outdoor. You name it. We've got it in LED.



LED replacement lamps

Decorative Lamps

Bulb Shape	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (in)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information
Candles																	
	CA11	MED	3.5	68168	LED3DCAM-C/TP	120	3	4.2	170	2700	80	25W	15,000	Yes	★	Damp	Clear, Bent tip
			4	68167	LED4DCAM-F/TP	120	3	4.2	270	2700	82	25W	15,000	Yes	★	Damp	Frost, Bent tip
				65655	LED4DCAM-C/827	120	3	4.2	300	2700	80	40W	15,000	Yes	★	Damp	Clear, Bent tip
			23707	LED4DCAM-C/5K/TP	120	3	4.2	350	5000	80	40W	15,000	Yes	★	Damp	Clear, Bent tip	
			21250	LED4DCAM-C3/827	120	6	4.2	300	2700	80	40W	15,000	Yes		Damp	Clear, Bent tip	
			75554	LED4DCAMCF/824	120	6	4.2	250	2400	80	25W	15,000	Yes		Damp	Clear, Bent tip	
	CAND	4.5		23706	LED4.5DCAM-F5KTP	120	3	4.2	350	5000	80	40W	15,000	Yes	★	Damp	Frost, Bent tip
				89950	LED4.5DCAM-F/TP	120	3	4.2	300	2700	80	40W	15,000	Yes	★	Damp	Frost, Bent tip
			7	21251	LED7DCAM-C3/827	120	6	4.8	500	2700	80	60W	15,000	Yes		Damp	Clear, Bent tip
		3.5		68166	LED3DCAC-C/TP	120	3	4.3	170	2700	80	25W	15,000	Yes	★	Damp	Clear, Bent tip
			4	68165	LED4DCAC-F/TP	120	3	4.3	270	2700	82	25W	15,000	Yes	★	Damp	Frost, Bent tip
				65654	LED4DCAC-C/827	120	3	4.2	300	2700	80	40W	15,000	Yes	★	Damp	Clear, Bent tip
				23691	LED4DCAC-C/5K/TP	120	3	4.2	350	5000	80	40W	15,000	Yes	★	Damp	Frost, Bent tip
				21231	LED4DCAC-C3/827	120	6	4.3	300	2700	80	40W	15,000	Yes		Damp	Clear, Bent tip
				75553	LED4DCACCF/824	120	6	4.3	250	2400	80	25W	15,000	Yes		Damp	Clear, Bent tip
		4.5		89948	LED4.5DCAC-F/TP	120	3	4.2	300	2700	80	40W	15,000	Yes	★	Damp	Frost, Bent tip
				22239	LED4.5DCAC-F5KTP	120	3	4.2	350	5000	80	40W	15,000	Yes	★	Damp	Frost, Bent tip
			7	21233	LED7DCAC-C3/827	120	6	4.8	500	2700	80	60W	15,000	Yes		Damp	Clear, Bent tip
Globes																	
	G16.5	MED	4.5	68169	LED4DG16C-W/TP	120	3	3.0	270	2700	82	25W	15,000	Yes	★	Damp	White
				68170	LED4DG16C-C/TP	120	3	3.0	270	2700	82	25W	15,000	Yes		Damp	Clear
				89952	LED5DG16C-W/TP	120	3	3.0	350	2700	80	40W	15,000	Yes		Damp	White
	G25	MED	4.5	68171	LED4DG25M-W/TP	120	3	4.3	280	2700	82	25W	15,000	Yes	★	Damp	White
				68172	LED4DG25M-C/TP	120	3	4.3	280	2700	82	25W	15,000	Yes		Damp	Clear
			5	64678	LED5DG25M-W/827	120	6	4.3	350	2700	80	40W	15,000	Yes	★	Damp	White
				21253	LED5DG25-W3/827	120	6	4.3	350	2700	80	40W	15,000	Yes		Damp	White
			7	21255	LED7DG25-W3/827	120	6	4.3	500	2700	80	60W	15,000	Yes		Damp	White
Night Lights																	
C7	CAND	0.5	76422	LED1C7/W/CD2	120	6	2			2700			25,000				Dry

A-Line Lamps

Bulb Shape	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (in)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information
A-15																	
	MED	3	63011	LED3A15/W/TP	120	3	3.5	120		3000	80	-	15,000	-		Dry	White
			63012	LED3A15/C/TP	120	3	3.5	120		3000	80	-	15,000	-		Dry	Clear
	MED	4.5	68173	LED4DA15-W/TP	120	3	3.5	270		2700	82	25W	15,000	Yes		Damp	White
			68174	LED4DA15-C/TP	120	3	3.5	270		2700	82	25W	15,000	Yes		Damp	Clear
			14644	LED4.5DA15-C/827	120	6	3.5	300		2700	80	40W	15,000	Yes		Damp	Clear
			23708	LED4.5DA15-W5KTP	120	3	3.5	350		5000	80	40W	15,000	Yes		Damp	White
			23724	LED4.5DA15-C5KTP	120	3	3.5	350		5000	80	40W	15,000	Yes		Damp	Clear
			83645	LED4.5DA15C-FRIG	120	3	3.5	350		5000	80	40W	15,000	Yes		Damp	Clear Refrigerator bulb
A-19																	
	MED	7	14063	LED7DAV3/827W	120	6	4.6	470		2700	80	40W	25,000	Yes		Damp	White, Semi-Omni
			95928	LED7DAV3/5K	120	6	4.6	500		5000	80	40W	25,000	Yes		Damp	White, Semi-Omni
			11332	LED7DA19/827	120	6	4.4	450		2700	80	40W	25,000	Yes	★	Damp	White, Omnidirectional
			71208	LED7DA19/830	120	6	4.4	450		3000	80	40W	25,000	Yes	★	Damp	White, Omnidirectional
			34238	LED7DA19/824	120	6	4.44	450		2400	80	40W	25000	Yes		Damp	White
	10.5	13791	LED11DAV3/827W	120	6	4.6	800		2700	80	60W	15,000	Yes		Damp	White, Semi-Omni	
		95927	LED11DAV3/5K	120	6	4.4	850		5000	80	60W	15,000	Yes		Damp	White, Semi-Omni	
		11	11328	LED11DA19/827	120	6	4.4	800		2700	80	60W	25,000	Yes	★	Damp	White, Omnidirectional
		71209	LED11DA19/830	120	6	4.4	800		3000	80	60W	25,000	Yes	★	Damp	White, Omnidirectional	
		29268	LED11DA19/824	120	6	4.44	800		2400	80	60W	25,000	-		Damp	White	
		74357	LED11DA19827GU24	120	6	5.43	800		2700	80	60W	25,000	-	★	Damp	White	
		A-Line reveal®															
	MED	7	63178	LED7DA19RVLESTP	120	3	4.43	450		2700	84	40w	25,000	Yes		Damp	White, Omnidirectional
		11	63180	LED11DA19RVLESTP	120	3	4.43	800		2700	84	60w	25,000	Yes		Damp	White, Omnidirectional
A-21																	
	MED	12	73384	LED12A21/830FE	120	6	5.31	1100		3000	80	100W	25,000	Yes		Damp	Enclosed
			73404	LED12DA21/850FE	120	6	5.31	1100		5000	80	100W	25,000	Yes		Damp	Enclosed
		13	12422	LED13DA212/827	120	6	5.28	1100		2700	80	75W	25,000	Yes	★	Damp	White, Omnidirectional
		14	94936	LED14DA21/827W	120	6	5.3	1100		2700	80	75W	15,000	Yes		Damp	White, Semi-Omni
		16	14074	LED16DA21/827	120	6	5.3	1600		2700	80	100W	25,000	Yes	★	Damp	White, Omnidirectional
		12349	LED16DA212/827	120	6	5.28	1600		2700	80	100W	25,000	Yes	★	Damp	White, Omnidirectional	

Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

* The life rating is based on the hours of operation the lamp will provide before reaching 70% of its original rating (L70)

** Minimum order quantity = 6

★ ENERGY STAR® status: ENERGY STAR® certified. Lamps without a ★ are not ENERGY STAR® certified.

UL 1993 Environmental Requirements for LED LAMPS

Location, damp - Exterior or interior location that is normally or periodically subject to condensation of moisture in, on, or adjacent to, electrical equipment, and includes partially protected locations.

Location, dry - Location not normally subject to dampness, may include a location subject to temporary dampness, i.e., building under construction, provided ventilation is adequate to prevent an accumulation of moisture.

Location, wet - Location in which water or other liquid can drip, splash, or flow on or against electrical equipment.

Notes: 1) Product descriptions ending in "/TP" indicate a carded blister or clamshell package nested in a tray for shelf display. Cards also designed for hook display.

2) LED A19 Locking device works on PC: 85791, 85792, 89898, 62182, 89899 and 89900

Get more information at

GELighting.com/ThinkLED

LED replacement lamps

A-Line Lamps (Continued)

Bulb Shape	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information
	A-21																
	GU24	92498	LED16DA21827GU24	120	6	5.43	1600			2700	80	100W	25,000	Yes	★	Damp	White
	MED	73376	LED16A30/100/827	120	6	5.31	400/1600/1050			2700	80	30/70/100	25,000	-		Damp	3-Way
		92118	LED16A30/100/5KB	120	3	5.31	400/1600/1050			5000	80	30/70/100	25,000	-			White, 3-Way
		12399	LED16DA212/830	120	6	5.3	1600			3000	80	100W	25,000	Yes	★	Damp	White, Omnidirectional
	17	16113	LED17DA21/827	120	6	5.3	1600			2700	78	100W	15,000	Yes		Damp	White, Semi-Omni
	22	73378	LED22A50/150/827	150	6	5.31	700/2155/1600			2700	80	50/100/150	25,000	-		Damp	3-Way
		92120	LED22A50/150/5KB	120	3	5.31	700/2155/1600			5000	80	50/100/150	25,000	-			White, 3-Way

LED Bright Stik™

Bulb Shape	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information
	LED Bright Stik™																
	MED	10	28089	LED10LS3/828	120	48	4.45	760		2840	80	60	12,000	-		Indoor	Case = 16 3-packs

Reflector Lamps

Bulb Shape	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information
	R20																
	MED	7	13829	LED7DRS20F827	120	6	3.6	470		2700	80		25,000	Yes		Damp	White
			14065	LED7DRS20F830	120	6	3.6	470		3000	80		25,000	Yes		Damp	White
	BR30																
	MED	10	68160	LED10DR303/827W	120	6	5.4	700		2700	80	65W	25,000	Yes	★	Damp	Frosted, White body
			68161	LED10DR303/830W	120	6	5.4	700		3000	80	65W	25,000	Yes	★	Damp	Frosted, White body
	BR30 reveal®																
			83574	LED12DR303RVLES	120	3	5.37	650		2700	90	65W	25,000	Yes	★	Damp	Frosted, White body
	BR40																
	MED	13	64176	LED13DBR40/827	120	6	6.3	1070		2700	80	85W	25,000	Yes	★	Damp	Frosted, White body
			14708	LED13DBR40/830	120	6	6.3	1070		3000	80	85W	25,000	Yes	★	Damp	Frosted, White body

Directional Lamps (MR16 - GU10)

Bulb Shape	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information	
12 Volt AC/DC MR16																		
	MR16	7	93412	LED7DMR16S830/15	12	6	2.3	460	3800	3000	80	35W	25,000	Yes	★	Dry	Accent, 15° beam, Silver	
			69920	LED7DMR16D830/25	12	6	1.9	390	1900	3000	83	35W	25,000	Yes	★	Dry	Accent, 25° beam, Silver	
			69925	LED7DMR16D840/15	12	6	1.9	430	4000	4000	87	35W	25,000	Yes		Dry	Accent, 15° beam, Silver	
			69927	LED7DMR16D840/35	12	6	1.9	430	1200	4000	84	35W	25,000	Yes	★	Dry	Accent, 35° beam, Silver	
			93431	LED7DMR16S827/15	12	6	1.97	440	3700	2700	80	35W	25,000	Yes	★	Dry	Accent, 15° beam, Silver	
			39351	LED7DMR16S830/15	12	6	1.97	420	1100	3000	82	35W	25,000	Yes	★	Dry	Accent, 35° beam, White	
			69949	LED7XDMR16S83025	12	6	1.9	500	2500	3000	82	50W	25,000	Yes	★	Dry	Accent, 25° beam, Silver	
			69950	LED7XDMR16S83035	12	6	1.9	500	1500	3000	82	50W	25,000	Yes	★	Dry	Accent, 35° beam, Silver	
			69951	LED7XDMR16S82725	12	6	1.9	480	2400	2700	80	50W	25,000	Yes	★	Dry	Accent, 25° beam, Silver	
			69952	LED7XDMR16S82735	12	6	1.9	480	1400	2700	80	50W	25,000	Yes	★	Dry	Accent, 35° beam, Silver	
	MRX16	7	39360	LED7DMRX16827/25	12	6	2.2	400	1800	2700	80	35W	25,000	Yes	★	Dry	Accent, 25° beam, White	
			39405	LED7DMRX16827/35	12	6	2.2	400	1000	2700	80	35W	25,000	Yes	★	Dry	Accent, 35° beam, White	
			39408	LED7DMRX16840/25	12	6	2.2	460	2100	4000	83	35W	25,000	Yes	★	Dry	Accent, 25° beam, White	
Value 12 Volt AC/DC MR16																		
		6	39468	LED6DMR16-V82735	12	6	1.8	430	1150	2700	80	35W	25,000	Yes		Dry	Accent, 35° beam, White	
			39438	LED6DMR16-V83035	12	6	1.8	460	1200	3000	80	35W	25,000	Yes		Dry	Accent, 35° beam, White	
			39472	LED6DMR16-V84035	12	6	1.8	500	1300	4000	80	35W	25,000	Yes		Dry	Accent, 35° beam, White	
		7	39473	LED7XDMR16-V8325	12	6	1.88	550	2400	3000	80	50W	25,000	Yes		Dry	Accent, 25° beam, White	
			39483	LED7XDMR16-V8335	12	6	1.88	550	1400	3000	80	50W	25,000	Yes		Dry	Accent, 35° beam, White	
			39542	LED7XDMR16-V2725	12	6	1.88	530	2400	2700	80	50W	25,000	Yes		Dry	Accent, 25° beam, White	
			39567	LED7XDMR16-V2735	12	6	1.88	530	1400	2700	80	50W	25,000	Yes		Dry	Accent, 35° beam, White	
120 Volt GU10																		
	MR16	GU10	4	89020	LED4D/GU10/NFLTP	120	3	2.3	250	720	3000	80	35W	25,000	Yes	★	Dry	Accent, 35° beam, White
			6	26346	LED6D/GU10/NFL/TP	120	3	2.3	380	1100	3000	80	50W	25,000	Yes	★	Dry	Accent, 35° beam, White

Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

* The life rating is based on the hours of operation the lamp will provide before reaching 70% of its original rating (L70)

** Minimum order quantity = 6

★ ENERGY STAR® status: ENERGY STAR® certified. Lamps without a ★ are not ENERGY STAR® certified.

UL 1993 Environmental Requirements for LED LAMPS

Location, damp - Exterior or interior location that is normally or periodically subject to condensation of moisture in, on, or adjacent to, electrical equipment, and includes partially protected locations.

Location, dry - Location not normally subject to dampness, may include a location subject to temporary dampness, i.e., building under construction, provided ventilation is adequate to prevent an accumulation of moisture.

Location, wet - Location in which water or other liquid can drip, splash, or flow on or against electrical equipment.

Notes: 1) Product descriptions ending in "/TP" indicate a carded blister or clamshell package nested in a tray for shelf display. Cards also designed for hook display. 2) LED A19 Locking device works on PC: 85791, 85792, 89898, 62182, 89899 and 89900

Get more information at
GELighting.com/ThinkLED

LED replacement lamps

Directional Lamps (PAR16 - PAR20)

Bulb Shape	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information
Compact PAR16																	
	MED	4	26383	LED4D/P16/NFLTP	120	3	2.8	250	720	3000	80	40W	25,000	Yes	★	Dry	Accent, 35° beam, White
		6	26384	LED6D/P16/NFLTP	120	3	2.8	380	1100	3000	80	60W	25,000	Yes	★	Dry	Accent, 35° beam, White
Compact PAR20																	
	MED	7	92121	LED7DP203NFL5KTP	120	3	3.5	550	4000	5000	80	70w	25,000	Yes	★	Damp	Accent, 20° beam White
			93327	LED7DP203B830/20	120	6	3.5	520	3600	3000	80	70W	25,000	Yes	★	Damp	Accent, 20° beam Black
	MED	7	93347	LED7DP203W830/20	120	6	3.5	520	3600	3000	80	70W	25,000	Yes	★	Damp	Accent, 20° beam White
			93348	LED7DP203W830/35	120	6	3.5	520	1200	3000	80	65W	25,000	Yes	★	Damp	Accent, 35° beam White
			93349	LED7DP203B827/20	120	6	3.5	500	3600	2700	80	70W	25,000	Yes	★	Damp	Accent, 20° beam Black
			93354	LED7DP203B827/35	120	6	3.5	500	1150	2700	80	65W	25,000	Yes	★	Damp	Accent, 35° beam Black
			93360	LED7DP203W827/20	120	6	3.5	500	3600	2700	80	70W	25,000	Yes	★	Damp	Accent, 20° beam White
			93362	LED7DP203W827/35	120	6	3.5	500	1150	2700	80	65W	25,000	Yes	★	Damp	Accent, 35° beam White

Directional Lamps (PAR30 - Low Glare - Visual Comfort Lens™)

Bulb Shape	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information
Compact PAR30 - Low Glare - Visual Comfort Lens™																	
	MED	12	67925	LED12DP30R927/15	120	6	3.8	820	5350	2700	91	65W	25,000	Yes		Dry	Accent, 15° beam, Silver
			67926	LED12DP30R927/25	120	6	3.8	820	2950	2700	91	75W	25,000	Yes		Dry	Accent, 25° beam, Silver
			84379	LED12DP30RW93025	120	6	3.74	900	3900	3000	90	75W	25,000	Yes	★	Dry	Narrow Flood, 25° beam, White
			84380	LED12DP30RW93040	120	6	3.74	900	1800	3000	90	75W	25,000	Yes	★	Dry	Flood, 40° beam, White
			84392	LED12DP30RW92725	120	6	3.74	850	3500	2700	90	75W	25,000	Yes	★	Dry	Narrow Flood, 25° beam, White
			84395	LED12DP30RW92740	120	6	3.74	850	1700	2700	90	75W	25,000	Yes	★	Dry	Flood, 40° beam, White
			84384	LED12DP30RW83025	120	6	3.74	1050	4800	3000	80	75W	25,000	Yes	★	Dry	Narrow Flood, 25° beam, White
			42131	LED12DP30RW83040	120	6	3.74	1050	2400	3000	80	75W	25,000	Yes	★	Dry	Flood, 40° beam, White
			42133	LED12DP30RW82725	120	6	3.74	1000	4700	2700	80	75W	25,000	Yes	★	Dry	Narrow Flood, 25° beam, White
			42134	LED12DP30RW82740	120	6	3.74	1000	2200	2700	80	75W	25,000	Yes	★	Dry	Flood, 40° beam, White
	73583	LED12DP30RB82740	120	6	3.74	1000	2200	2700	80	75W	25,000	Yes	★	Dry	Flood, 40° beam, Black		
Compact PAR30 - Long Neck - Low Glare - Visual Comfort Lens™																	
	MED	12	68390	LED12DP3LR927/15	120	6	4.8	820	5350	2700	91	65W	50,000	Yes		Dry	Accent, 15° beam, Silver
			68391	LED12DP3LR927/25	120	6	4.8	820	2950	2700	91	75W	50,000	Yes		Dry	Accent, 25° beam, Silver
			84399	LED12DP3LRW93025	120	6	4.72	900	3900	3000	90	75W	25,000	Yes	★	Dry	Narrow Flood, 25° beam, White
			84400	LED12DP3LRW93040	120	6	4.72	900	1800	3000	90	75W	25,000	Yes	★	Dry	Flood, 40° beam, White
			84407	LED12DP3LRW92740	120	6	4.72	850	1700	2700	90	75W	25,000	Yes	★	Dry	Flood, 40° beam, White
			42136	LED12DP3LRW83025	120	6	4.72	1050	4800	3000	80	75W	25,000	Yes	★	Dry	Narrow Flood, 25° beam, White
			42137	LED12DP3LRW83040	120	6	4.72	1050	2400	3000	80	75W	25,000	Yes	★	Dry	Flood, 40° beam, White
			42144	LED12DP3LRW82740	120	6	4.72	1000	2200	2700	80	75W	25,000	Yes	★	Dry	Flood, 40° beam, White
			20135	LED17DP30LW93015	120	6	4.8	1100	12000	3000	90	75W	25,000	Yes	★	Damp	Spot, 15° beam, White
			20151	LED17DP30LW93025	120	6	4.8	1100	4600	3000	90	75W	25,000	Yes	★	Damp	Spot, 25° beam, White

Directional Lamps (PAR30)

Bulb Shape	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information
Compact PAR30																	
	MED	12	94220	LED12DP302W82735	120	6	3.7	850	2300	2700	84	85W	25,000	Yes	★	Damp	Flood, 35° beam, White
			98755	LED12DP303W83035	120	6	3.66	950	2600	3000	80	85W	25,000	Yes	★	Damp	Flood, 35° beam, White, STIR
Compact PAR30 Long Neck																	
	MED	12	98811	LED12DP3L3W83035	120	6	4.61	950	2600	3000	80	85W	25,000	Yes	★	Damp	Accent, 35° beam, White, STIR

Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

* The life rating is based on the hours of operation the lamp will provide before reaching 70% of its original rating (L70)

** Minimum order quantity = 6

★ ENERGY STAR® status: ENERGY STAR® certified. Lamps without a "★" are not ENERGY STAR® certified.

UL 1993 Environmental Requirements for LED LAMPS

Location, damp – Exterior or interior location that is normally or periodically subject to condensation of moisture in, on, or adjacent to, electrical equipment, and includes partially protected locations.

Location, dry – Location not normally subject to dampness, may include a location subject to temporary dampness, i.e., building under construction, provided ventilation is adequate to prevent accumulation of moisture.

Location, wet – Location in which water or other liquid can drip, splash, or flow on or against electrical equipment.

Notes: 1) Product descriptions ending in "TP" indicate a carded blister or clamshell package nested in a tray for shelf display. Cards also designed for hook display.

2) LED A19 Locking device works on PC: 85791, 85792, 89898, 62182, 89899 and 89900

Get more information at

GELighting.com/ThinkLED

LED replacement lamps

Directional Lamps (PAR38 - Low Glare - Visual Comfort Lens™)

Bulb Shape	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information
PAR38 - Low Glare - Visual Comfort Lens™																	
	MED	12	63233	LED12DP38W830/25	120	6	5.3	1000	4800	3000	80	90W	25,000	Yes		Dry	Narrow Flood, 25° beam, White
			63323	LED12DP38W827/25	120	6	5.3	960	4600	2700	80	90W	25,000	Yes		Dry	Narrow Flood, 25° beam, White
			63330	LED12DP38W930/15	120	6	5.3	860	11400	3000	91	90W	25,000	Yes		Dry	Spot, 15° beam, White
			63334	LED12DP38W927/25	120	6	5.3	820	3900	2700	91	90W	25,000	Yes		Dry	Narrow Flood, 25° beam, White
			92971	LED12D38W3827/40	120	6	5.31	1050	2300	2700	81	100W	25,000	Yes	★	Damp	Flood, 40° beam, White
	18		92972	LED12D38W3830/25	120	6	5.31	1050	5500	3000	81	100W	25,000	Yes	★	Damp	Narrow Flood, 25° beam, White
			94904	LED18D38W930/25	120	6	5.3	1200	4400	3000	91	100W	25,000	Yes	★	Damp	Narrow Flood, 25° beam, White
			92923	LED18D38W3927/25	120	6	5.31	1250	4900	2700	92	100W	25,000	Yes	★	Damp	Narrow Flood, 25° beam, White
			92934	LED18D38W3930/40	120	6	5.12	1350	3200	3000	92	120W	25,000	Yes	★	Damp	Flood, 40° beam, White
			92958	LED18D38OW382740	120	6	5.12	1550	3800	2700	81	120W	25,000	Yes	★	Wet	Flood, 40° beam, White
			92963	LED18D38OW383025	120	6	5.12	1550	6000	3000	81	120W	25,000	Yes	★	Wet	Narrow Flood, 25° beam, White
			92967	LED18D38OW383040	120	6	5.12	1550	4000	3000	81	150W	25,000	Yes	★	Wet	Flood, 40° beam, White
			92926	LED18D38W3927/40	120	6	5.12	1250	2900	2700	92	120W	25,000	Yes	★	Dry	Flood, 40° beam, White
			93172	LED18D38OW384040	120	6	5.31	1700	4400	4000	81	150W	25,000	Yes	★	Wet	Flood, 40° beam, White
			65730	LED18D38OW385025	120	6	5.31	1700	6500	5000	81	120W	25,000	Yes	★	Wet	Narrow Flood, 25° beam, White
			65731	LED18D38OW385040	120	6	5.31	1700	4400	5000	81	150W	25,000	Yes	★	Wet	Flood, 40° beam, White

Directional Lamps (Commercial PAR38)

Bulb Shape	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information	
Commercial PAR38 (Indoor/Outdoor)																		
	MED	12	90150	LED12DP382W83025	120	6	5.1	950	4400	3000	84	85W	25,000	Yes	★	Wet	Narrow Flood, 25° beam, White	
			90151	LED12DP382W83035	120	6	5.1	950	2700	3000	84	85W	25,000	Yes	★	Wet	Flood, 35° beam, White	
			90132	LED12DP382W82725	120	6	5.1	850	4000	2700	84	85W	25,000	Yes	★	Wet	Narrow Flood, 25° beam, White	
			18	90154	LED18DP38W827/25	120	6	5.1	1200	7000	2700	84	100W	25,000	Yes	★	Wet	Narrow Flood, 25° beam, White
				90162	LED18DP38W840/25	120	6	5.1	1400	8200	4000	84	100W	25,000	Yes	★	Wet	Narrow Flood, 25° beam, White
	26		22235	LED18DP38FL5K/TP	120	3	5.1	1500	3200	5000	84	100W	25,000	Yes	★	Wet	Flood, 40° beam, White	
			68183	LED26DP38S830/12	120	6	5.3	1500	24000	3000	82	130W	25,000	Yes	★	Wet	Spot, 12° beam, Silver	
			68184	LED26DP38S830/25	120	6	5.3	1500	6800	3000	82	130W	25,000	Yes	★	Wet	Narrow Flood, 25° beam, Silver	
			68185	LED26DP38S830/40	120	6	5.3	1500	3100	3000	82	120W	25,000	Yes	★	Wet	Flood, 40° beam, Silver	
			68182	LED26DP38S840/40	120	6	5.3	1650	3200	4000	82	120W	25,000	Yes	★	Wet	Flood, 40° beam, Silver	
			33647	LED26DP38S835/12	120	6	5.3	1900	31000	3500	82	160W	25,000	Yes	★	Wet	Spot, 12° beam, Silver	
			70591	LED26DP38S835/40	120	6	5.3	1900	4000	3500	82	160W	25,000	Yes	★	Wet	Flood, 40° beam, Silver	
			28	15139	LED28P38S830/15	120	6	5.3	2400	20000	3000	81	150W	25,000	-	★	Dry	Spot, 15° beam, Silver, Non-Dimming
				25844	LED28P38S830/25	120	6	5.31	2400	11,000	3000	81	150W	25,000	-	★	Dry	Narrow Flood, 25° beam, Silver, Non-Dimming
				25953	LED28P38S830/40	120	6	5.31	2400	5,600	3000	81	150W	25,000	-	★	Dry	Flood, 40° beam, Silver, Non-Dimming

LED HID

Bulb Shape	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information
400 Watt HID Replacement Lamp																	
	EX39	165	21259	LED165/M400/740		3	11.42	20,000		4000	73	400	50,000	-		Dry	Open Rated, ANSI - M59, M135, M155

Plug-In

Bulb Shape	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)	Dimmable	#Location Rating	Additional Information
Vertical																
	G24q/GX24	12	96801	LED12G24Q-V/827	#	6	5.31	950		2700	80		50000	-	Dry	Vertical Plug-in, White
			96775	LED12G24Q-V/830	#	6	5.31	950		3000	80		50000	-	Dry	Vertical Plug-in, White
			96689	LED12G24Q-V/835	#	6	5.31	1000		3500	80		50000	-	Dry	Vertical Plug-in, White
			96771	LED12G24Q-V/840	#	6	5.31	1000		4000	80		50000	-	Dry	Vertical Plug-in, White
Horizontal																
	G24q/GX24	12	96799	LED12G24Q-H/827	#	6	5.31	950		2700	80		50000	-	Dry	Horizontal Plug-in, White
			96798	LED12G24Q-H/830	#	6	5.31	950		3000	80		50000	-	Dry	Horizontal Plug-in, White
			96761	LED12G24Q-H/835	#	6	5.31	1000		3500	80		50000	-	Dry	Horizontal Plug-in, White
			96769	LED12G24Q-H/840	#	6	5.31	1000		4000	80		50000	-	Dry	Horizontal Plug-in, White

- Check compatibility at GELighting.com/LED4pin-compatibility

Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

* The life rating is based on the hours of operation the lamp will provide before reaching 70% of its original rating (L70)

** Minimum order quantity = 6

★ ENERGY STAR® status: ENERGY STAR® certified. Lamps without a ★ are not ENERGY STAR® certified.

UL 1993 Environmental Requirements for LED LAMPS

Location, damp - Exterior or interior location that is normally or periodically subject to condensation of moisture in, on, or adjacent to, electrical equipment, and includes partially protected locations.

Location, dry - Location not normally subject to dampness, may include a location subject to temporary dampness, i.e., building under construction, provided ventilation is adequate to prevent an accumulation of moisture.

Location, wet - Location in which water or other liquid can drip, splash, or flow on or against electrical equipment.

Notes: 1) Product descriptions ending in "/TP" indicate a carded blister or clamshell package nested in a tray for shelf display. Cards also designed for hook display.
2) LED A19 Locking device works on PC: 85791, 85792, 89898, 62182, 89899 and 89900

Get more information at
GELighting.com/ThinkLED

LED Tubes
Integrated and Refit

Type	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)	DLC	UL	#Location Rating	Additional Information
Integrated 4ft LED Tubes (operates on Instant Start or Program Start Ballast)																
T8	G13	18	31550	LED18ET8/4/830		25	48	2200	3000K	80+		50,000	Yes	Yes	Damp	Dimmability Requires PRS Ballast
	G13	18	93133	LED18ET8/4/835		25	48	2200	3500K	80+		50,000	Yes	Yes	Damp	Dimmability Requires PRS Ballast
	G13	18	93135	LED18ET8/4/840		25	48	2200	4000K	80+		50,000	Yes	Yes	Damp	Dimmability Requires PRS Ballast
	G13	18	93140	LED18ET8/4/850		25	48	2200	5000K	80+		50,000	Yes	Yes	Damp	Dimmability Requires PRS Ballast
Integrated 3ft LED Tubes (operates on Instant Start or Program Start Ballast)																
G13	12	31554	LED12ET8/3/830		25	36	1400	3000K	80+			50,000	-	Yes	Damp	Dimmability Requires PRS Ballast
	12	26544	LED12ET8/3/835		25	36	1400	3500K	80+			50,000	-	Yes	Damp	Dimmability Requires PRS Ballast
	12	26625	LED12ET8/3/840		25	36	1400	4000K	80+			50,000	-	Yes	Damp	Dimmability Requires PRS Ballast
	12	26627	LED12ET8/3/850		25	36	1400	5000K	80+			50,000	-	Yes	Damp	Dimmability Requires PRS Ballast
Integrated 2ft LED Tubes (operates on Instant Start or Program Start Ballast)																
G13	9	31557	LED9ET8/2/830		25	24	1100	3000K	80+			50,000	-	Yes	Damp	Dimmability Requires PRS Ballast
	9	26635	LED9ET8/2/835		25	24	1100	3500K	80+			50,000	-	Yes	Damp	Dimmability Requires PRS Ballast
	9	26648	LED9ET8/2/840		25	24	1100	4000K	80+			50,000	-	Yes	Damp	Dimmability Requires PRS Ballast
	9	26676	LED9ET8/2/850		25	24	1100	5000K	80+			50,000	-	Yes	Damp	Dimmability Requires PRS Ballast
Refit 4 ft LED Tubes (operates with Remote Driver)																
T8	G13	16	88138	LED18T8/4/850/BT		25	48	2300	5000K	80+		50,000	Yes	Yes	Damp	Requires Driver / Dimming Driver
	G13	18	94381	LED21T8/4/835		10	48	2100	3500K	80+		50,000	Yes	Yes	Damp	Requires Driver / Dimming Driver
	G13	18	94382	LED21T8/4/840		10	48	2100	4000K	80+		50,000	Yes	Yes	Damp	Requires Driver / Dimming Driver
	G13	18	94383	LED21T8/4/850		10	48	2200	5000K	80+		50,000	Yes	Yes	Damp	Requires Driver / Dimming Driver
	G13	18	26059	LED21T8/4/865		10	48	2200	6500K	80+		50,000	-	Yes	Damp	Requires Driver / Dimming Driver
	G13	18	62428	LED21T8/G/4/835		10	48	2200	3500K	80+		50,000	Yes	Yes	Damp	Requires Driver / Dimming Driver
	G13	18	62485	LED21T8/G/4/840		10	48	2200	4000K	80+		50,000	Yes	Yes	Damp	Requires Driver / Dimming Driver
	G13	18	62487	LED21T8/G/4/850		10	48	2300	5000K	80+		50,000	Yes	Yes	Damp	Requires Driver / Dimming Driver
Refit 3 ft LED Tubes (Operates with Remote Driver)																
T8	G13	16	82343	LED18T8/3/835		10	36	1800	3500K	80+		50,000	-	Yes	Damp	Requires Driver / Dimming Driver
	G13	16	82345	LED18T8/3/840		10	36	1800	4000K	80+		50,000	-	Yes	Damp	Requires Driver / Dimming Driver
	G13	16	82346	LED18T8/3/850		10	36	1800	5000K	80+		50,000	-	Yes	Damp	Requires Driver / Dimming Driver
Refit 2 ft LED Tubes (Operates with Remote Driver)																
T8	G13	8	92997	LED9T8/2/865		20	24	900	6500K	80+		50,000	-	Yes	Damp	Requires Driver / Dimming Driver
	G13	8	65706	LED9T8/2/835		20	24	900	3500K	80+		50,000	Yes	Yes	Damp	Requires Driver / Dimming Driver
	G13	8	65707	LED9T8/2/840		20	24	900	4000K	80+		50,000	Yes	Yes	Damp	Requires Driver / Dimming Driver
	G13	8	65711	LED9T8/2/850		20	24	900	5000K	80+		50,000	Yes	Yes	Damp	Requires Driver / Dimming Driver
Refit LED U-Tubes (Operates with Remote Driver)																
T8	G13	12	28084	LED14T8/U/835		15	U -1 5/8	1700	3500K	80+		50,000	-	Yes	Damp	Requires Driver / Dimming Driver
	G13	12	28164	LED14T8/U/840		15	U -1 5/8	1700	4000K	80+		50,000	-	Yes	Damp	Requires Driver / Dimming Driver

Remote Drivers

Type	Base Type	Watts	Order Code	Description	Volts	Case Qty**	Output Current (A)	Frequency	Eff	Output	Output Voltage	Temp (Min)	Temp (Max)	Dimmable	Additional Information
Lightech Drivers - Non-Dimming															
		18	93100	LED9T8/DR/UN/2L	120-277V	10	0.27x2	50/60 Hz	>.9	DC	27-33V	-4 F	104 F	-	Maximum 2 Tubes (non potted)
		36	82347	LED18T8/DR/UN/2L	120-277V	10	0.35	50/60 Hz	>.9	DC	27-33V	-4 F	104 F	-	Maximum 2 Tube (non potted)
		21	94384	LED21T8/DR/1L	120-277V	10	0.62	50/60 Hz	>.9	DC	27-33V	-4 F	104 F	-	Maximum 1 Tube
		42	94385	LED21T8/DR/2L	120-277V	10	0.62x2	50/60 Hz	>.9	DC	27-33V	-4 F	104 F	-	Maximum 2 Tube
Lightech Drivers - Dimming															
		36	88141	LED18T8/DR/D2L	120-277V	10	0.53x2	50/60 Hz	>.9	DC	27-33V	-4 F	104 F	Yes	Maximum 2 Tube
		72	88139	LED18T8/DR/D4L	120-277V	10	0.53x4	50/60 Hz	>.9	DC	27-33V	-4 F	104 F	Yes	Maximum 4 Tube
		42	60041	LED21T8/DR/D2L	120-277V	10	0.62x2	50/60 Hz	>.9	DC	27-33V	-4 F	104 F	Yes	Maximum 2 Tube
		84	62030	LED21T8/DR/D4L	120-277V	10	0.62x4	50/60 Hz	>.9	DC	27-33V	-4 F	104 F	Yes	Maximum 4 Tube
		42	28174	LED14/DR/D3L	120-277V	10	0.43x3	50/60 Hz	>.9	DC	27-33V	-4 F	104 F	Yes	Maximum 3 Tube

Awaken like never before the moment
you turn on GE's LED replacement lamp.

Light influences people's emotions, how they view their space and
their world, and how they start and end their day. GE understands
this and wants to help transform your stores, buildings or
facilities, while ensuring your upfront investment is paid
back as quickly as possible.

If you're inspired to enhance your space
— with substantial savings — call your
GE Lighting representative.

To experience what we've done for our
existing customers, see case studies,
videos and image galleries at
gelighting.com/ThinkLED



Product is compliant with material restriction requirements of RoHS

ENERGY STAR® is a registered U.S. mark



www.gelighting.com

GE and the GE Monogram are trademarks of the General Electric Company. All other trademarks are the property of their respective owners. Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions. GE Lighting and GE Lighting Solutions, LLC are businesses of the General Electric Company. © 2015 GE.

78945 (Rev 9/4/2015)