



GREENCREATIVE

Bringing You the Latest in LED Technology


REFINE
SERIES





PAR REFINE SERIES

PATENT PENDING REFINE OPTIC

The innovative REFINE optic provides a high candela to lumen output ratio, optimizing light usage for directional applications.



WATCH THE VIDEO



SLEEK DESIGN - SUPERIOR PERFORMANCE




PAR LINE

PAR38 17W DIM.



- 120W halogen replacement
- 2700K / 3000K / 4000K CCT
- Spot / Narrow Flood / Flood beam angles
- 120-277V & GU24 versions available

3000K NF Candela




Degree	Candela
0	5400
5	4875
15	143
25	294
35	106
45	85

PAR30 12.5W DIM.




- 75W halogen replacement
- 2700K / 3000K / 4000K CCT
- Spot / Narrow Flood / Flood beam angles
- 120-277V & GU24 versions available

3000K NF Candela




Degree	Candela
0	3600
5	3100
15	1230
25	258
35	74
45	44

PAR30SN 11W DIM.



- 75W halogen replacement
- 2700K / 3000K / 4000K CCT
- Spot / Narrow Flood / Flood beam angles

3000K NF Candela




Degree	Candela
0	2910
5	2506
15	994
25	209
35	59
45	35

PAR20 7W DIM.











- 50W halogen replacement
- 2700K / 3000K / 4000K CCT
- Flood beam angle

3000K FL Candela



Degree	Candela
0	650
5	646
15	444
25	205
35	120
45	80

SPECIFICATIONS*

	Model	Product	CCT	Lumens (lm)	Equiv. LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	Encl.		
 PAR38 17W	18.5PAR38G4DIM/927SP15	16147	2700K	950	100W	51	15°	10,500	90	Yes	40,000	120V	Yes	✓
	18.5PAR38G4DIM/927NF25	16148	2700K	950	120W	51	25°	5390	90	Yes	40,000	120V	Yes	✓
	17PAR38G4DIM/927FL40	16149	2700K	1105	120W	65	40°	2400	90	Yes	40,000	120V	Yes	✓
	18.5PAR38G4DIM/930SP15	16150	3000K	1000	100W	54	15°	11,000	90	Yes	40,000	120V	Yes	✓
	18.5PAR38G4DIM/930NF25	16151	3000K	1000	120W	54	25°	5400	90	Yes	40,000	120V	Yes	✓
	17PAR38G4DIM/930FL40	16152	3000K	1150	120W	68	40°	2500	90	Yes	40,000	120V	Yes	✓
	17PAR38G4DIM/940FL40	16155	4000K	1200	120W	71	40°	2650	90	Yes	40,000	120V	Yes	✓
	18.5PAR38G4DIM/930SP15/B ●	16256	3000K	1000	100W	54	15°	11,000	90	Yes	40,000	120V	Yes	✓
	18.5PAR38G4DIM/930NF25/B ●	16257	3000K	1000	120W	54	25°	5400	90	Yes	40,000	120V	Yes	✓
	17PAR38G4DIM/930FL40/B ●	16258	3000K	1150	120W	68	40°	2500	90	Yes	40,000	120V	Yes	✓
 PAR38 17W 277V	17PAR38G4/930FL40/277V	16161	3000K	1150	120W	68	40°	2500	90	No	40,000	120-277V	Yes	✓
	17PAR38G4/940FL40/277V	16164	4000K	1200	120W	71	40°	2650	90	No	40,000	120-277V	Yes	✓
 PAR38 17W GU24	17PAR38G4DIM/927FL40/GU24	16303	2700K	1105	120W	65	40°	2400	90	Yes	40,000	120V	Yes	✓
	17PAR38G4DIM/930FL40/GU24	16306	3000K	1150	120W	68	40°	2500	90	Yes	40,000	120V	Yes	✓
 PAR30 12.5W	14.5PAR30G4DIM/927SP15	16111	2700K	725	75W	50	15°	6155	90	Yes	40,000	120V	Yes	✓
	12.5PAR30G4DIM/927NF25	16112	2700K	815	75W	65	25°	3350	90	Yes	40,000	120V	Yes	✓
	12.5PAR30G4DIM/927FL40	16113	2700K	815	75W	65	40°	1750	90	Yes	40,000	120V	Yes	✓
	14.5 PAR30G4DIM/930SP15	16114	3000K	760	75W	52	15°	6250	90	Yes	40,000	120V	Yes	✓
	12.5PAR30G4DIM/930NF25	16115	3000K	850	75W	68	25°	3600	90	Yes	40,000	120V	Yes	✓
	12.5PAR30G4DIM/930FL40	16116	3000K	850	75W	68	40°	1850	90	Yes	40,000	120V	Yes	✓
	12.5PAR30G4DIM/940FL40	16119	4000K	900	75W	72	40°	2050	90	Yes	40,000	120V	Yes	✓
	14.5PAR30G4DIM/930SP15/B ●	16208	3000K	760	75W	52	15°	6250	90	Yes	40,000	120V	Yes	✓
	12.5PAR30G4DIM/930NF25/B ●	16209	3000K	850	75W	68	25°	3600	90	Yes	40,000	120V	Yes	✓
	12.5PAR30G4DIM/930FL40/B ●	16210	3000K	850	75W	68	40°	1850	90	Yes	40,000	120V	Yes	✓
 PAR30 12.5W 277V	12.5PAR30G4/930FL40/277V	16125	3000K	850	75W	68	40°	1850	90	No	40,000	120-277V	Yes	✓
	12.5PAR30G4/940FL40/277V	16128	4000K	900	75W	72	40°	2050	90	No	40,000	120-277V	Yes	✓
 PAR30 12.5W GU24	12.5PAR30G4DIM/927FL40/GU24	16279	2700K	815	75W	65	40°	1750	90	Yes	40,000	120V	Yes	✓
	12.5PAR30G4DIM/930FL40/GU24	16282	3000K	850	75W	68	40°	1850	90	Yes	40,000	120V	Yes	✓
 PAR30SN 11W	14PAR30SNG4DIM/927SP15	16129	2700K	700	75W	50	15°	6155	90	Yes	40,000	120V	Yes	✓
	11PAR30SNG4DIM/927NF25	16130	2700K	705	75W	64	25°	2910	90	Yes	40,000	120V	Yes	✓
	11PAR30SNG4DIM/927FL40	16131	2700K	705	75W	64	40°	1400	90	Yes	40,000	120V	Yes	✓
	14PAR30SNG4DIM/930SP15	16132	3000K	725	75W	52	15°	6200	90	Yes	40,000	120V	Yes	✓
	11PAR30SNG4DIM/930NF25	16133	3000K	740	75W	67	25°	2910	90	Yes	40,000	120V	Yes	✓
	11PAR30SNG4DIM/930FL40	16134	3000K	740	75W	67	40°	1450	90	Yes	40,000	120V	Yes	✓
	11PAR30SNG4DIM/940FL40	16137	4000K	780	75W	71	40°	1500	90	Yes	40,000	120V	Yes	✓
	14PAR30SNG4DIM/930SP15/B ●	16232	3000K	725	75W	52	15°	6200	90	Yes	40,000	120V	Yes	✓
	11PAR30SNG4DIM/930NF25/B ●	16233	3000K	740	75W	67	25°	2910	90	Yes	40,000	120V	Yes	✓
	11PAR30SNG4DIM/930FL40/B ●	16234	3000K	740	75W	67	40°	1450	90	Yes	40,000	120V	Yes	✓
 PAR20 7W	7PAR20G4DIM/927FL40	16108	2700K	460	50W	66	40°	600	90	Yes	40,000	120V	Yes	✓
	7PAR20G4DIM/930FL40	16109	3000K	480	50W	69	40°	650	90	Yes	40,000	120V	Yes	✓
	7PAR20G4DIM/940FL40	16110	4000K	505	50W	69	40°	700	90	Yes	40,000	120V	Yes	✓
	7PAR20G4DIM/930FL40/B ●	16202	3000K	480	50W	72	40°	650	90	Yes	40,000	120V	Yes	✓

* PAR38 models are suitable for use in wet locations
● Black finish



GREEN CREATIVE
1200 Bayhill Drive, Suite 220
San Bruno, CA 94066

Tel / Fax: (866) 774-5433
info@greencreative.com
www.greencreative.com

f / GREENCREATIVELED
t / GClightingLED
in / GREEN CREATIVE