

## INSULATING PLASTIC BUSHINGS

### 105°C FLAME RETARDANT

THERMOPLASTIC


CAT#	A	B
831	1.06	.43
832	1.31	.43
833	1.59	.48
834	1.96	.56
835	2.18	.56
836	2.68	.59
837	3.25	.72
838	3.87	.75
839	4.37	.77
840	5.00	.77
840A	6.25	1.00
840B	7.50	1.00

TOPAZ CAT #	UPC#	SIZE	UNIT CTN	SHIP CASE	WT/ CASE
831	18450	1/2"	100	1000	6
832	18460	3/4"	100	1000	9
833	18470	1"	50	500	11
834	18480	1 1/4"	25	250	5
835	18490	1 1/2"	25	250	7
836	18500	2"	20	200	12
837	18510	2 1/2"	—	50	5
838	18520	3"	—	25	3
839	18530	3 1/2"	—	25	5
840	18540	4"	—	10	7
840A	18550	5"	—	10	3
840B	18560	6"	—	10	4

DOWNLOAD SPEC SHEET



E148716



## RIGID BUSHINGS

### INSULATED

• 105° C. THERMOPLASTIC LINERS

ZINC DIE CAST

CAT#	A	B
311	1.053	.394
312	1.327	.394
313	1.584	.477
314	1.952	.503
315	2.201	.522
316	2.693	.564
317	3.235	.866
318	3.855	.866
319	4.359	.866
320	5.011	.866

TOPAZ CAT #	UPC#	SIZE	UNIT CTN	SHIP CASE	WT/ CASE
311	12730	1/2"	100	1000	30
312	12740	3/4"	50	500	20
313	12750	1"	50	500	40
314	12760	1 1/4"	25	250	25
315	12770	1 1/2"	25	250	30
316	12780	2"	—	100	14
317	12790	2 1/2"	—	50	20
318	12800	3"	—	25	12
319	12810	3 1/2"	—	25	14
320	12820	4"	—	10	6

DOWNLOAD SPEC SHEET



E170258

CAT#	A	B
311M	1.223	.506
312M	1.498	.547
313M	1.818	.662
314M	2.423	.735
315M	2.512	.808
316M	3.053	.808
317M	3.624	.958
318M	4.172	1.052
319M	4.767	1.169
320M	5.321	1.178
320AM	6.15	1.30
320BM	7.19	1.30


MALLEABLE IRON

TOPAZ CAT #	UPC#	SIZE	UNIT CTN	SHIP CASE	WT/ CASE
311M	12830	1/2"	100	1000	20
312M	12840	3/4"	50	500	20
313M	12850	1"	50	500	40
314M	12860	1 1/4"	25	250	43
315M	12870	1 1/2"	25	100	25
316M	12880	2"	10	100	30
317M	12890	2 1/2"	—	50	20
318M	12900	3"	—	25	13
319M	12910	3 1/2"	—	25	18
320M	12920	4"	—	10	10
320AM	12922	5"	—	10	25
320BM	12924	6"	—	10	35

DOWNLOAD SPEC SHEET



E170258




CAT#	A	B
981	1.35	1.40
982	1.62	1.40

## RIGID MALE ENLARGERS

ZINC DIE CAST

TOPAZ CAT #	UPC#	SIZE	UNIT CTN	SHIP CASE	WT/ CASE
981	19640	1/2" M x 3/4" F	25	250	50
982	19650	3/4" M x 1" F	10	100	12



CAT#	A	B
321	1.25	.50
322	1.50	.50
323	1.75	.56
324	2.12	.62
325	2.37	.75
326	2.81	.75
327	3.62	.93
328	4.18	.93
329	4.68	.93
330	5.25	.93
321M	1.25	.50
322M	1.48	.54
323M	1.80	.65
324M	2.40	.73
325M	2.50	.80
326M	3.03	.80
327M	3.60	.95
328M	4.16	1.03
329M	4.75	1.15
330M	5.30	1.17
330AM	6.15	1.130
330BM	7.19	1.130

## INSULATED METALLIC GROUNDING BUSHINGS WITH ALUMINUM LUG

- FOR COPPER OR ALUMINUM BARE GROUND WIRE
- 105° C. THERMOPLASTIC LINERS

ZINC DIE CAST

TOPAZ CAT #	UPC#	SIZE	GROUNDING LUG WIRE SIZE		UNIT CTN	SHIP CASE	WT/ CASE
			MIN	MAX			
321	12930	1/2"	14	4	50	500	25
322	12940	3/4"	14	4	50	500	35
323	12950	1"	14	4	25	250	30
324	12960	1 1/4"	14	4	20	200	34
325	12970	1 1/2"	14	2	10	100	20
326	12980	2"	14	2	10	100	35
327	12990	2 1/2"	14	1/0	—	50	25
328	13000	3"	14	1/0	—	10	6
329	13010	3 1/2"	14	2/0	—	10	7
330	13020	4"	6	250 MCM	—	10	8

DOWNLOAD SPEC SHEET



E148716

MALLEABLE IRON

321M	13030	1/2"	14	4	50	500	25
322M	13040	3/4"	14	4	50	500	30
323M	13050	1"	14	4	25	250	23
324M	13060	1 1/4"	14	4	20	200	34
325M	13070	1 1/2"	14	2	25	250	53
326M	13080	2"	14	2	25	250	78
327M	13090	2 1/2"	14	1/0	—	10	4
328M	13100	3"	14	1/0	—	10	5
329M	13110	3 1/2"	14	2/0	—	10	15
330M	13120	4"	14	2/0	—	10	20
330AM	13122	5"	6	250 MCM	—	10	25
330BM	13124	6"	6	250 MCM	—	10	35


DOWNLOAD SPEC SHEET



E170258

## INSULATED METALLIC GROUNDING BUSHINGS WITH ALUMINUM LAY-IN LUG

- 105° C. THERMOPLASTIC LINERS
  - FOR COPPER OR ALUMINUM BARE GROUND CONNECTOR
- ZINC DIE CAST**



CAT#	A	B
331	1.25	.50
332	1.50	.50
333	1.75	.56
334	2.12	.62
334A	2.12	.62
335	2.37	.75
335A	2.37	.75
336	2.81	.75
336A	2.81	.75
337	3.62	.93
337A	3.62	.93
338	4.18	.93
338A	4.18	.93
339	4.68	.93
339A	4.68	.93
340	5.25	.93
340A	5.25	.93

331M	1.25	.50
332M	1.48	.54
333M	1.80	.65
334M	2.40	.73
334AM	2.40	.73
335M	2.50	.80
335AM	2.50	.80
336M	3.03	.80
336AM	3.03	.80
337M	3.60	.95
337AM	3.60	.95
338M	4.16	1.03
338AM	4.16	1.03
339M	4.75	1.15
339AM	4.75	1.15
340M	5.30	1.17
340AM	6.15	1.30
340ALM	6.15	1.30
340BLM	7.19	1.30

331MSS	1.25	.50
332MSS	1.48	.54
333MSS	1.80	.65
334MSS	2.40	.73
335MSS	2.50	.80
336MSS	3.03	.80
337MSS	3.60	.95
338MSS	4.16	1.03
339MSS	4.75	1.15
340MSS	5.30	1.17
340AMSS	6.15	1.30
340BMSS	7.19	1.30

### GROUNDING LUG

TOPAZ CAT #	UPC#	SIZE	WIRE SIZE		UNIT CTN	SHIP CASE	WT/ CASE
			MIN	MAX			
331	13130	1/2"	14	4	50	500	30
332	13140	3/4"	14	4	50	500	35
333	13150	1"	14	4	25	250	23
334	13160	1 1/4"	14	4	20	200	26
334A	13170	1 1/4"	14	1/0	20	200	26
335	13180	1 1/2"	14	4	10	100	16
335A	13190	1 1/2"	14	1/0	10	100	16
336	13200	2"	14	4	10	100	21
336A	13210	2"	14	1/0	10	100	21
337	13220	2 1/2"	14	1/0	—	50	20
337A	13230	2 1/2"	6	250 MCM	—	50	20
338	13240	3"	14	1/0	—	50	29
338A	13250	3"	6	250 MCM	—	50	29
339	13260	3 1/2"	14	1/0	—	10	15
339A	13270	3 1/2"	6	250 MCM	—	10	15
340	13280	4"	14	1/0	—	10	20
340A	13290	4"	6	250 MCM	—	10	20

### MALLEABLE IRON

331M	13300	1/2"	14	4	50	500	45
332M	13310	3/4"	14	4	50	500	50
333M	13320	1"	14	4	25	250	40
334M	13330	1 1/4"	14	4	20	200	35
334AM	13340	1 1/4"	14	1/0	20	200	35
335M	13350	1 1/2"	14	4	10	100	25
335AM	13360	1 1/2"	14	1/0	10	100	25
336M	13370	2"	14	4	10	100	30
336AM	13380	2"	14	1/0	10	100	30
337M	13390	2 1/2"	14	1/0	—	50	25
337AM	13400	2 1/2"	6	250 MCM	—	50	25
338M	13410	3"	14	1/0	—	25	18
338AM	13420	3"	6	250 MCM	—	25	18
339M	13430	3 1/2"	14	1/0	—	10	20
339AM	13440	3 1/2"	6	250 MCM	—	10	20
340M	13450	4"	14	1/0	—	10	25
340AM	13460	4"	6	250 MCM	—	10	25
340ALM	13462	5"	6	250 MCM	—	10	25
340BLM	13463	6"	6	250 MCM	—	10	35

### SET SCREW NO THREAD

331MSS	13321	1/2"	14	4	50	500	25
332MSS	13331	3/4"	14	4	50	500	30
333MSS	13341	1"	14	4	25	250	23
334MSS	13351	1 1/4"	14	4	20	200	30
335MSS	13361	1 1/2"	14	4	10	100	25
336MSS	13371	2"	14	4	10	100	30
337MSS	13391	2 1/2"	14	1/0	5	50	38
338MSS	13411	3"	14	1/0	—	25	35
339MSS	13431	3 1/2"	14	1/0	—	10	15
340MSS	13451	4"	14	1/0	—	10	20
340AMSS	13461	5"	6	250MCM	—	10	25
340BMSS	13471	6"	6	250MCM	—	10	35

DOWNLOAD SPEC SHEET



E170258

DOWNLOAD SPEC SHEET



E170258

DOWNLOAD SPEC SHEET



E170258