

Stainless Steel Grounding Bushings

Features:

- Manufactured in type 316 stainless steel to meet any stringent sanitary condition
- Polished with standard "brite" finish to increase corrosion resistance and aesthetic appearance
- Set screw provides fixed alignment and positive ground continuity
- Allows easy insertion of grounding conductor for thru or end connection
- No package qty. required



Certifications and Complies:



UL 467 / CSA C22-41 Listed

Standard for Grounding and Bonding Equipment

UL 514B / CSA C22.2-18.3 Listed

Standard for Conduit, Tubing and Cable Fittings

UL 486A-486B / CSA C22.2-65-13 Listed

Standard for Safety for Wire Connectors

UL File # E352416



Manufactured in the USA

Applications:

For use on stainless steel rigid or threaded IMC conduit, to provide a means of grounding conduit through a bushing.

Industries Commonly Served:

- Food & Beverage Production & Distribution
- Chemical Plants
- Water & Wastewater Treatment
- Pharmaceuticals & Cosmetics
- Refining & Extraction Sites
- Petrochemical Operations
- Marine & Coastal Facilities
- Pulp and Paper Mills
- Along with other corrosive environments



Size	Part Number	A	B	C	D	Grounding Screw	Weight per ea (lbs)
3/4"	S60700GB00	.732"	1.560"	1.313"	.850"	10-24 x 3/4"	.27
1"	S61000GB00	.824"	1.900"	1.313"	.850"	10-24 x 3/4"	.38

All dimensions are for informational purposes only *Tolerances +/- 5%