Claro® & Satin Colors® | accessories & wallplates

For more information
visit www.lutron.com/claro
visit www.lutron.com/satincolors

2.94" (75mm)

4.69" (119mm)

.30" (7.6mm) profile

Shown actual size: Satin Colors® GFCI receptacle with LED status indicator light, and 1-gang wallplate in greenbriar (GB)

claro®

SATIN COLORS

product family features

- full line of wiring devices in designer style opening
- wallplates feature clean appearance with no visible hardware
- coordinating Claro® and Satin Colors® wallplates available separately (including stainless steel) for Lutron® dimmers, switches, and systems

available colors (see pages 12-13 for color swatches)

colors (gloss finish)

WH	white	GR	gray
IV	ivory	BR	brown
AL	almond	BL	black
LA	light almond		

colors (metal finish)

| SS | stainless steel (wallplates only) |

colors (satin finish)

HT	hot	ES	eggshell
MR	merlot	BI	biscuit
PL	plum	GS	goldstone
TQ	turquoise	DS	desert stone
TC	terracotta	ST	stone
GB	greenbriar	LS	limestone
BG	bluestone	SW	snow
MS	mocha stone	PD	palladium
SG	sea glass	MN	midnight
TP	taupe	SI	sienna

colors & finishes key

	available in gloss finish
	available in satin finish
	available in all gloss and satin finishes

Multiple devices with line and low-voltage can be mounted behind a common wallplate using a standard barrier backbox (see Application Note #213) at www.lutron.com/applicationnotes

CAD file downloads available at www.lutron.com/cad

Questions on installation or selection?
Call Lutron® 24 hours/7 days a week at
1.800.523.9466 or visit www.lutron.com

Claro® & Satin Colors® | accessories & wallplates

For more information
visit www.lutron.com/claro
visit www.lutron.com/satincolors

switches

- paddle turns on/off
- use with any 15A load
- general purpose switching of all sources and motor loads
- no derating if ganged

general purpose switches (120/277 V)

single pole	15A	**CA-1PSH-**
		SC-1PS-
3-way	15A	**CA-3PSH-**
		SC-3PS-
4-way	15A	**CA-4PSH-**
		SC-4PS-

general purpose switch with locator light
(120 V only)

single pole	15A	**CA-1PSNL-**
		SC-1PSNL-
3-way	15A	**CA-3PSNL-**
		SC-3PSNL-
4-way	15A	**CA-4PSNL-**
		SC-4PSNL-

colors & finishes key

- available in gloss finish
- available in satin finish
- available in all gloss and satin finishes

See page 85 for available colors.
To order, add color suffix to model number.
Example: **CA-1PSH- WH**

telephone and cable jacks

- 6-conductor telephone jack, RJ11
- F-style, 75-Ohm coaxial cable

single telephone jacks	**CA-PJH-**
	SC-PJ-
single cable jacks	**CA-CJH-**
	SC-CJ-

receptacles and GFCI receptacles

- press test button to confirm LED indicator status
- press reset button to reset GFCI after circuit interruption

receptacles

15A, 125V		**CAR-15H-**
		SCR-15-
20A, 125V		**SCR-20-**

tamper resistant receptacles

15A, 125V		**CARS-15-TR-**
		SCRS-15-TR-
20A, 125V		**SCRS-20-TR-**

tamper resistant GFCI receptacles

15A, 125V		**CAR-15-GFTR-**
	GFCI	**SCR-15-GFTR-**
20A, 125V	GFCI	**SCR-20-GFTR-**

Claro® **& Satin Colors**® │ accessories & wallplates

For more information
visit www.lutron.com/claro
visit www.lutron.com/satincolors

receptacles for dimming use

- duplex for dimming both connected loads
- projecting nubs prevent standard plugs from being used
- requires replacement plugs for dimming use

duplex for dimming use

15 A	120/127 V	**CAR-15-DFDU-**
15 A	120/127 V	**SCR-15-DFDU-**
20 A	120/127 V	**CAR-20-DFDU-**
20 A	120/127 V	**SCR-20-DFDU-**

receptacle for dimming use

- top half for dimming
- projecting nub prevents standard plug from being used
- requires replacement plugs for dimming use
- bottom half is a general use receptacle and will fit standard duplex plugs

split duplex (half for dimming use)

15 A	120/127 V	**CAR-15-HFDU-**
15 A	120/127 V	**SCR-15-HFDU-**
20 A	120/127 V	**CAR-20-HFDU-**
20 A	120/127 V	**SCR-20-HFDU-**

replacement plug for dimming
(use with receptacles above)

- this plug required for use with Lutron® receptacles for dimming use—plug will work in standard receptacle
- easily replaces the existing plugs on lamps

120/127 V	white	**RP-FDU-10-WH**
120/127 V	brown	**RP-FDU-10-BR**

UL/CSA/NOM regulatory approvals

IMPORTANT NOTES

- If the hot and dimmed hot feeds to the split duplex HFDU are supplied from different circuits or split-wired, with separate switch-legs, a means to simultaneously disconnect these circuits must be provided at the panel board where they originate (NEC 210.7(C) 2002 Edition). A 2-pole circuit breaker or two single-pole circuit breakers with an approved handle tie can be used to accomplish this simultaneous disconnect. Feed-through dimming panels, which are those without breakers, are recommended when using the HFDU.

- Receptacles and plug for dimming use are UL listed for use with all Lutron® wallbox dimmers included in this catalog.

- If there is only one electrical feed to the receptacle, then the duplex DFDU must be used.

- For detailed information, see Application Notes #91 (Guide to Dimming Table Lamps) and #109 (Guide to Dimming Portable Lamps via Receptacles) at www.lutron.com/applicationnotes

See page 85 for available colors.
To order, add color suffix to model number.
Example: **CAR-15-GFCIH- WH**

Claro® & Satin Colors® | accessories & wallplates

For more information
visit www.lutron.com/claro
visit www.lutron.com/satincolors

field customizable multi-port frames

- shipped with 6 blanks
- connectors sold separately (shown below)
- connectors snap in (no tools required)
- available in gloss and satin colors – connectors available in white and black only unless noted

| 6-port frames | **CA-6PF-** |
| | **SC-6PF-** |

connectors

telephone jacks

	8-conductor, RJ45 category 3	**CON-1P-C3-**	*
	8-conductor, RJ45 category 5e	**CON-1P-C5E-**	*
	8-conductor, RJ45 category 6	**CON-1P-C6-**	*

fiber jacks

	MT-RJ feed through	**CON-1F-MTRJ-WH**
	SC simplex	**CON-1F-SC-WH**
	LC non-flush	**CON-1F-LC-WH**
	ST style	**CON-1F-ST-WH**

cable jack

| | F-style, 75-Ohm coaxial cable | **CON-1C-** | * |

BNC jack

| | BNC connector, 50-Ohm | **CON-1B-WH** |

Multiple devices with line and low-voltage can be mounted behind a common wallplate using a standard barrier backbox (see Application Note #213) at www.lutron.com/applicationnotes

* only available in white and black

also compatible with Hubbell® jacks.
See www.hubbell.com Colors not Lutron® standard.

wallplates for Maestro®, Spacer System®, Diva®, Lyneo® Lx, Skylark®, Osprey®, and RadioRA®

1-gang**	**CW-1-**
	SC-1-
W: 2.94" (75mm); H: 4.69" (119mm); D: .30" (7.6mm)	
2-gang**	**CW-2-**
	SC-2-
W: 4.75" (121mm); H: 4.69" (119mm); D: .30" (7.6mm)	
3-gang**	**CW-3-**
	SC-3-
W: 6.56" (167mm); H: 4.69" (119mm); D: .30" (7.6mm)	
4-gang**	**CW-4-**
	SC-4-
W: 8.37" (213mm); H: 4.69" (119mm); D: .30" (7.6mm)	
5-gang**	**CW-5-**
	SC-5-
W: 10.18" (259mm); H: 4.69" (119mm); D: .30" (7.6mm)	
6-gang**	**CW-6-**
	SC-6-
W: 12.00" (305mm); H: 4.69" (119mm); D: .30" (7.6mm)	

contractor packs

1-gang (qty. 96)	**CW-1-** **-96**
2-gang (qty. 48)	**CW-1-** **-48**
3-gang (qty. 24)	**CW-1-** **-24**
4-gang (qty. 12)	**CW-1-** **-12**

** order stainless steel using CW- model numbers

Custom wallplate configurations, colors, and engraving are available from Lutron®. For additional information and for help ordering contact customer service at 1.888.LUTRON1.

All Lutron® wallplates are screwless, seamless, and have no visible hardware. There are two parts:
1) alignment adapter plate
2) front plate – securely snaps onto alignment adapter plate

Controls must have heat-sink fins broken for multi-gang installations. Please derate dimmers and switches (page 182) as required.

See page 85 for available colors.
To order, add color suffix to model number.
Example: **SC-6PF-** **HT**