

Multiple Tap Connector Dual Rated

 RoHS
Compliant

 UL
LISTED
453G

 CSA
LR-29601

TYPE PTA

Features

- Manufactured from high strength 6061-T6 aluminum alloy
- Electro-tin plated
- UL Listed and CSA Certified for 600 volts, 90° C
- Compact design
- Range taking
- Re-usable
- Lay-in main conductors
- Supplied with insulating cover

Benefits

- Suitable for use with either copper or aluminum conductors
- Provides low contact resistance
- Ensures reliability for copper or aluminum conductors
- Saves space and reduces installation time
- Permits inventories to be kept to a minimum
- Provides efficient use and flexibility in the field
- No need to break the feeder cables
- Eliminates taping



Fig. 1



Fig. 2



Fig. 3

Catalog Number Connector	Figure Number	Main Wire Range	Bottom Tap Range	Dimensions			Hex Size	
				H	W	D	Main	Tap
PTA2-500-500-W/C	1	Two: 500kcmil-250kcmil	Two: 500kcmil-4	3-15/16	3-1/2	1-1/4	3/8	3/8
PTA2-750-500-W/C	1	Two: 750kcmil-350kcmil	Two: 500kcmil-4	3-5/8	4-3/32	1-5/16	3/8	3/8
PTA4-750-500-W/C	2	Four: 750kcmil-350kcmil	Two: 500kcmil-4	5-7/8	4-3/32	1-5/16	3/8	3/8
PTA26-500-4/0*+	3	Two: 500kcmil-4/0	Four: 4/0-6 Two: 2-14	3-15/16	3-1/2	1-1/4	3/8	5/16 Slotted

All wire sizes, unless noted otherwise, are American Wire Gauge (AWG)

Note: W/C indicates product is supplied with insulating cover.

* Not CSA Certified.

+ Cover must be ordered separately. For non UL cover, order 1 each RO614W00A and RO615W00A.

DE-OX Inhibitor is recommended for all aluminum terminations.

Tested to UL 486A/B, UL File E6207

Multiple Tap Connector Dual Rated

TYPE PTA

Features

- Manufactured from high strength 6061-T6 aluminum alloy
- Electro-tin plated
- UL Listed and CSA Certified for 600 volts, 90° C
- Compact design
- Range taking
- Re-usable
- Lay-in main conductors
- Supplied with insulating cover

Benefits

- Suitable for use with either copper or aluminum conductors
- Provides low contact resistance
- Ensures reliability for copper or aluminum conductors
- Saves space and reduces installation time
- Permits inventories to be kept to a minimum
- Provides efficient use and flexibility in the field
- No need to break the feeder cables
- Eliminates taping



Fig. 1



Fig. 2



Fig. 3



Catalog Number Connector	Figure Number	Main Wire Range	Bottom Tap Wire Range	Dimensions			Hex Size	
				H	W	D	Main	Tap
PTA2-500-500-W/C	1	Two: 500kcmil-250kcmil	Two: 500kcmil-4	3-15/16	3-1/2	1-1/4	3/8	3/8
PTA2-750-500-W/C	1	Two: 750kcmil-350kcmil	Two: 500kcmil-4	3-5/8	4-3/32	1-5/16	3/8	3/8
PTA4-750-500-W/C	2	Four: 750kcmil-350kcmil	Two: 500kcmil-4	5-7/8	4-3/32	1-5/16	3/8	3/8
PTA26-500-4/0*+	3	Two: 500kcmil-4/0	Four: 4/0-6 Two: 2-14	3-15/16	3-1/2	1-1/4	3/8	5/16 Slotted

All wire sizes, unless noted otherwise, are American Wire Gauge (AWG)

Note: W/C indicates product is supplied with insulating cover.

* Not CSA Certified.

+ Cover must be ordered separately. For non UL cover, order 1 each RO614W00A and RO615W00A.

DE-OX Inhibitor is recommended for all aluminum terminations.

Tested to UL 486A/B, UL File E6207