

# illuminate



The bright white radiance of GE's LED A-Line lamps is not just something you see, it's something you feel.

## LED A-Line general purpose lamps

GE offers dimmable LED A-Line lamps as excellent replacements for standard 25-watt, 40-watt, 60-watt, 75-watt and 100-watt incandescent lamps.

### LOW-COST OPERATION

- For example, a 100-watt incandescent replacement lamp using 13 watts of energy and producing 800 lumens can save over \$129 in energy costs over the rated life of the lamp versus a standard 840 lumen, 60-watt incandescent A19 based on \$0.11 per kWh
- Energy efficiency and long life mean fewer lamp replacements versus standard incandescent or halogen light sources

### EXCELLENT COLOR RENDERING

- Available with a CRI of 78 - 84

### COLOR TEMPERATURE

- Halogen-like color
- Available in 2400K, 2700K, 3000K and 5000K

### LONG LIFE

- Up to 25,000 hours rated life (L70)

### DIMMABLE

- Dims from 100% to as low as 10%

### ENVIRONMENTALLY CONSCIOUS

- These lamps are energy efficient, contain no lead or mercury, and are compliant with material restriction requirements of RoHS

### GE QUALITY AND RELIABILITY

- 3-year limited warranty

To learn more about saving money and energy,  
go to: [gelighting.com/ThinkLED](http://gelighting.com/ThinkLED)

When you Think LED lighting, Think GE.

ecomagination<sup>SM</sup>









imagination at work

Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

## LED A-Line general purpose lamps

### A-Line Lamps

Bulb Shape	Base Type	Watts	Grainger Item Number	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information	
A-15																			
	MED	4.5	22MX10	68173	LED4DA15-W/TP	120	3	3.5	270		2700	82	25W	15,000	Yes		Damp	White	
			22MX11	68174	LED4DA15-C/TP	120	3	3.5	270		2700	82	25W	15,000	Yes		Damp	Clear	
			36GJ36	14644	LED4.5DA15-C/827	120	6	3.5	300		2700	80	40W	15,000	Yes		Damp	Clear	
				23708	LED4.5DA15-W5KTP	120	3	3.5	350		5000	80	40W	15,000	Yes		Damp	White	
				23724	LED4.5DA15-C5KTP	120	3	3.5	350		5000	80	40W	15,000	Yes		Damp	Clear	
				83645	LED4.5DA15C-FRIG	120	3	3.5	350		5000	80	40W	15,000	Yes		Damp	Clear Refrigerator bulb	
A-19																			
	MED	7	40D437	14063	LED7DAV3/827W	120	6	4.6	470		2700	80	40W	25,000	Yes		Damp	White, Semi-Omni	
			36GJ38	95928	LED7DAV3/5K	120	6	4.6	500		5000	80	40W	25,000	Yes		Damp	White, Semi-Omni	
			36GJ37	11332	LED7DA19/827	120	6	4.4	450		2700	80	40W	25,000	Yes	★	Damp	White, Omnidirectional	
			44ZV38	71208	LED7DA19/830	120	6	4.4	450		3000	80	40W	25,000	Yes	★	Damp	White, Omnidirectional	
				34238	LED7DA19/824	120	6	4.44	450		2400	80	40W	25000	Yes		Damp	White	
				92140	LED7A19BUG	120	3	4.63	400				40W	15,000	-		Damp	Bug Light	
	10.5		13791	LED11DAV3/827W	120	6	4.6	800		2700	80	60W	15,000	Yes		Damp	White, Semi-Omni		
		44ZV39	95927	LED11DAV3/5K	120	6	4.4	850		5000	80	60W	15,000	Yes		Damp	White, Semi-Omni		
		11	32WX16	11328	LED11DA19/827	120	6	4.4	800		2700	80	60W	25,000	Yes	★	Damp	White, Omnidirectional	
			44ZV42	71209	LED11DA19/830	120	6	4.4	800		3000	80	60W	25,000	Yes	★	Damp	White, Omnidirectional	
			29268	LED11DA19/824	120	6	4.44	800		2400	80	60W	25,000	-		Damp	White, Omnidirectional		
		GU24	74357	LED11DA19827GU24	120	6	5.43	800		2700	80	60W	25,000	-	★	Damp	White, Omnidirectional		
A-Line reveal®																			
	MED	7		63178	LED7DA19RVLESTP	120	3	4.43	450		2700	84	40w	25,000	Yes		Damp	White, Omnidirectional	
			11	63180	LED11DA19RVLESTP	120	3	4.43	800		2700	84	60w	25,000	Yes		Damp	White, Omnidirectional	
			14	92284	LED14DA21RVL/TP	120	3	5.28	1100		2700	85	75w	25,000	Yes		Damp	White, Omnidirectional	
A-21																			
	MED	12	44ZV41	73384	LED12A21/830FE	120	6	5.31	1100		3000	80	100W	25,000	Yes		Damp	White, Enclosed, Omni	
			44ZV45	73404	LED12DA21/850FE	120	6	5.31	1100		5000	80	100W	25,000	Yes		Damp	White, Enclosed, Omni	
			13	45KH99	12422	LED13DA212/827	120	6	5.28	1100		2700	80	75W	25,000	Yes	★	Damp	White, Omnidirectional
			14	32WX12	94936	LED14DA21/827W	120	6	5.3	1100		2700	80	75W	15,000	Yes		Damp	White, Semi-Omni
			16	45KH97	12349	LED16DA212/827	120	6	5.28	1600		2700	80	100W	25,000	Yes	★	Damp	White, Omnidirectional
				45KH98	12399	LED16DA212/830	120	6	5.3	1600		3000	80	100W	25,000	Yes	★	Damp	White, Omnidirectional
	GU24		92498	LED16DA21827GU24	120	6	5.43	1600		2700	80	100W	25,000	Yes	★	Damp	White		
		MED	16	44ZV36	73376	LED16A30/100/827	120	6	5.31	400/1600/1050		2700	80	30/70/100	25,000	-	★	Damp	3-Way
					92118	LED16A30/100/5KB	120	3	5.31	400/1600/1050		5000	80	30/70/100	25,000	-			White, 3-Way
				17	44ZV40	16113	LED17DA21/827	120	6	5.3	1600		2700	78	100W	15,000	Yes		Damp
		22	44ZV43	73378		LED22A50/150/827	150	6	5.31	700/2155/1600		2700	80	50/100/150	25,000	-		Damp	3-Way
					92120		LED22A50/150/5KB	120	3	5.31	700/2155/1600		5000	80	50/100/150	25,000	-		

Get more information at  
**GELighting.com/ThinkLED**

Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

\* The life rating is based on the hours of operation the lamp will provide before reaching 70% of its original rating (L70)

\*\* Minimum order quantity = 6

★ ENERGY STAR® status: ENERGY STAR® certified. Lamps without a "★" are not ENERGY STAR® certified.

# UL 1993 Environmental Requirements for LED LAMPS

Location, damp - Exterior or interior location that is normally or periodically subject to condensation of moisture in, on, or adjacent to, electrical equipment, and includes partially protected locations.

Location, dry - Location not normally subject to dampness, may include a location subject to temporary dampness, i.e., building under construction, provided ventilation is adequate to prevent an accumulation of moisture.

Location, wet - Location in which water or other liquid can drip, splash, or flow on or against electrical equipment.

Notes: 1) Product descriptions ending in "TP" indicate a carded blister or clamshell package nested in a tray for shelf display. Cards also designed for hook display.  
2) LED A19 Locking device works on PC: 85791, 85792, 89898, 62182, 89899 and 89900



Product is compliant with material restriction requirements of RoHS

ENERGY STAR® is a registered U.S. mark



[www.gelighting.com](http://www.gelighting.com)

GE and the GE Monogram are trademarks of the General Electric Company. All other trademarks are the property of their respective owners. Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions. GE Lighting and GE Lighting Solutions, LLC are businesses of the General Electric Company. © 2015 GE.

63563-G (Rev 12/07/15)

Distributor:

AVAILABLE THROUGH

**GRAINGER**  
FOR THE ONES WHO GET IT DONE