


INDUSTRIAL SPEC GRADE TURNLOK® LOCKING DEVICES


L630C & L630P Connector & Plug

- A. Raised ribs** provide non-slip gripping profile for turning to lock and unlock.
- B. Quick-thread assembly screws** and cord-grip screws come backed-out, ready-to-wire.
- C. Industrial-strength, brass alloy plug blades**, and connector contacts resist heat rise, provide excellent conductivity.
- D. Rounded back contour** reduces snags and hang-ups on the job site.
- E. Impact- and corrosion-resistant** durable nylon 6 shell material.
- F. Integral flexible rubber cord grommet** conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.
- G. New-design external cord grips** provide visible assurance of safe and proper cord retention.
- H. Scallop shell design** provides non-slip gripping surface for insertion and withdrawal.
- I. Double dovetail design** provides superior protection against cord pull-out forces.
- J. Visible stamped NEMA configuration and device rating.**



L630R Receptacles

- A. Compact, impact-resistant nylon face and body** are ultrasonically welded together for unrivaled strength.
- B. Clearly marked NEMA configuration, rating, and third party listing** on each unit's face.
- C. One-piece, high-grade brass contacts** offer excellent conductivity and heat-rise resistance.
- D. Single-piece, solid brass mounting strap** is free of easily loosened rivets found on other brands.
- E. Side and external screw-pressure-plate back wire capability.** Accepts #14 - #10 AWG.



F. P&S Turnlok Receptacles. Voltage color coding on the outside. Proven designs and quality materials on the inside. Any way you look at them, they're the standard of the industry.



125V



250V



277VAC



480VAC



600VAC



125/250V

INDUSTRIAL SPEC GRADE TURNLOK® LOCKING DEVICES

NEMA Configurations

Locking Plugs & Receptacles

		15 AMPERE		20 AMPERE		30 AMPERE	
		RECEPTACLE	PLUG	RECEPTACLE	PLUG	RECEPTACLE	PLUG
2 POLE, 2 WIRE NON-GROUNDING							
125V	L1	L1-15R	L1-15P				
	L2			L2-20P	L2-20P		
250V							
2 POLE, 3 WIRE GROUNDING							
125V	L5	L5-15R	L5-15P	L5-20R	L5-20P	L5-30R	5-30P
250V	L6	L6-15R	L6-15P	L6-20R	L6-20P	L6-30R	6-30P
277VAC	L7	L7-15R	L7-15P	L7-20R	L7-20P	L7-30R	7-30P
347VAC	L24			L24-20R	L24-20P		
480VAC	L8			L8-20R	L8-20P	L8-30R	L8-30P
600VAC	L9			L9-20R	L9-20P	L9-30R	L9-30P
3 POLE, 3 WIRE NON-GROUNDING							
125/250V	L10			L10-20R	L10-20P	L10-30R	L10-30P
3Ø250V	L11			L11-20R	L11-20P	L11-30R	L11-30P
3Ø480V	L12			L12-20R	L12-20P	L12-30R	L12-30P
3Ø600V	L13					L13-30R	L13-30P
3 POLE, 4 WIRE GROUNDING							
125/250V	L14			L14-20R	L14-20P	L14-30R	L14-30P
3Ø250V	L15			L15-20R	L15-20P	L15-30R	L15-30P
3Ø480V	L16			L16-20R	L16-20P	L16-30R	L16-30P
3Ø600V	L17					L17-30R	L17-30P
4 POLE, 4 WIRE NON-GROUNDING							
3ØY 120/208V	L18			L18-20R	L18-20P	L18-30R	L18-30P
3ØY 277/480V	L19			L19-20R	L19-20P	L19-30R	L19-30P
3ØY 347/600V	L20			L20-20R	L20-20P	L20-30R	L20-30P
4 POLE, 5 WIRE GROUNDING							
3ØY 120/208V	L21			L21-20R	L21-20P	L21-30R	L21-30P
3ØY 277/480V	L22			L22-20R	L22-20P	L22-30R	L22-30P
3ØY 347/600V	L23			L23-20R	L23-20P	L23-30R	L23-30P

Midget – Locking


		15 AMPERE	
		RECEPTACLE	PLUG
2 POLE, 2 WIRE NON-GROUNDING			
125V	ML1	ML-1R	ML-1P
2 POLE, 3 WIRE GROUNDING			
125V	ML2	ML-2R	ML-2P
3 POLE, 3 WIRE NON-GROUNDING			
125/250V	ML3	ML-3R	ML-3P

Labels & Their Meaning

X, Y, Z	Hot Lead
W	Neutral Lead
G	Grounding Lead

Open Slots

Indicate receptacle configurations (female).




Closed Slots

Indicate plug blade configurations (male).




INDUSTRIAL SPEC GRADE TURNLOK® LOCKING DEVICES


Non-NEMA 3 Wire Grounding & Non-Grounding 10 & 15A, 125 & 250V; 20 & 30A, 125/250 & 250V




7582




7580G



7555SS




7554SS



7556SS

CATALOG NUMBER	RATING		DESCRIPTION/COLOR	CORD DIAMETER	3rd PARTY COMPLIANCE			
	A.	V.			 UL498	FSUL WC596	 CSA	
RECEPTACLES								
7582*	15 10	125 250	Single Receptacle					
7580	15 10	125 250	Duplex Receptacle					
7580G	15 10	125 250	Duplex Receptacle, Grounding					
7310*	20	125/250	Single Receptacle					
3330	30	125/250	Single Receptacle					
3330G	30	125/250	Single Receptacle, Grounding					
CONNECTORS IP20 SUITABILITY								
7555SS*	15 10	125 250	Yellow	.296"-.625"				
7555G	15	125	Yellow	.280"-.710"				
7313SS	20	125/250	Black Back, White Front Body	.225"-.750"				
7313SSBK	20	125/250	Black Back, Black Front Body	.225"-.750"				
3333SS	30	125/250	Black Back, White Front Body	.225"-.750"				
PLUGS IP20 SUITABILITY								
S2348DF	14	125-480	Black Back, White Front Body					
7554SS*	15 10	125 250	Yellow					.296"-.625"
7572G	15	125	Yellow, Grounding					.280"-.710"
7311SS	20	125/250	Black Back, White Front Body					.225"-.750"
7311SSBK	20	125/250	Black Back, Black Front Body					.225"-.750"
7311G	20	250	Yellow, Grounding					.410"-1.060"
3331SS	30	125/250	Black Back, White Front Body					.225"-.750"
3331G	30	250	Yellow, Grounding					.410"-1.060"
FLANGED INLETS & OUTLETS								
S2347	14	125-480	Outlet					
7556SS*	15 10	125 250	Gray Inlet					
7557SS*	15 10	125 250	Gray Outletw					
3334SS	30	125/250	Gray Inlet					
3335SS	30	125/250	Gray Outlet					



7557SS



Non-NEMA
7580, 7580G
7582, 7555SS
7557SS



Non-NEMA
7554SS
7556SS
7572G



Non-NEMA
S2348DF



Non-NEMA
S2347



Non-NEMA
7310
7313SS



Non-NEMA
7311SS
7311G



Non-NEMA
3331SS
3334SS
3331G



Non-NEMA
3330, 3330G
3333SS
3335SS

*For replacement use only.
Reference Pages G-38 and G-39 for Accessories.

All devices listed on this page conform to NEMA WD-1 and WD-6.