



***2016 COMMERCIAL PRODUCT  
REFERENCE GUIDE***



LIGHTING SCIENCE

**LSPRO** COMMERCIAL LAMP SERIES

The efficient and reliable products in our new LSPRO™ commercial line were engineered to take commercial LED to the next level by exceeding standard commercial specifications. Take a look and you will see products with high CRI, increased lumen output and Energy Star ratings. These products adhere to our highest design and testing requirements and are poised to become the new standard that designers and commercial consumers will demand.



**A19 40WE / 60WE \***  
CCT: 2700K, 3000K, 5000K  
(LS 4-Packs Only)



**A19 75WE**  
CCT: 3000K  
COMING SOON!



**A21 100WE**  
CCT: 3000K  
COMING SOON!



**A21 3-WAY 60WE / 75WE / 100WE**  
CCT: 3000K  
COMING SOON!



**DURABULB™ \***  
An Amazing Shatter-Resistant Lamp!  
COMING SOON!



**GP19 40WE / 60WE \***  
CCT: 2700K, 5000K  
(LS 4-Packs Only)



**G25 40WE / 60WE \***  
CCT: 2700K AVAILABLE IN FROSTED AND CLEAR  
COMING SOON!



**R20 50WE \***  
CCT: 2700K, 3000K, 4000K, 5000K  
CRI: ≥ 90 BEAM ANGLE: 120°



**BR30 65WE / 75WE \***  
CCT: 2700K, 3000K, 4000K, 5000K  
CRI: ≥ 90 BEAM ANGLE: 120°



**BR40 75WE / 90WE \***  
CCT: 2700K, 3000K, 4000K, 5000K  
CRI: ≥ 90 BEAM ANGLE: 120°



**MR16 35WE / 50WE \***  
CCT: 2700K, 3000K, 4000K, 5000K  
CRI: ≥ 90 BEAM ANGLES: 25° / 40°



**MR16 GU10 35WE / 50WE \***  
CCT: 2700K, 3000K, 4000K, 5000K  
CRI: ≥ 90 BEAM ANGLES: 25° / 40°



**PAR16 35WE \***  
CCT: 2700K, 3000K, 4000K, 5000K  
CRI: ≥ 90 BEAM ANGLES: 25° / 40°



**PAR20 50WE \***  
CCT: 2700K, 3000K, 4000K, 5000K  
CRI: ≥ 90 BEAM ANGLES: 25° / 40°



**PAR30 75WE \***  
CCT: 2700K, 3000K, 4000K, 5000K  
CRI: ≥ 90 BEAM ANGLES: 25° / 40°



**PAR 38 90WE / 120WE \***  
CCT: 2700K, 3000K, 4000K, 5000K  
CRI: ≥ 90 BEAM ANGLES: 25° / 40°



\* Versions of this product may be Energy Star Certified, DLC Certified or in-progress for other certifications. Call us for more details. For Energy Star specific questions, you can also visit <http://www.energystar.gov/products/certified-products>

## LSPRO™ T8 LINEAR SERIES

Sleek, modern LED linear lighting. Retrofit your old fluorescent linear lighting with our new LSPRO™ energy-efficient T8 Linears. Designed with the commercial lighting marketplace in mind, these linears combine high-quality dimmer, ballast and fixture compatibility and cool, uninterrupted lines to give you a new standard in LED. No matter the project, we have the LED linear solution for you.

### DIRECT-FIT



**2' T8 Direct-Fit\***  
CCT: 3000K, 40000K, 5000K  
CRI: ≥ 80 BEAM ANGLE: 270°  
CALL FOR ORDERING DETAILS



**3' T8 Direct-Fit\***  
CCT: 3000K, 40000K, 5000K  
CRI: ≥ 80 BEAM ANGLE: 270°  
CALL FOR ORDERING DETAILS



**4' T8 Direct-Fit\***  
CCT: 3000K, 40000K, 5000K  
CRI: ≥ 80 BEAM ANGLE: 270°



### DIRECT-WIRE



**2' T8 Direct-Wire\***  
CCT: 3000K, 40000K, 5000K  
CRI: ≥ 80 BEAM ANGLE: 270°  
CALL FOR ORDERING DETAILS



**3' T8 Direct-Wire\***  
CCT: 3000K, 40000K, 5000K  
CRI: ≥ 80 BEAM ANGLE: 270°  
CALL FOR ORDERING DETAILS



**4' T8 Direct-Wire\***  
CCT: 3000K, 40000K, 5000K  
CRI: ≥ 80 BEAM ANGLE: 270°



## SERIES-A+™: EXPERIENCE PERFECT LIGHT

Our patented, ultimate combination of best-in-class components: high CRI of ≥ 97, premium optics, drivers and state of the art LEDs. Crafted to achieve exceptional color rendering, smooth dimming to 5%, and beam shaping for clean lines. You have to experience this light to actually believe it is possible!

COMING SOON!



**MR16 35WE / 50WE\***  
CCT: 3000K, 40000K, 5000K  
CRI: ≥ 97 BEAM ANGLES: 10° / 25° / 40°

COMING SOON!



**PAR20 50WE\***  
CCT: 3000K, 40000K, 5000K  
CRI: ≥ 97 BEAM ANGLES: 10° / 25° / 40°

COMING SOON!



**PAR30 75WE\***  
CCT: 3000K, 40000K, 5000K  
CRI: ≥ 97 BEAM ANGLES: 10° / 25° / 40°

COMING SOON!



**PAR 30 GIMBAL 75WE\***  
CCT: 3000K, 40000K, 5000K  
CRI: ≥ 97 BEAM ANGLES: 10° / 25° / 40°



\* Versions of this product may be Energy Star Certified, DLC Certified or in-progress for other certifications. Call us for more details. For Energy Star specific questions, you can also visit <http://www.energystar.gov/products/certified-products>

## GLIMPSE™ LED DOWNLIGHTS

Invented by Lighting Science's engineering team, the patented GLIMPSE™ is designed to convert most 4", 5" or 6" recessed cans into a high performance LED luminaire almost as simply as installing a new bulb. Lighting Science's integration of leading optical, thermal and driver design excellence are fully on display with Glimpse™ – a luminaire to which there truly is no equal. Using just a fraction of the material of other LED downlight modules, Glimpse™ is light in material, but never light on performance. LED down lighting has never been so easy.



**4" GLIMPSE® 50WE \***  
2700K, 3000K, 4000K



**6" GLIMPSE® 75WE \***  
2700K, 3000K, 4000K



COMING SOON!



**4" GLIMPSE® ADVANTAGE \***

COMING SOON!



**6" GLIMPSE® ADVANTAGE \***

## LS PRO COMMERCIAL TROFFERS

Crisp, clean light that's easy on the eye. Commercial troffer lighting has never been this easy and energy efficient with sleek troffers that can be easily retrofit into most any fixture.



**Troffer**  
2' x 2'  
CALL FOR ORDERING DETAILS



**Troffer**  
2' x 4'  
CALL FOR ORDERING DETAILS



\* Versions of this product may be Energy Star Certified, DLC Certified or in-progress for other certifications. Call us for more details. For Energy Star specific questions, you can also visit <http://www.energystar.gov/products/certified-products>

## THE HEALTHE™ SERIES: HUMAN HEALTH LIGHTING

Boost your energy and productivity, or wind down to a healthy, restorative sleep all through the science and technology of light. Rooted in science and designed in collaboration with NASA to help Astronauts sleep better and be more alert while stationed aboard the International Space Station, the HEALTHE™ Series of LEDs utilize specific light wavelengths to optimize your daytime performance and enhance your body's natural release of melatonin production to encourage restorative sleep. We put the power in your hands.

COMING SOON!



**GOODDAY™ A19**  
CCT: PROPRIETARY GOODDAY™



**GOODDAY™ BR30**  
CCT: PROPRIETARY GOODDAY™



**GOODDAY™ BR40**  
CCT: PROPRIETARY GOODDAY™



**GENESIS DynaSpectrum™**  
CCT: PROPRIETARY GOODDAY™/ GOODNIGHT™  
+ MORE



**GOODNIGHT™ A19**  
CCT: PROPRIETARY GOODNIGHT™



**SLEEPY BABY™ P15**  
CCT: PROPRIETARY SLEEPY BABY™

COMING SOON!



**6" GOODDAY™ GLIMPSE™\***  
CCT: PROPRIETARY GOODDAY™



**MYNATURE COASTAL™ PAR30-SN**  
CCT: PROPRIETARY MYCOASTAL™

COMING SOON!



**GOODDAY™ T8 Direct Fit**  
CCT: PROPRIETARY GOODDAY™

COMING SOON!



**GOODDAY™ T8 Direct-Wire**  
CCT: PROPRIETARY GOODDAY™

COMING SOON!



**GOODDAY™ Troffer**  
AVAILABLE SIZES: 2' x 2' OR 2' x 4'  
CCT: PROPRIETARY GOODDAY™

COMING SOON!



**GOODDAY™/GOODNIGHT™**  
AVAILABLE SIZES: 2' x 2' OR 2' x 4'  
CCT: PROPRIETARY GOODDAY™/ GOODNIGHT™

COMING SOON!



**GOODNIGHT™ Troffer**  
AVAILABLE SIZES: 2' x 2' OR 2' x 4'  
CCT: PROPRIETARY GOODNIGHT™

COMING SOON!



**GENESIS DynaSpectrum™ Downlight**  
CCT: ADJUSTABLE, PROPRIETARY GOODDAY™/ GOODNIGHT™



\* Versions of this product may be Energy Star Certified, DLC Certified or in-progress for other certifications. Call us for more details. For Energy Star specific questions, you can also visit <http://www.energystar.gov/products/certified-products>

## THE MARQUEE™ SERIES FILAMENT LED

Inspired by the past, but designed for the future. Lighting Science's Marquee™ filament LED series recreates the nostalgic look of an incandescent lamp - sleek, simple and room-enhancing, yet lasting up to 7x longer than a traditional incandescent. These lamps are the perfect choice to give you the look and feel you have grown to love in soft, inviting, decorative indoor lighting.



**A19** 40WE / 60WE \*  
CCT: 2700K

*THE ROXY*



**A19** 40WE / 60WE\*  
CCT: 2200K

*THE ROXY*



**B11** 25WE / 40WE \*  
CCT: 2700K  
BASES AVAILABLE: E26, E12

*THE MAJESTIC*



**B11** 25WE / 40WE \*  
CCT: 2200K

BASES AVAILABLE: E26, E12  
*THE MAJESTIC*



**G25** 40WE / 60WE \*  
CCT: 2700K

*THE GLOBE*



**G25** 40WE / 60WE \*  
CCT: 2200K

*THE GLOBE*



**G40** 40WE / 75WE \*  
CCT: 2700K

*THE GLOBE*



**G40** 40WE / 75WE \*  
CCT: 2200K

*THE GLOBE*

*COMING SOON!*



**ST19** 40WE / 60WE \*  
CCT: 2700K

*THE AVON*

*COMING SOON!*



**ST19** 40WE / 60WE \*  
CCT: 2200K

*THE AVON*

*COMING SOON!*



**BT15** 40WE / 60WE \*  
CCT: 2700K

*THE GOODMAN*

*COMING SOON!*



**BT15** 40WE / 60WE \*  
CCT: 2200K

*THE GOODMAN*

*MIRROR SERIES*



**A19 MIRROR** 40WE / 60WE \*  
CCT: 2700K



**G25 MIRROR** 40WE / 75WE \*  
CCT: 2700K



**G30 MIRROR** 40WE / 75WE \*  
CCT: 2700K



**G40 MIRROR** 40WE / 75WE \*  
CCT: 2700K




\* Versions of this product may be Energy Star Certified, DLC Certified or in-progress for other certifications. Call us for more details. For Energy Star specific questions, you can also visit <http://www.energystar.gov/products/certified-products>

# VIVIDGRO™ SERIES

Achieve energy-efficiency and optimize plant yield under white, visible light with our user-friendly VIVIDGRO™ Lights. These revolutionary products were created by the same Lighting Science engineers who helped both Astronauts aboard the International Space Station and field station scientists in Antarctica to cultivate their own food. Utilizing our proprietary grow spectrum, our LED grow lighting solutions are excellent for a variety of agricultural and horticultural lighting applications, including commercial grow facilities, homeowner/hobbyists, greenhouses, and growth chambers.



VIVIDGRO™ PAR38 Grow Lamp



VIVIDGRO™ v1 Grow Fixture



VIVIDGRO™ v2 Grow Fixture




COMING SOON!



VIVIDGRO™ v3 Grow Fixture



\* Versions of this product may be Energy Star Certified, DLC Certified or in-progress for other certifications. Call us for more details. For Energy Star specific questions, you can also visit <http://www.energystar.gov/products/certified-products>



LIGHTING  
SCIENCE

877.999.5742 | [www.lsgc.com](http://www.lsgc.com)  
1830 Penn Street | Melbourne, FL 32901 USA

© 2016 LIGHTING SCIENCE GROUP CORPORATION  
ALL RIGHTS RESERVED. SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.  
2016 LSPRO COMMERCIAL PRG\_REV\_04-04-16 FINAL

