

Support grips

Bus drop

Product description

Closed mesh
Single eye & locking bale grips

Features & applications

- Bus drop grips are woven of galvanized steel wire
- Relieve any direct tension from the critical connection and absorb vibration and flexing
- Offered with either the single eye or locking bale attachment
- Bus drop grips are used as cable support from bus duct
- Optional bus drop safety spring can be used with single eye type of disassembling draw bar from coil, placing through eye loop and replacing draw bar
- Single eye for use when cable is vertical and for applications where cable bends
- Locking bale attachment fits around beam or pipe and can be locked in place




BDS53




BDU53

Single eye grips

Cord diameter	Bale length	Mesh length	Approx. break strength†	Catalog no.*	
0.22-0.32" (5.6-8.1mm)	9" (228.6mm)	3.5" (88.9mm)	1,100 lbs.	<input type="checkbox"/> BDS22	•
0.30-0.43" (7.6-10.9mm)	9" (228.6mm)	4.5" (114.3mm)	1,100 lbs.	<input type="checkbox"/> BDS30	•
0.41-0.56" (10.4-14.2mm)	9" (228.6mm)	5.0" (127.0mm)	1,100 lbs.	<input type="checkbox"/> BDS41	•
0.53-0.73" (13.5-18.5mm)	9" (228.6mm)	6.5" (165.1mm)	1,100 lbs.	<input type="checkbox"/> BDS53	•
0.70-0.85" (17.8-21.6mm)	9" (228.6mm)	8.5" (215.9mm)	1,900 lbs.	<input type="checkbox"/> BDS70	•
0.82-1.00" (20.8-25.4mm)	9" (228.6mm)	8.5" (215.9mm)	1,900 lbs.	<input type="checkbox"/> BDS82	•
0.96-1.25" (24.4-31.8mm)	9" (228.6mm)	11.0" (279.4mm)	1,900 lbs.	<input type="checkbox"/> BDS96	•

Locking bale grips

Cord diameter	Bale length	Mesh length	Approx. break strength†	Catalog no.*	
0.22-0.32" (5.6-8.1mm)	12" (304.8mm)	3.5" (88.9mm)	1,100 lbs.	<input type="checkbox"/> BDU22	•
0.30-0.43" (7.6-10.9mm)	12" (304.8mm)	4.5" (114.3mm)	1,100 lbs.	<input type="checkbox"/> BDU30	•
0.41-0.56" (10.4-14.2mm)	12" (304.8mm)	5.0" (127.0mm)	1,100 lbs.	<input type="checkbox"/> BDU41	•
0.53-0.73" (13.5-18.5mm)	15" (381.0mm)	6.5" (165.1mm)	1,100 lbs.	<input type="checkbox"/> BDU53	•
0.70-0.85" (17.8-21.6mm)	16" (406.4mm)	8.5" (215.9mm)	1,900 lbs.	<input type="checkbox"/> BDU70	•
0.82-1.00" (20.8-25.4mm)	16" (406.4mm)	8.5" (215.9mm)	1,900 lbs.	<input type="checkbox"/> BDU82	•
0.96-1.25" (24.4-31.8mm)	17" (431.8mm)	11.0" (279.4mm)	1,900 lbs.	<input type="checkbox"/> BDU96	•

Accessories for support grips: service drop & bus drop, closed mesh grips

Description	<input type="checkbox"/>	
Safety spring, 40 lbs. load	<input type="checkbox"/> B2001	•
Safety spring, 80 lbs. load	<input type="checkbox"/> B2002	•



B2001



B2002

*Contact the factory for stainless steel support grips.

† To determine workload safety factor, divide approximate break strength by 10. See page N-34 for strength information. Consult factory for price and availability.

Compliances, specifications and availability are subject to change without notice.