

### CAST BRONZE GROUND CLAMPS

#### With Lay-in Feature

For connecting grounding conductor to water pipe, copper tube, ground rod or rebar. The open face design allows for fast lay-in of the tap conductor without the need for cutting. Simply reverse bottom clamp for smaller size rebar or rod. Connectors are provided with Silicon Bronze hardware.




Fig. 1




Fig. 2



D-35

CATALOG NUMBER	FIG #	ACCOMMODATES CONDUCTOR RANGE				REFERENCE DIMENSIONS			RECOMMENDED SCREW TORQUE “INCH POUNDS”
		MAIN			TAP				
		WATER PIPE	REBAR	GROUND ROD	GROUND	H	L	W	
C11K16D	Fig 1	1/2" - 1"	#4 - #6	3/8" - 1"	#10 - #2 Str.	1.64	2.28	0.66	50 in.-lbs.
C11K17D	Fig 2	[13 - 25]							

### DIE CAST CLAMPS

Die cast zinc with zinc plated screws.



CATALOG NUMBER	ACCOMMODATES CONDUCTOR RANGE		REFERENCE DIMENSIONS				RECOMMENDED SCREW TORQUE "INCH POUNDS"	
	WATER PIPE	GROUND					PIPE CLAMP	WIRE CLAMP
			H	L	W	C		
CZ-11	1/2 - 1 [13 - 25]	10 - 2 Str.	1.56 [40]	2.25 [56]	.56 [14]	.50 [13]	50 in.-lb.	50 in.-lb.