

# Hubbell SystemOne

Metal and Non-Metallic Floor Boxes

Fire-Rated Poke-Throughs



## The Hubbell SystemOne Floor Box Family

### Cast Iron



S1CFB

- Corrosion resistant for on-grade applications
- Oversized 1½" N.P.T. threaded conduit access holes for low voltage
- 1" N.P.T. threaded conduit access holes for power

### Steel



S1SFB

- Stamped steel construction
- Economical and light weight for above-grade applications
- Concentric knockouts permit various conduit sizes for both power and data services

### Steel AV



S1SFBAV

- Accommodates high-capacity multimedia applications in a 3½" minimum depth of pour
- Oversized 1½" N.P.T. threaded data hub
- ¾", 1" concentric knockouts for power services

### Features



- Easily installed, aesthetic and configurable floor box solution, for open floor plans that require both power and data services
- The Hubbell SystemOne™ Universal Cover mounts directly to the floor box riser, eliminating the need for an additional adapter collar
- The Hubbell SystemOne Universal Cover features ScrubShield™ technology that exceeds UL514 scrub water exclusion requirements
- Convenient cubic inch capacity (cm³) markings on interior of box
- Leveling feet provide before pour adjustability
- Non-metallic riser allows a simple saw cut for adjustment after pour
- Supplied with concrete cover and closure plugs (where applicable)
- Designed to accommodate multi-service applications with the wide offering of Hubbell SystemOne sub-plates
- Hubbell SystemOne Metal Floor Boxes are approved for use in the City of Chicago

### Non-Metallic



S1PFB

- Non-corrosive plastic construction
- Oversized 1½" data conduit hub for increased cable capacity and bend radius
- Parallel conduit hubs reduce labor and material cost, facilitating easier wire pull


### Features



- Economical, easy to install, in-floor delivery system for open plan spaces
- The Hubbell SystemOne Universal Cover mounts directly to the floor box riser, eliminating the need for an additional adapter collar
- Concrete cover, conduit reducers and conduit hub plugs included

## Hubbell SystemOne Universal Covers

### Universal Flange and Cover Assembly



- Hinged doors open 180 degrees flush to the carpet flange or tile
- Locking studs allow each door to be secured independently
- The universal carpet or tile flange can be used for Hubbell SystemOne Floor Boxes and Fire-Rated Poke-Throughs
- Finishes and colors available:



### Features

- Durable cast aluminum construction available in black, gray, brass, aluminum and ivory powder coat finishes
- Features ScrubShield<sup>™</sup> technology that exceeds UL514 scrub water exclusion requirements
- Provides consistent look and maximum functionality throughout the installed life

## Hubbell SystemOne Sub-Plates

### Sub-Plates

Hubbell's modular sub-plate design allows users to economically upgrade Hubbell SystemOne FRPT and Floor Boxes to accommodate future moves, adds and changes. See page 5 for complete offering.



4x4 Sub-Plate



Datacom and Power Sub-Plate



Extron<sup>®</sup> APP/MAPP and Power Sub-Plate



Dual Style Line<sup>®</sup> Decorator Sub-Plate



Twist-Lock<sup>®</sup> Sub-Plate



Furniture Feed Cover, Carpet

### Features

- Durable cast aluminum construction, powder coat finish
- Hubbell 4X4: four 20A, 125V receptacles, four keystone openings for voice/data jacks and flush multimedia connectors
- Hubbell X-END<sup>™</sup> and iSTATION<sup>™</sup> modular connectivity
- Accommodates Extron<sup>®</sup> Electronics Architectural Series audio/video system integration products
- Accommodates GFCI, surge and standard Style Line<sup>®</sup> Decorator receptacles
- Twist-Lock<sup>®</sup> receptacle with two flush keystone openings
- Large capacity and multi-service furniture feed applications
- Open system sub-plates permit maximum data flexibility

## Hubbell Power Devices and Connectivity

### Power Devices and Connectivity



Hubbell-Pro<sup>™</sup> Receptacles



Hubbell iSTATION<sup>™</sup>




Hubbell X-END<sup>™</sup>

### Features

- Choose from Hubbell's industry leading selection of wiring devices for power services
- Hubbell iSTATION<sup>™</sup> connectivity modules integrate with SystemOne to provide comprehensive multi-media solutions
- Hubbell X-END<sup>™</sup> application cables and tails allow for more connectivity in a smaller footprint

## Hubbell SystemOne Metal and Non-Metallic Floor Boxes

Dimensions Inches (mm)	Cast Iron	Steel	Steel A/V	Non-Metallic
 <p>Metal</p> <p>Non-Metallic</p>	 <p><b>S1CFB*</b></p>	 <p><b>S1SFB*</b></p>	 <p><b>S1SFBV*</b></p>	 <p><b>S1PFB</b></p>
Min. Depth of Pour	3.50" (88.9)	3.50" (88.9)	3.50" (88.9)	3.00" (76.2)
Adjustability	Fully	Fully	Fully	Fully
Cubic Inch Capacity (cm <sup>3</sup> )	156.0 cu. in. (2556.4)	175.7 cu. in. (2879.2)	177.5 cu. in. (2909.7)	100 cu. in. (1638.7)
Dimensions – A	3.00" (76.2)	3.00" (76.2)	3.00" (76.2)	6.00" (152.4)
Dimensions – B (Inside Diameter)	5.00" (127.0)	5.00" (127.0)	5.00" (127.0)	5.00" (127.0)
Dimensions – C	7.45" (189.2)	7.38" (187.4)	7.38" (187.4)	—
Dimensions – D	7.26" (184.4)	7.50" (190.5)	7.50" (190.5)	—
Power Entries	1" N.P.T. Access Holes	¾", 1" Concentric K.O.	¾", 1" Concentric K.O.	1" Conduit Hub
Data Entries	1½" N.P.T. Access Holes	¾", 1", 1 ¼" Concentric K.O.	1½" Threaded Hub (included)	1½" Conduit Hub
Concrete Cover Included	✓	✓	✓	✓
Closure Plugs Included	✓	—	✓	✓
Reducers	—	—	—	✓
Accepts Hubbell SystemOne Universal Cover	✓	✓	✓	✓
Cover Mounting Clips Included	✓	✓	✓	✓
Non-Metallic Low Voltage Divider (S1DIV1) Included	✓	✓	✓	✓

- UL File Number E92074.
- CSA File Number LR18416.

\*S1CFB, S1SFB, S1SFBV are approved for use in the City of Chicago.

## Hubbell SystemOne Universal Cover

- Cast aluminum construction
- Durable powder coat finish

Color	Carpet	Tile
Aluminum Finish	<b>S1CFCAL</b>	<b>S1TFCAL</b>
Brass Finish	<b>S1FCBRS</b>	<b>S1TFCBRS</b>
Black	<b>S1FCBBL</b>	<b>S1TFCBL</b>
Gray	<b>S1FCGY</b>	<b>S1TFCGY</b>
Ivory	<b>S1FCFI</b>	<b>S1TFCI</b>



## Floor Box Accessories


Description	Catalog Number
<b>Abandonment Plates</b> Used to cover abandoned SystemOne Fire-Rated Poke-Throughs or Floor Boxes.  Black Gray	 <b>S1AP4BL</b> <b>S1AP4GY</b>
<b>Replacement Side by Side Divider</b> Used to isolate compartments in S1SP, S1SPFFx, S1SPFFTx, S1SPDU, S1SPDUSL, S1SPDU2IM and S1SPSL2IM sub-plates. Included with all SystemOne Floor Boxes.	 <b>S1DIV1</b>
<b>1½" Threaded Hub</b> For use with S1SFBV ONLY. Permits feed-through applications. S1SFBV floor box includes one (1) threaded hub.	 <b>S1AVHUB15</b>
<b>Replacement Universal Cover Mounting Clips</b> Used to mount SystemOne Universal Cover to SystemOne metal and non-metallic floor boxes (S1CFB, S1SFB, S1SFBV, S1PFB). Includes clips and ground leads for (5) floor boxes. All SystemOne Floor Boxes include mounting clips.	 <b>S1FBCLIP5PK</b>

## Hubbell SystemOne Sub-Plates

Description	Catalog Number	Description	Catalog Number	Description	Catalog Number
<b>Style Line® Decorator/GFCI</b> (2) Style Line® Decorator openings for power and/or datacom applications.	 <b>S1SP</b>	<b>Duplex/Duplex</b> (2) Duplex openings for power and/or datacom applications.	 <b>S1SPDU</b>	<b>Duplex/Style Line® Decorator</b> (1) Duplex and (1) Style Line® Decorator opening for power and/or datacom applications.	 <b>S1SPDUSL</b>
ⓐ Non-Metallic ⓑ Metal		ⓐ Non-Metallic ⓑ Metal		ⓐ Non-Metallic ⓑ Metal	
<b>Hubbell 4 X 4</b> (4) 20A, 125V receptacles. (4) Keystone openings for Hubbell jacks or flush A/V connectors. Power can be wired as single or two circuit with isolated ground capability.	 <b>S1SP4X4</b>	<b>Carpet Furniture Feed Cover/Flange*</b> (1) 3/4" and (1) 1 1/2" N.P.T. access holes for power and/or datacom applications. Universal Cover not required. Includes carpet flange.		<b>Tile Furniture Feed Cover/Flange*</b> (1) 3/4" and (1) 1 1/2" N.P.T. access holes for power and/or datacom applications. Universal Cover not required. Includes tile flange.	
Ⓓ		ⓐ Non-Metallic Aluminum Fin. ⓑ Metal Brass Fin. Black Gray	<b>S1SPFFAL</b> <b>S1SPFFBRS</b> <b>S1SPFFBL</b> <b>S1SPFFGY</b>	ⓐ Non-Metallic Aluminum Fin. ⓑ Metal Brass Fin. Black Gray	<b>S1SPFFTAL</b> <b>S1SPFFTBRS</b> <b>S1SPFFTBL</b> <b>S1SPFFTGY</b>
Provided with 15 ft. wire leads Provided with 30 ft. wire leads	<b>S1SP4X415</b> <b>S1SP4X430</b>				
<b>Single Receptacle + Data</b> Opening for 20 or 30A Twist-Lock® receptacle (1.56" OD) and (2) Keystone openings for Hubbell jacks or flush A/V connectors.	 <b>S1SPTL</b>	<b>Hubbell DataCom + Power</b> (1) 20A, 125V receptacle and 3 unit recessed iSTATION™ opening for data, voice, and A/V applications.	 <b>S1SP3IM</b>	<b>Hubbell DataCom + Duplex</b> (1) Duplex opening, (2) flush Keystone openings and 1.5 unit recessed iSTATION™ opening for data, voice and A/V applications.	 <b>S1SPDU2IM</b>
Ⓓ		ⓐ		ⓐ	
<b>Hubbell DataCom + Style Line® Decorator</b> (1) Style Line® Decorator opening, (2) flush Keystone openings and 1.5 unit recessed iSTATION™ opening for data, voice and A/V applications.	 <b>S1SPSL2IM</b>	<b>Hubbell DataCom</b> 1 unit flush iSTATION™ opening and 3 unit recessed iSTATION™ opening for data, voice, and A/V applications.	 <b>S1SP4IM</b>	<b>Active Multimedia + Power</b> Single 20A, 125V receptacle; (2) flush Keystone openings; (1) rectangular Style Line® Decorator opening to accommodate active multimedia modules or low voltage outlet frames.	 <b>S1SPAMM20</b>
ⓐ		ⓑ		ⓐ	
<b>Extron® or FSR + Power</b> (1) 20A, 125V receptacle. Recessed opening for (3) single Extron® MAAP series adapter plates or FSR IPS plates.	 <b>S1SPEXT1</b>	<b>Extron® or FSR + Power</b> (1) 20A, 125V receptacle. Recessed opening for (1) single Extron® MAAP and (2) single AAP series adapter plates or FSR IPS plates.	 <b>S1SPEXT2</b>	<b>Extron® or FSR Single-Service</b> Recessed opening for (2) single Extron® MAAP and (2) single AAP series adapter plates or FSR IPS plates.	 <b>S1SPEXT3</b>
Ⓓ		Ⓓ		Ⓓ.5	
<b>Extron® AAP + Power</b> (1) 20A, 125V receptacle. (2) flush Keystone and recessed opening for (2) single Extron® AAP Series adapter plates.	 <b>S1SPEXT4</b>	<b>Ortronics Series II® + Power</b> (1) 20A, 125V receptacle. Recessed opening for (3) 1 unit Ortronics Series II® modules.	 <b>S1SPORT</b>	<b>Ortronics TracJack® + Power</b> (1) 20A, 125V receptacle. Recessed bezel for (6) Ortronics TracJack® modules.	 <b>S1SPTRAC</b>
Ⓓ		ⓐ		ⓐ	
<b>Panduit Mini Com® 4 X 4</b> (4) 20A, 125V receptacles. (4) Openings for Panduit Mini-Com Connectivity.	 <b>S1SP4X4PA</b>	<b>SYSTIMAX® 4 X 4</b> (4) 20A, 125V receptacles. (4) Openings for SYSTIMAX® Connectivity.	 <b>S1SP4X4SYS</b>	<b>Siemon MAX® + Power</b> (1) 20A, 125V receptacle. Recessed bezel for (6) Siemon MAX® modules.	 <b>S1SPMAX</b>
Ⓓ		Ⓓ		ⓐ	

ⓐ Signifies minimum depth of concrete pour in inches for Metal Floor Boxes (**S1CFB**, **S1SFB** and **S1SFBV**) and Non-Metallic Floor Box (**S1PFB**).  
\*Furnished with two screw-in flexible metal conduit connectors.

## Sub-Plate Accessories

Description	Catalog Number	Description	Catalog Number
<b>Replacement Threaded Conduit Plugs</b> Used with <b>S1SPFFx</b> and <b>S1SPFFTx</b> ONLY. Sub-plate is supplied with plugs.			
<b>6-Port Replacement Data Frames</b> Used with open systems sub-plates. Sub-plate is supplied with data frame. Siemon MAX® for use with <b>S1SPMAX</b> sub-plate. Ortronics TracJack® for use with <b>S1SPTRAC</b> sub-plate.			<b>S1DFMAX</b> <b>S1DFTRAC</b>
Black Style Line® blank frame.			<b>2100BK</b>
Description	Catalog Number	Description	Catalog Number
1 1/2" Aluminum Fin.	<b>S1FP15AL</b>	3/4" Aluminum Fin.	<b>S1FP34AL</b>
1 1/2" Brass Fin.	<b>S1FP15BRS</b>	3/4" Brass Fin.	<b>S1FP34BRS</b>
1 1/2" Black	<b>S1FP15BL</b>	3/4" Black	<b>S1FP34BL</b>
1 1/2" Gray	<b>S1FP15GY</b>	3/4" Gray	<b>S1FP34GY</b>

Extron® is a registered trademark of Extron Electronics. MAX® is a registered trademark of The Siemon Company. Mini-Com® and Panduit® are registered trademarks of Panduit Corp. SYSTIMAX® is a registered trademark of CommScope, Inc. TracJack®, Series II® & Ortronics® are registered trademarks of Ortronics/Legrand.

## Hubbell SystemOne Poke Through


### 4-Inch Core Through Floor Fittings



- Step down installation clips allow the fitting to be installed or removed from the floor above
- Fire barrier expands during fire conditions to maintain the floor's fire rating
- Adjustable lower fire barrier accommodates concrete floor thicknesses from 2¼ to 7 in.
- Oversized E.M.T. conduit tubes for increased cable capacity

## Hubbell SystemOne Universal Cover

### Universal Flange and Cover Assembly



- Hinged doors open 180 degrees flush to the carpet flange or tile
- Locking studs allow each door to be secured independently
- The universal carpet or tile flange can be used for Hubbell SystemOne Fire-Rated Poke-Throughs and Floor Boxes
- Finishes and colors available:



## Hubbell SystemOne Sub-Plates

### Sub-Plates

Hubbell's modular sub-plate design allows users to economically upgrade Hubbell SystemOne FRPT and Floor Boxes to accommodate future moves, adds and changes. See page 9 for complete offering.



**4x4 Sub-Plate**



**Datacom and Power Sub-Plate**



**Extron® APP/MAPP and Power Sub-Plate**



**Dual Style Line® Decorator Sub-Plate**



**Twist-Lock® Sub-Plate**



**Furniture Feed Cover, Carpet**

Extron® is a registered trademark of Extron Electronics. Siemon™ is a trademark of The Siemon Company. Panduit® is a registered trademark of Panduit Corp. SYSTIMAX® is a registered trademark of CommScope, Inc. Ortronics® is a registered trademark of Ortronics/Legrand.

### Features US LISTED

- Accepts all Hubbell SystemOne covers and sub-plates
- Excellent solution for retrofit and new construction
- Delivers power, voice, data and multimedia
- UL listed for use in 1 – 4 hour fire rated floors at 100% rated fill
- Available with integral power junction box
- SystemOne Fire-Rated Poke-Throughs are approved for use in the City of Chicago
- UL installation spacing - minimum 2 feet on center, not more than one per 65 square feet of floor area in each span

### Features

- Durable cast aluminum construction available in black, gray, brass, aluminum and ivory powder coat finishes
- Features ScrubShield™ technology that exceeds UL514 scrub water exclusion requirements
- Provides consistent look and maximum functionality throughout the installed life

### Features

- Durable cast aluminum construction, powder coat finish
- Hubbell 4X4: four 20A, 125V receptacles, four keystone openings for voice/data jacks and flush multimedia connectors
- Hubbell X-END™ and iSTATION™ modular connectivity
- Accommodates Extron® Electronics Architectural Series audio/video system integration products
- Accommodates GFCI, surge and standard Style Line® Decorator receptacles
- Twist-Lock® receptacle with two flush keystone openings
- Large capacity and multi-service furniture feed applications
- Open system sub-plates permit maximum data flexibility

## Hubbell SystemOne 4-Inch Core Hole, One-Piece Units

All Hubbell SystemOne 4-inch core, **one-piece units** include the sub-plate and cover to simplify your order and reduce installation time. Units are also available with a power junction box installed. The junction box is also available for purchase separately.



Description	Color	Catalog Number without Junction Box	Catalog Number with Junction Box*
<p><b>One-Piece 4X4 Poke-Through</b></p> <p>Assembled-unit includes:</p> <ul style="list-style-type: none"> <li>Hubbell SystemOne 4X4 floor fitting (<b>S1PT4X4FIT</b>)</li> <li>4x4 sub-plate (<b>S1SP4X4</b>)</li> <li>Finish flange and universal carpet cover assembly (<b>S1CFCxx</b>)</li> </ul> <p>Keystone openings accept Hubbell modular jacks, X-END™ connectors and flush multimedia Snap Fit connectors. Receptacles feature single or two circuit wiring and isolated ground capability.</p>	<p>Aluminum Finish</p> <p>Brass Finish</p> <p>Black/Brass Finish</p> <p>Black</p> <p>Gray</p>	<p><b>S1PT4X4AL</b></p> <p><b>S1PT4X4BRS</b></p> <p><b>S1PT4X4BRS3</b></p> <p><b>S1PT4X4BL</b></p> <p><b>S1PT4X4GY</b></p>	<p><b>S1PT4X4ALJ</b></p> <p><b>S1PT4X4BRSJ</b></p> <p><b>S1PT4X4BRS3J</b></p> <p><b>S1PT4X4BLJ</b></p> <p><b>S1PT4X4GYJ</b></p>
<p><b>One-Piece Dual Style Line® Decorator Poke-Through</b></p> <p>Assembled-unit includes:</p> <ul style="list-style-type: none"> <li>Hubbell SystemOne dual channel floor fitting (<b>S1PTFIT</b>)</li> <li>Dual Style Line® Decorator opening sub-plate (<b>S1SP</b>)</li> <li>Finish flange and universal carpet cover assembly (<b>S1CFCxx</b>)</li> </ul> <p>Style Line® Decorator openings accept two Style Line® Decorator or one surge or GFCI receptacle and one Style Line® Decorator receptacle. Outlet frames can be used to convert the application to a 6-port multi-service or a 12-port all communication solution. Fitting is 4-hr rated at 100% fill to accommodate (12) Cat 6A cables (0.330" diameter).</p>	<p>Aluminum Finish</p> <p>Brass Finish</p> <p>Black</p> <p>Gray</p>	<p><b>S1PTAL</b></p> <p><b>S1PTBRS</b></p> <p><b>S1PTBL</b></p> <p><b>S1PTGY</b></p>	<p><b>S1PTALJ</b></p> <p><b>S1PTBRSJ</b></p> <p><b>S1PTBLJ</b></p> <p><b>S1PTGYJ</b></p>
<p><b>One-Piece Modular A/V Poke-Through</b></p> <p>Assembled-unit includes:</p> <ul style="list-style-type: none"> <li>Hubbell SystemOne A/V floor fitting (<b>S1PTAVFIT</b>)</li> <li>20A, 125V power and 3-unit iSTATION™ sub-plate (<b>S1SP3IM</b>)</li> <li>Finish flange and universal carpet cover assembly (<b>S1CFCxx</b>)</li> </ul> <p>The iSTATION™'s recessed opening can accommodate data/voice/audio and video solutions including 15-pin VGA, RCA, S-Video, 3.5mm stereo, X-END™, HDMI and XLR microphone jacks.</p>	<p>Aluminum Finish</p> <p>Brass Finish</p> <p>Black</p> <p>Gray</p>	<p><b>S1PT3IMAL</b></p> <p><b>S1PT3IMBRS</b></p> <p><b>S1PT3IMBL</b></p> <p><b>S1PT3IMGY</b></p>	<p><b>S1PT3IMALJ</b></p> <p><b>S1PT3IMBRSJ</b></p> <p><b>S1PT3IMBLJ</b></p> <p><b>S1PT3IMGYJ</b></p>
<p><b>One-Piece Furniture Feed Poke-Through</b></p> <p>Assembled-unit includes:</p> <ul style="list-style-type: none"> <li>Hubbell SystemOne A/V floor fitting (<b>S1PTAVFIT</b>)</li> <li>Hubbell SystemOne Furniture Feed Cover Plate (<b>S1SPFFxx</b>)</li> </ul> <p>This solution provides one ¾ in. conduit for power and one 1½ in. conduit for low-voltage. Furnished with two screw-in flexible metal conduit connectors.</p>	<p>Aluminum Finish</p> <p>Brass Finish</p> <p>Black</p> <p>Gray</p>	<p><b>S1PTFFAL</b></p> <p><b>S1PTFFBRS</b></p> <p><b>S1PTFFBL</b></p> <p><b>S1PTFFGY</b></p>	<p><b>S1PTFFALJ</b></p> <p><b>S1PTFFBRSJ</b></p> <p><b>S1PTFFBLJ</b></p> <p><b>S1PTFFGYJ</b></p>

\* Junction box factory installed on through floor fitting.

## Hubbell SystemOne 4-Inch Core Through Floor Fittings



Description

Catalog Number  
without Junction Box

Catalog Number  
with Junction Box\*

### 4X4 Through Floor Fitting

**S1PT4X4FIT**

**S1PT4X4FITJ**

Through floor fitting with two ¾ in. E.M.T. for communications and one ¾ in. E.M.T. for power. For use with Hubbell SystemOne Universal Covers and **S1SP4X4** and **S1SPTL** series sub-plates **only**. Universal cover and sub-plate ordered separately.



### Dual Channel Through Floor Fitting

**S1PTFIT**

**S1PTFITJ**

Through floor fitting with two 1 in. E.M.T. conduit stems to feed power and/or communication services. For use with Hubbell SystemOne universal covers and all Hubbell sub-plates **except S1SP4X4** and **S1SPTL** series. Universal cover and sub-plate ordered separately.



### A/V Through Floor Fitting

**S1PTAVFIT**

**S1PTAVFITJ**

Through floor fitting with one ¾ in. E.M.T. conduit stem for power and one 1½ in. E.M.T. conduit stem for communication services. Ideal for demanding, high capacity audio/video and data requirements. For use with Hubbell SystemOne universal covers and all Hubbell sub-plates **except S1SP4X4** and **S1SPTL** series. Universal cover and sub-plate ordered separately.



\* Junction box factory installed on through floor fitting.

## Hubbell SystemOne Universal Cover

- Cast aluminum construction
- Durable powder coat finish



Color	Carpet	Tile
Aluminum Finish	<b>S1CFCAL</b>	<b>S1TFCAL</b>
Brass Finish	<b>S1CFCBRS</b>	<b>S1TFCBRS</b>
Black	<b>S1CFCBL</b>	<b>S1TFCBL</b>
Gray	<b>S1CFCGY</b>	<b>S1TFCGY</b>
Ivory	<b>S1CFCI</b>	<b>S1TFCI</b>



## Poke Through Accessories

Description

Catalog Number

### Abandonment Plates

Used to cover abandoned SystemOne Fire-Rated Poke-Throughs or Floor Boxes.



Black  
Gray

**S1AP4BL**  
**S1AP4GY**

### Fire-Rated Closure Plug

Used to seal a 4-inch core hole when the FRPT is no longer required and the through-floor fitting is removed. Maintains the floor's 1–4 hour fire rating.



Black  
Gray

**S1FRP4BL**  
**S1FRP4GY**

### Power Junction Box

For use with SystemOne Fire-Rated Poke-Throughs. Provides 27.0 cubic inches.

Trade size knockouts:

Top (1) 1 inch  
Bottom (1) ¾ inch  
Sides (2) ½ inch  
(1) ¾ inch



**S1FRPTJB**

## Hubbell SystemOne Sub-Plates

Description	Catalog Number	Description	Catalog Number	Description	Catalog Number
<b>Style Line<sup>®</sup> Decorator/GFCI</b> (2) Style Line <sup>®</sup> Decorator openings for power and/or datacom applications.	 <b>S1SP</b>	<b>Duplex/Duplex</b> (2) Duplex openings for power and/or datacom applications.	 <b>S1SPDU</b>	<b>Duplex/Style Line<sup>®</sup> Decorator</b> (1) Duplex and (1) Style Line <sup>®</sup> Decorator opening for power and/or datacom applications.	 <b>S1SPDUSL</b>
<b>Hubbell 4 X 4</b> (4) 20A, 125V receptacles. (4) Keystone openings for Hubbell jacks or flush A/V connectors. Power can be wired as single or two circuit with isolated ground capability.	 <b>S1SP4X4</b>	<b>Carpet Furniture Feed Cover/Flange*</b> (1) 3/4" and (1) 1 1/2" N.P.T. access holes for power and/or datacom applications. Universal Cover not required. Includes carpet flange.	 <b>S1SPFFAL</b> Aluminum Fin. <b>S1SPFFBRS</b> Brass Fin. <b>S1SPFFBL</b> Black <b>S1SPFFGY</b> Gray	<b>Tile Furniture Feed Cover/Flange*</b> (1) 3/4" and (1) 1 1/2" N.P.T. access holes for power and/or datacom applications. Universal Cover not required. Includes tile flange.	 <b>S1SPFFTAL</b> Aluminum Fin. <b>S1SPFFTBRS</b> Brass Fin. <b>S1SPFFTBL</b> Black <b>S1SPFFTGY</b> Gray
Provided with 15 ft. wire leads Provided with 30 ft. wire leads	<b>S1SP4X415</b> <b>S1SP4X430</b>				
<b>Single Receptacle + Data</b> Opening for 20 or 30A Twist-Lock <sup>®</sup> receptacle (1.56" OD) and (2) Keystone openings for Hubbell jacks or flush A/V connectors.	 <b>S1SPTL</b>	<b>Hubbell DataCom + Power</b> (1) 20A, 125V receptacle and 3 unit recessed iSTATION <sup>™</sup> opening for data, voice, and A/V applications.	 <b>S1SP3IM</b>	<b>Hubbell DataCom + Duplex</b> (1) Duplex opening, (2) flush Keystone openings and 1.5 unit recessed iSTATION <sup>™</sup> opening for data, voice and A/V applications.	 <b>S1SPDU2IM</b>
<b>Hubbell DataCom + Style Line<sup>®</sup> Decorator</b> (1) Style Line <sup>®</sup> Decorator opening, (2) flush Keystone openings and 1.5 unit recessed iSTATION <sup>™</sup> opening for data, voice and A/V applications.	 <b>S1SPSL2IM</b>	<b>Hubbell DataCom</b> 1 unit flush iSTATION <sup>™</sup> opening and 3 unit recessed iSTATION <sup>™</sup> opening for data, voice, and A/V applications.	 <b>S1SP4IM</b>	<b>Active Multimedia + Power</b> Single 20A, 125V receptacle; (2) flush Keystone openings; (1) rectangular Style Line <sup>®</sup> Decorator opening to accommodate active multimedia modules or low voltage outlet frames.	 <b>S1SPAMM20</b>
<b>Extron<sup>®</sup> or FSR + Power</b> (1) 20A, 125V receptacle. Recessed opening for (3) single Extron <sup>®</sup> MAAP series adapter plates or FSR IPS plates.	 <b>S1SPEXT1</b>	<b>Extron<sup>®</sup> or FSR + Power</b> (1) 20A, 125V receptacle. Recessed opening for (1) single Extron <sup>®</sup> MAAP and (2) single AAP series adapter plates or FSR IPS plates.	 <b>S1SPEXT2</b>	<b>Extron<sup>®</sup> or FSR Single-Service</b> Recessed opening for (2) single Extron <sup>®</sup> MAAP and (2) single AAP series adapter plates or FSR IPS plates.	 <b>S1SPEXT3</b>
<b>Extron<sup>®</sup> AAP + Power</b> (1) 20A, 125V receptacle. (2) flush Keystone and recessed opening for (2) single Extron <sup>®</sup> AAP Series adapter plates.	 <b>S1SPEXT4</b>	<b>Ortronics Series II<sup>®</sup> + Power</b> (1) 20A, 125V receptacle. Recessed opening for (3) 1 unit Ortronics Series II <sup>®</sup> modules.	 <b>S1SPORT</b>	<b>Ortronics TracJack<sup>®</sup> + Power</b> (1) 20A, 125V receptacle. Recessed bezel for (6) Ortronics TracJack <sup>®</sup> modules.	 <b>S1SPTRAC</b>
<b>Panduit Mini Com<sup>®</sup> 4 X 4</b> (4) 20A, 125V receptacles. (4) Openings for Panduit Mini-Com Connectivity.	 <b>S1SP4X4PA</b>	<b>SYSTIMAX<sup>®</sup> 4 X 4</b> (4) 20A, 125V receptacles. (4) Openings for SYSTIMAX <sup>®</sup> Connectivity.	 <b>S1SP4X4SYS</b>	<b>Siemon MAX<sup>®</sup> + Power</b> (1) 20A, 125V receptacle. Recessed bezel for (6) Siemon MAX <sup>®</sup> modules.	 <b>S1SPMAX</b>

\*Furnished with two screw-in flexible metal conduit connectors.

## Sub-Plate Accessories

Description	Catalog Number	Description	Catalog Number
<b>Replacement Threaded Conduit Plugs</b> Used with <b>S1SPFFx</b> and <b>S1SPFFTx</b> ONLY. Sub-plate is supplied with plugs.		<b>6-Port Replacement Data Frames</b> Used with open systems sub-plates. Sub-plate is supplied with data frame. Siemon MAX <sup>®</sup> for use with <b>S1SPMAX</b> sub-plate. Ortronics TracJack <sup>®</sup> for use with <b>S1SPTRAC</b> sub-plate.	 <b>S1DFMAX</b>  <b>S1DFTRAC</b>
<b>1 1/2" Aluminum Fin.</b>	<b>S1FP15AL</b>	<b>3/4" Aluminum Fin.</b>	<b>S1FP34AL</b>
<b>1 1/2" Brass Fin.</b>	<b>S1FP15BRS</b>	<b>3/4" Brass Fin.</b>	<b>S1FP34BRS</b>
<b>1 1/2" Black</b>	<b>S1FP15BL</b>	<b>3/4" Black</b>	<b>S1FP34BL</b>
<b>1 1/2" Gray</b>	<b>S1FP15GY</b>	<b>3/4" Gray</b>	<b>S1FP34GY</b>
		Black Style Line <sup>®</sup> blank frame.	 <b>2100BK</b>

Extron<sup>®</sup> is a registered trademark of Extron Electronics. MAX<sup>®</sup> is a registered trademark of The Siemon Company. Mini-Com<sup>®</sup> and Panduit<sup>®</sup> are registered trademarks of Panduit Corp. SYSTIMAX<sup>®</sup> is a registered trademark of CommScope, Inc. TracJack<sup>®</sup>, Series II<sup>®</sup> & Ortronics<sup>®</sup> are registered trademarks of Ortronics/Legrand.

# Hubbell Power Devices



	Description <b>Heavy Duty Spec Grade</b> 15A, 125V 20A, 125V	Catalog No. <b>HBL5262x</b> <b>HBL5362x</b>		Description <b>Style Line® Decorator</b> 15A, 125V 20A, 125V	Catalog No. <b>DR15x</b> <b>DR20x</b>		Description <b>Hubbell-Pro™</b> Finder groove face 15A, 125V 20A, 125V	Catalog No. <b>5262x</b> <b>5362x</b>		Description <b>Isolated Ground Orange</b> 15A, 125V 20A, 125V	Catalog No. <b>IG5252</b> <b>IG5352</b>
	Description <b>Twist-Lock®</b> 2 Pole, 3 Wire 20A, 125V 20A, 250V	Catalog No. <b>HB2310</b> <b>HB2320</b>		Description <b>Twist-Lock®</b> 2 Pole, 3 Wire 15A, 125/250V 20A, 3Ø 250V	Catalog No. <b>HBL2610</b> <b>HBL2620</b>		Description <b>Surge Suppression</b> 15A, 125V 20A, 125V	Catalog No. <b>HBL5262xSA</b> <b>HBL5362xSA</b>		Description <b>LED GFCI</b> 15A, 125V 20A, 125V	Catalog No. <b>GF15xLA</b> <b>GF20xLA</b>

For color options: replace x with the following: AL (Almond), BK (Black), GY (Gray), I (Ivory), OW (Office White) or W (White).  
For Brown, remove x. Devices without an x are available in Brown only. Please visit our website a [www.hubbell-wiring.com](http://www.hubbell-wiring.com) to view colors in our virtual catalog.

# Hubbell Multimedia Connectivity

	Description <b>HXJ Series Jack</b> 10GbE Cat 6 Cat5e	Catalog No. <b>HXJ6Axx</b> <b>HXJ6xx</b> <b>HXJ5Exx</b>		Description <b>RCA Connector</b> Solder 110 Termination Pass-through	Catalog No. <b>SFRCx(x)</b> <b>SFRC110(x)</b> <b>SFRC(x)Rx</b>		Description <b>S-Video Connector</b> 110 Termination Pass-through	Catalog No. <b>SFSV110BK</b> <b>SFSVBK</b>
	Description <b>3.5mm Stereo Jack</b> Solder Screw Terminal Pass-through	Catalog No. <b>SF35SJx</b> <b>SF35STx</b> <b>SF35FFx</b>		Description <b>USB Coupler</b> A to B A to A	Catalog No. <b>SFUSBABW</b> <b>SFUSBAAW</b>		Description <b>Data Coupler</b> Cat 6 Cat 5e	Catalog No. <b>SFC6BK</b> <b>SFC5EBK</b>
	Description <b>XLR 3-Pin Connector</b> Solder Screw Terminal	Catalog No. <b>XLR10</b> <b>XLRST10</b>		Description <b>RCA Module</b> Solder 110 Termination Pass-through	Catalog No. <b>IMCRS1xx</b> <b>IMCR110xx</b> <b>IMCRF1xx</b>		Description <b>X-End™ Tails - 15-pin to 8-pin</b> Non-Plenum Plenum	Catalog No. <b>15M6P1</b> <b>15MP6P1</b>
	Description <b>HDMI Connector</b> Coupler 3" Tail	Catalog No. <b>HDMIC1</b> <b>HDMIT1</b>		Description <b>X-End™ A/V Horizontal Run</b> Non-Plenum, 8-Pin Plenum, 8-Pin	Catalog No. <b>VGA6***BK</b> <b>VGA6P***BK</b>		Description <b>X-End™ VGA Plug-n-Play Conn.</b> Straight 180° Angled 45° 180°	Catalog No. <b>15S6P1</b> <b>15A6P1</b> <b>15N6P1</b>
	Description <b>Link Cord</b> Connector to Device	Catalog No. <b>HDL*BK</b>		Description <b>X-End™ Patch Cords</b> S-Video & 3.5mm S-Video & 2 RCA 3 RCA w/ L/R Audio 3 RCA Video 3 RCA w/ S/PDIF 5 RCA w/ L/R Audio 3 RCA & S-Video S-Video, 3 RCA w/ L/R Audio 3 RCA & 3.5mm 5-BNC RGBHV	Catalog No. <b>AVS35**</b> <b>AVSRA**</b> <b>AVRC**</b> <b>AVCR**</b> <b>AVCRD**</b> <b>AVCAR**</b> <b>AVSCR**</b> <b>AVSRC**</b> <b>AVC35**</b> <b>AVB**</b>		Description <b>X-End™ Video Plug-n-Play Module</b> RCA Component w/S-Video 5-BNC RGBHV	Catalog No. <b>IMSCR815x</b> <b>IMB815x</b>
	Description <b>HDMI Patch Cord</b> 3' Black 6' Black	Catalog No. <b>HDPC03BK</b> <b>HDPC06BK</b>		Description <b>X-End™ AV Plug-n-Play Module</b> RCA Component S-Video, 2 RCA S-Video, 3.5mm	Catalog No. <b>IMCR81x</b> <b>IMSRA81x</b> <b>IMS3581x</b>		Description <b>X-End™ Keystone Coupler</b> 4 Inch Tail 90 Degree Straight	Catalog No. <b>SFAVCT</b> <b>SFAVCN</b> <b>SFAVCS</b>
	Description <b>Horizontal Cord</b> Connector to Connector	Catalog No. <b>HDH*BK</b>						

For housing color options: Replace x with the following: AL (Almond), BK (Black), GY (Gray), EI (Electric Ivory), OW (Office White) or W (White).  
Replace xx with the following: AL (Almond), BK (Black), B (Blue), EI (Electric Ivory), GL (Gold), GY (Gray), GN (Green), LA (Light Almond), OW (Office White), OR (Orange), P (Purple), R (Red), TI (Telco Ivory), W (White) or Y (Yellow).  
For insulator color options: Replace (x) with the following: BK (Black), B (Blue), GN (Green), OR (Orange), R (Red), W (White) or Y (Yellow).  
For length options: Replace \* with the following 10 (10'), 15 (15'), 20 (20'), 25 (25') and 30 (30'). Black and non-plenum only.  
Replace \*\* with the following 05 (5'), 10 (10') or T1 (1" Tail)  
\*\*\* Available from 05 (5') to 100 (100'). Order in multiples of 5 ft.  
Please visit our website a [www.hubbell-wiring.com](http://www.hubbell-wiring.com) to view colors in our virtual catalog.

# Hubbell Multimedia Modules and Frames

	Description <b>XLR Panel Mount Module</b> Blank, 1.5-Unit	Catalog No. <b>IMAVB15x</b>		Description <b>Keystone Module</b> 1-Port, 1-Unit 2-Port, 1-Unit	Catalog No. <b>IM1K1x</b> <b>IM2K1x</b>		Description <b>Angled Keystone Module</b> 1-Port, 1.5-Unit 2-Port, 1.5-Unit	Catalog No. <b>IM1KA15x</b> <b>IM2KA15x</b>
	Description <b>Style Line® Decorator Frame</b> 2-Port 3-Port 4-Port 6-Port	Catalog No. <b>ISF2x</b> <b>ISF3x</b> <b>ISF4x</b> <b>ISF6x</b>		Description <b>Duplex Outlet Frame</b> 2-Port 4-Port	Catalog No. <b>BR106B</b> <b>Q106x</b>		Description <b>15/9-pin or HDMI Blank Module</b> 1-Unit 2-Unit w/3.5mm Stereo Jack	Catalog No. <b>IMBDS1x</b> <b>IMB15315x</b>

For color options: Replace x with the following: AL (Almond), BK (Black), GY (Gray), EI (Electric Ivory), OW (Office White) or W (White).  
Please visit our website a [www.hubbell-wiring.com](http://www.hubbell-wiring.com) to view colors in our virtual catalog.

# Hubbell SystemOne Configuration Chart

		Floor Boxes				4" Core Hole Fire-Rated Poke-Throughs*			
		Non-Metallic	Metal						
Sub-Plates									
		<b>S1PFB</b>	<b>S1CFB</b>	<b>S1SFB</b>	<b>S1SFB</b>	<b>S1PTFIT</b>	<b>S1PT4X4FIT</b>	<b>S1PTAVFIT</b>	
<b>S1SP</b>	Style Line® Decorator/GFCI		3	3.5	3.5	3.5	✓+ (Single-Service)	✗ (Multi-Service)	
<b>S1SPDU</b>	Duplex/Duplex		3	3.5	3.5	3.5	✓+ (Single-Service)	✗ (Multi-Service)	
<b>S1SPDU</b>	Duplex/Style Line® Decorator		3	3.5	3.5	3.5	✓+ (Single-Service)	✗ (Multi-Service)	
<b>S1SP4X4</b> <b>S1SP4X4PA</b> <b>S1SP4X4SYS</b>	Hubbell 4 X 4 Panduit Mini-Com® 4 X 4 SYSTIMAX® 4 X 4		4	4	4	4	✗	✓+ ✗	
<b>S1SPTL</b>	Twist-Lock® Receptacle + Data		4	4	4	4	✗	✓+ ✗	
<b>S1SP3IM</b>	Hubbell DataCom + Power		5	5	5	5	✓	✗ ✓+	
<b>S1SP4IM</b>	Hubbell DataCom		3.5	3.5	3.5	3.5	✓	✗ ✓+	
<b>S1SPDU2IM</b>	Hubbell DataCom + Duplex		5	5	5	5	✓	✗ ✓+	
<b>S1SPSL2IM</b>	Hubbell DataCom + Style Line® Decorator		5	5	5	5	✓	✗ ✓+	
<b>S1SPFFxx</b> (Carpet) <b>S1SPFFTx</b> (Tile)	Furniture Feed Cover/ Flange (Replace "x" with BRS (brass finish), AL (aluminum finish), BL (black) or GY (gray).		3	3.5	3.5	3.5	✓	✗ ✓+	
<b>S1SPEXT1</b>	Extron® MAAP + Power		4	4	4	4	✓	✗ ✓+	
<b>S1SPEXT2</b>	Extron® AAP/MAAP + Power		4	4	4	4	✓	✗ ✓+	
<b>S1SPEXT3</b>	Extron Datacom		4.5	4.5	4.5	4.5	✓	✗ ✓+	
<b>S1SPEXT4</b>	Extron AAP + Flush Keystone + Power		4	4	4	4	✓	✗ ✓+	
<b>S1SPORT</b>	Ortronics Series II® + Power		5	5	5	5	✓	✗ ✓+	
<b>S1SPTRAC</b>	Ortronics TracJack® + Power		5	5	5	5	✓	✗ ✓+	
<b>S1SPMAX</b>	Siemon MAX® + Power		5	5	5	5	✓	✗ ✓+	
<b>S1SPAMM20</b>	Active Multimedia + Flush Keystone + Power		5	5	5	5	✓	✗ ✓+	
<b>S1CFCxx</b> SystemOne Carpet Cover	SystemOne Floor Boxes and FRPTs use SystemOne Universal Covers (Replace "x" with BRS (brass finish), AL (aluminum finish), BL (black), GY (gray) or I (ivory).			Signifies minimum depth of concrete pour in inches for Hubbell SystemOne Floor Boxes.			✓+ Recommended Floor Fitting	✓ Alternative Floor Fitting	✗ Not Compatible
<b>S1TFCxx</b> SystemOne Tile Cover				*Fire-Rated Poke-Throughs available with integral power junction box. Add "J" suffix to Catalog Numbers listed above (Example: <b>S1PTFITJ</b> ).			Extron® is a registered trademark of Extron Electronics. MAX® is a registered trademark of The Siemon Company. Mini-Com® and Panduit® are registered trademarks of Panduit Corp. SYSTIMAX® is a registered trademark of CommScope, Inc. TracJack®, Series II® & Ortronics® are registered trademarks of Ortronics/Legrand.		

**For more information on Hubbell's complete line of labor saving Delivery Systems products:**



Hubbell's Delivery Systems Product Guide is a complete guide to delivery products. It also offers a comprehensive offering of Power, Data and A/V accessories.



Hubbell offers a line of modular wiring and raised access floor products that minimize installation cost and simplify moves, adds and changes of commercial spaces.



Hubbell takes raceway to the next level with Pre-Wired Raceway Systems, manufactured to your exact specifications. Reduce on site installation time by 30%.



The Hubbell SystemOne Selector Wheel makes it easy to select the SystemOne sub-plates and covers best suited to your specific application.




Hubbell's streamlined website features intuitive navigation and dynamic virtual catalogs that make accessing product and specification information fast and easy. Visit [www.hubbell-wiring.com](http://www.hubbell-wiring.com).



**Hubbell Supports the Green Initiative**



Many of Hubbell's products help save energy, support space efficiency, and reduce waste in various industrial, commercial and residential applications. The purpose of the GreenWise initiative is to demonstrate and promote how Hubbell's innovative products, and the company as a whole, do their part to safeguard the environment and support sustainable building design. Visit Hubbell's new GreenWise solutions landing page [www.hubbell-wiring.com/green](http://www.hubbell-wiring.com/green) to learn more.



**U.S. Green Building Council Member**

Hubbell is a U.S. Green Building Council (USGBC) member dedicated to advancing buildings that are environmentally responsible in the way they are designed, built and operated. USGBC drives its mission with the LEED (Leadership in Energy and Environmental Design) Green Building Rating System™. LEED is a third-party certification program, and the nationally accepted benchmark, that encourages and accelerates global adoption of sustainable green building and development practices through the creation and implementation of universally understood and accepted tools and performance criteria.

**HUBBELL®**  
Wiring Systems

[www.hubbell-wiring.com](http://www.hubbell-wiring.com)  
[www.hubbell-premise.com](http://www.hubbell-premise.com)

