





Charging solutions for every device


Eaton's combination USB chargers offer consumers the ability to charge virtually any electronic device directly from a standard outlet without bulky adapters or powered computers. This innovative line quickly and conveniently charges smart phones, tablets, e-readers, cameras, MP3 players and more.

Perfect for use in residential, commercial and healthcare applications

- Homes Lounges
- · Lounges and coffee houses
- · OEM applications

Offices
Airports

Hotels





USB charging devices



Design features

Quick and easy access for both USB charging and electrical outlets

- 3.1A charging capacity on USB duplex receptacles
- USB devices available in single and duplex configurations
- USB devices available in 15A & 20A for multiple locations
- USB duplex receptacles available in hospital grade



USB charging station

Design features

Four USB charging ports rated at 5.0 Amps total for quick and convenient charging

- Charge up to 4 devices at the same time
- Replaces a standard receptacle

USB charging devices

TR7740



TR7741

Product description

2-pole, 3-wire grounding 15A, 125V/AC, 5V DC 700MA; 15A, 125V/AC, 5V DC 2.4A; 15A, 125V/AC, 5V DC 3.1A 20A, 125V/AC, 5V DC 3.1A

Design features

- · Standard AC receptacle with two USB charging ports for conveniently charging most electronic components
- · Dual USB charging ports charge most compatible electronic devices that charge via a 5V power adapter
- Three (3) pre-stripped 6" wire leads for line, neutral and ground for quick and easy installation (excluding TR7740 and TR7741)
- Tamper resistant receptacles provide compliance with 2014 NEC® Article 406.12 which states that all 15A and 20A, 125V/AC receptacles installed in dwelling units must be tamper resistant
- · Automatic grounding system eliminates need for bonding jumper in grounded metal enclosure and provides redundant measure of ground continuity where jumper is used
- Thermoplastic top and back-body are virtually unbreakable to deliver years of durable performance
- Backwire clamps on side terminals provide for easy installation of #12 and #14 AWG wire (TR7740 and TR7741 only)
- · Triple wipe blade contacts and double wipe ground contacts to ensure long-term plug retention
- · Replaces a standard duplex receptacle and uses a decorator style wallplate



TR7755

Combination USB charger with TR receptacle





М	6
	ш
DC TA	MPE
10 RE	SIST

Ra	ating	USB	Rating				
Α	V/AC	Α	V/DC	Description	Color suffix	Catalog no.	
15	125	0.7	5	Combination USB charger with TR single receptacle	A, BK, GY, LA, V, W	□ TR7740	
15	125	2.4	5	Combination USB charger with TR single receptacle	A, B, BK, GY, LA, V, W	□ TR7741	
15	125	3.1	5	USB charger with TR duplex receptacle, wire leads	A, B, BK, GY, LA, RB, SG, V, W	□ TR7755	
20	125	3.1	5	USB charger with TR duplex receptacle, wire leads	A, B, BK, GY, LA, RB, SG, V, W	□ TR7756	
15	125	3.1	5	USB charger with hospital grade TR duplex receptacle	GY, LA, RD, V, W	□ TR8255	
20	125	3.1	5	USB charger with hospital grade TR duplex receptacle	GY, LA, RD, V, W	□ TR8355	

cULus Listed UL 498 and UL1310; NOM certified

TR7756

USB charging station

Product description

5V/DC, 5.0A Total

Design features

- USB charging ports rated at 5.0 Amps total (2.5A top two ports, 2.5A bottom two ports)
- Three (3) pre-stripped 6" wire leads for line. neutral and ground for quick and easy installation
- Automatic grounding system eliminates need for bonding jumper in grounded metal enclosure and provides redundant measure of ground continuity where jumper is used
- · Thermoplastic top and back-body are virtually unbreakable to deliver years of durable performance
- Steel mounting strap is zinc plated for added corrosion resistance
- Convenient patented built-in wire strippers speeds installation
- · Replaces a standard duplex receptacle



TR8355

7750

USB charging station





USB Rating A V/DC	Description	Color suffix	Catalog no.
5.0 5	USB multiport charging station	A, BK, GY, LA, V, W	□ 7750
UL Listed to UL1310			

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), RB (Oil Rubbed Bronze), RD (Red), SG (Silver Granite), V (Ivory), W (White).



Compliances, specifications and availability are subject to change without notice



Visit our website: www.Eaton.com/wiringdevices

Electrical Sector 203 Cooper Circle Peachtree City, GA 30269 United States Eaton.com Eaton.com/wiringdevices

Electrical Sector Canada Operations 5925 McLaughlin Road Mississauga, Ontario, L5R 1B8 Canada EatonCanada.ca Eaton.com/wiringdevices

Electrical Sector Mexico Operations Carr. Tlalnepantla Cuautitlan Km 17.8 s/n Col. Villa Jardin esq. Cerrada 8 de Mayo Cuautitlan, Mexico CP 54800 Mexico Eaton.mx Eaton.com/wiringdevices

Eaton 1000 Eaton Boulevard Cleveland, OH 44122 United States Eaton.com

© 2016 Eaton All Rights Reserved Printed in USA Publication No. BR610013EN March 2016

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

