

CAST BRONZE CLAMPS

To connect armored cable to water pipe. Zinc plated screws. Pressure bar grips armor or outer cable insulation. 360° swing hub for easy alignment.




CATALOG NUMBER	ACCOMMODATES CONDUCTOR RANGE		REFERENCE DIMENSIONS			RECOMMENDED SCREW TORQUE "INCH POUNDS"	
	WATER PIPE	ARMORED CONDUCTOR	H	L	W	PIPE CLAMP	WIRE CLAMP
C-11JA	1/2 - 1 [13 - 25]	10 - 6 Sol.	1.38 [35]	3.05 [77]	1.41 [36]	50 in.-lb.	50 in.-lb.
C-22JA	1-1/4 - 2 [32 - 51]		2.60 [66]	3.69 [94]			
C-4JA	2-1/2 - 4 [64 - 102]		4.29 [109]	5.01 [128]			

D-35

CAST BRONZE GROUND CLAMPS

For connecting grounding conductor, EMT or rigid conduit to water pipe, copper tube, ground rod or rebar. Hub swings 360° for easy alignment. Simply reverse bottom clamp for smaller size rebar or rod. Connectors are provided with Silicon Bronze hardware.



CATALOG NUMBER	ACCOMMODATES CONDUCTOR RANGE				REFERENCE DIMENSIONS			RECOMMENDED SCREW TORQUE "INCH POUNDS"
	MAIN			TAP				
	WATER PIPE	REBAR	GROUND ROD	GROUND	H	L	W	
C11HD4/ODB	1/2" - 1" [13 - 25]	#4 - #6	3/8" - 1"	#8 - 4/0 AWG	2.25	2.65	1.56	50 in.-lbs.
C22HD4/ODB	1-1/4" - 2" [32 - 51]	—	—	#8 - 4/0 AWG	2.70	3.60	1.56	50 in.-lbs.