

# Enhance



Application illustration only, subject lamps not used in photo.

## LED PAR20 lamps

For hard-to-reach downlight application fixtures, GE's dimmable 7-watt LED PAR20 lamp is the ideal solution.

### LOW-COST OPERATION

- For example, using only 7 watts of energy, save over \$236 in energy costs over the life of the lamp versus a standard 35-watt halogen lamp based on \$0.11 per kWh
- Energy efficiency and long life mean fewer lamp replacements versus standard incandescent or halogen light sources

### EXCELLENT COLOR RENDERING

- Available with a CRI of 80-83

### COLOR TEMPERATURE

- Halogen-like color
- Available in 2700K, 3000K and 5000K

### LONG LIFE

- Up to 25,000 hours rated life (L70)

### DIMMABLE

- Dims from 100% to 10%

### BEAM PATTERNS

- Available in 20° and 35° beam patterns

### ENVIRONMENTALLY CONSCIOUS

- These lamps are energy efficient and contain no lead or mercury

### GE QUALITY AND RELIABILITY

- 3-year limited warranty

ecomagination<sup>SM</sup>

To learn more about saving money and energy, go to: <http://products.currentbyge.com>.


Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

**current**  
powered by GE



# LED PAR20 lamps

## Directional Lamps (PAR)

Bulb Shape	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information	
<b>Compact PAR16</b>																		
	PAR16	MED	4	26383	LED4D/P16/NFLTP	120	3	2.8	260	720	3000	80	40W	25,000	Yes	★	Dry	Flood, 35° beam, White
			6	26384	LED6D/P16/NFLTP	120	3	2.8	380	1100	3000	80	60W	25,000	Yes	★	Dry	Flood, 35° beam, White
<b>Compact PAR20</b>																		
	PAR20	MED	7	93327	LED7DP203B830/20	120	6	3.5	520	3600	3000	80	50W	25,000	Yes	★	Damp	Narrow Flood, 20° beam, Black Casing
				93347	LED7DP203W830/20	120	6	3.5	520	3600	3000	80	50W	25,000	Yes	★	Damp	Narrow Flood, 20° beam
				93348	LED7DP203W830/35	120	6	3.5	520	1200	3000	80	50W	25,000	Yes	★	Damp	Flood, 35° beam
				93349	LED7DP203B827/20	120	6	3.5	500	3600	2700	80	50W	25,000	Yes	★	Damp	Narrow Flood, 20° beam, Black Casing
				93354	LED7DP203B827/35	120	6	3.5	500	1150	2700	80	50W	25,000	Yes	★	Damp	Flood, 35° beam, Black Casing
				93360	LED7DP203W827/20	120	6	3.5	500	3600	2700	80	50W	25,000	Yes	★	Damp	Narrow Flood, 20° beam
				93362	LED7DP203W827/35	120	6	3.5	500	1150	2700	80	50W	25,000	Yes	★	Damp	Flood, 35° beam

Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

\* The life rating is based on the hours of operation the lamp will provide before reaching 70% of its original rating (L70)

\*\* Minimum order quantity = 6

★ ENERGY STAR® status: ENERGY STAR® certified. Lamps without a "★" are not ENERGY STAR® certified.

# UL 1993 Environmental Requirements for LED LAMPS

Location, damp - Exterior or interior location that is normally or periodically subject to condensation of moisture in, on, or adjacent to, electrical equipment, and includes partially protected locations.

Location, dry - Location not normally subject to dampness, may include a location subject to temporary dampness, i.e., building under construction, provided ventilation is adequate to prevent an accumulation of moisture.

Location, wet - Location in which water or other liquid can drip, splash, or flow on or against electrical equipment.

Notes: 1) Product descriptions ending in "/TP" indicate a carded blister or clamshell package nested in a tray for shelf display. Cards also designed for hook display.



Product is compliant with material restriction requirements of RoHS

ENERGY STAR® and the ENERGY STAR® logo are registered U.S. marks

**current**  
powered by GE

<http://products.currentbyge.com>

GE and the GE Monogram are trademarks of the General Electric Company. All other trademarks are the property of their respective owners. Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions. GE Lighting and GE Lighting Solutions, LLC are businesses of the General Electric Company. © 2016 GE.

