







Features:

Polypropylene case and handle offer the maximum in impact resistance.

Round inner ring design provides a smooth, surface for winding and rewinding.



Multi-Groove Fiberglass Fish Tapes

Additional Features:

Other patents pending

- Fiberglass Performance at 25% Lower Cost!*
- Rigidity for long distance.
- Less surface contact when pushing through crowded conduit.
- Durable 7" (178 mm) steel leader helps push through crowded conduit.
- Available resin eyelet for total non-conductivity.





Old Profile

New Profile





Cat. No.	Tape Size	Reel Diameter	Weight			
Multi-Gro	Multi-Groove Fiberglass – 7" (179 mm) Spiral Leader					
56055	100' L x 3/16"W (30 m L x 4.8 mm W)	13" (330 mm)	3.03 lbs. (1.37 kg)			
56056	200' L x 3/16"W (60 m L x 4.8 mm W)	17" (432 mm)	6.16 lbs. (2.79 kg)			
Multi-Gro	ove Fiberglass – Non-Conductive					
56057	50' L x 3/16" W (15 m L x 4.8 mm W)	13" (330 mm)	2.33 lbs. (1.05 kg)			
56058	100' L x 3/16"W (30 m L x 4.8 mm W)	13" (330 mm)	3.05 lbs. (1.38 kg)			
56059	200' L x 3/16"W (60 m L x 4.8 mm W)	17" (432 mm)	6.04 lbs. (2.74 kg)			
Replacen	Replacement Parts and Kits					
56115	56115 fiberglass fish tape repair kit 2.18 lbs. (0.1 kg)					
56025	non-conductive fiberglass fish tape repair kit		.03 lbs. (0.01 kg)			
56116	replacement eyelets		.06 lbs. (0.03 kg)			
56120	replacement flexible leaders		.11 lbs. (0.05 kg)			
*When com	*When compared to published price of Klein Tools fiberglass fish tapes.					

All dimensions are in inches and (millimeters) unless otherwise specified.



118







Unique sloped handle

optimizes hand position for quick

hand-over-hand rewinds.

Raised fingergrips transfer 100% of the winding power from

Fiberglass Fish Tapes

Additional Features:

- Designed for flexibility and easy navigation through conduit runs.
- Non-conductive, fiberglass fish tape slides easily over existing wires and through multiple bends.
- Durable 7" (179 mm) steel leader helps push through crowded conduit.
- The lightweight and strong fiberglass composite tape resists harsh elements and is strength rated up to 500 pulling pounds.
- Repair kit (Cat. No. 56115) available to replace tips.
- Replacement metal eyelets (Cat. No. 56116) and spiral steel leaders (Cat. No. 56120) available.



1' permanent laser etched descending increments.



Cat. No.	Tape Size	Reel Diameter	Weight		
56009	50' L x 3/16" W (7" leader) (15 m L x 4.8 mm W)	13" (330 mm)	2.8 lbs. (1.27 kg)		
56010	100' L x 3/16" W (7" leader) (30 m L x 4.8 mm W)	13" (330 mm)	3.5 lbs. (1.59 kg)		
56014	56014 200' L x 3/16" W (7" leader) (60 m L x 4.8 mm W) 17" (432 mm)		6.2 lbs. (2.81 kg)		
Replacemen	Replacement Parts and Kits				
56115	fiberglass fish tape repair kit		2.18 lbs. (0.1 kg)		
56116	replacement eyelets		.06 lbs. (0.03 kg)		
56120	replacement flexible leaders		.11 lbs. (0.05 kg)		

Fiberglass Fish Tape Accessories

Fiberglass Fish Tape Repair Kit

- Contains high leverage ratcheting crimper, two replacement eyelets, two 7" (179 mm) replacement leaders, one tube of quick dry glue and comprehensive instructions.
- Multi-function ratcheting crimper (Cat. No. 56115V) cuts tape cleanly, strips tapes and crimps on new attachments.
- Newly crimped on eyelets meet or exceed original factory pulling strength requirements.
- Protective carry case firmly holds all tools and additional parts in handy, organized compartments.
- Cat. No. 56025 is for repairing non-conductive fiberglass fish tapes.



Cat. No.	Set Contains	Weight	
56115	high leverage crimper (1 ea.), 7° flexible leader (2 ea.), eyelets (2 ea.), tube quick-drying glue (1 ea)	2.18 lbs. (0.1 kg)	
56025	non-conductive eyelets (2 ea.), tube quick-drying glue (1 ea)	2.18 lbs. (0.1 kg)	-



56115

2-Pack 7" (179 mm) Replacement Flexible Steel Leaders & 6-Pack Replacement Eyelets

WARNING: Never remove screws while fish tape is coiled inside reel.

- For use only with fiberglass fish tapes (Cat. No. 56009, 56010 & 56014).
- Attach with Klein Tools ratcheting crimper (Cat. No. 56115V) available in kit 56115 only.



Cat. No.	Length	Weight
56120	8.94" (227 mm)	.11 lbs. (0.05 kg)
56116	1.5" (38 mm)	.06 lbs. (0.03 kg)



All dimensions are in inches and (millimeters) unless otherwise specified.







Spiral Steel Fish Tapes

Additional Features:

- Designed for super flexibility and easy navigation through conduit runs.
- Slides easily over existing wires and through multiple bends.
- The durable spiral steel tape construction yields a maximum pulling force of up to 500 lbs.
- Replacement metal eyelets (Cat. No. 56116) and spiral steel leaders (Cat. No. 56120) available.

Cat. No.	Tape Size	Reel Diameter	Weight	
56013	50' L x 3/16" W (15 m L x 4.8 mm W)	13" (330 mm)	5.1 lbs. (2.31 kg)	
Replacement Parts				
56116	1.5" (38 mm)	-	.06 lbs. (0.03 kg)	



1/8" (3 mm) Wide Steel Fish Tapes

Additional Features:

 High strength spring steel fish tapes are stiff for long runs and are great for heavy duty wire pulls.

• Full grip style handle gives you a firm, steady grip as you pull tape from the case.

Stainless Steel fish tape (Cat. Nos. 56007, 56008) is corrosion resistant and extends the life of the tool.



1' permanent laser etched descending increments.







56002	56
-------	----

Cat. No.	Tape Size	Reel Diameter	Weight			
Stainless S	Stainless Steel for Corrosion Resistance					
56007	125' L x 1/8" W x .062" H (38 m L x 3 mm W x 1.5 mm H)	13" (330 mm)	4.7 lbs. (2.13 kg)			
56008	240' L x 1/8" W x .062" H (73 m L x 3 mm W x 1.5 mm H)	13" (330 mm)	7.5 lbs. (3.40 kg)			
Flat Steel						
56000	25' L x 1/8" W x .045" H (7 m L x 3 mm W x 1.1 mm H)	7" (178 mm)	1.0 lbs. (0.45 kg)			
56001	50' L x 1/8" W x .045" H (15 m L x 3 mm W x 1.1 mm H)	7" (178 mm)	1.3 lbs. (0.59 kg)			
56002	65' L x 1/8" W x .062" H (19 m L x 3 mm W x 1.5 mm H)	9" (229 mm)	2.6 lbs. (1.18 kg)			
56003	125' L x 1/8" W x .062" H (38 m L x 3 mm W x 1.5 mm H)	13" (330 mm)	4.7 lbs. (2.13 kg)			
56004	240' L x 1/8" W x .062" H (73 m L x 3 mm W x 1.5 mm H)	13" (330 mm)	7.5 lbs. (3.40 kg)			
Replaceme	nt Tapes					
56065	65' L x 1/8" W x .062" H (19 m L x 3 mm W x 1.5 mm H)	-	1.7 lbs. (0.77 kg)			
56125	125' L x 1/8" W x .062" H (38 m L x 3 mm W x 1.5 mm H)	-	3.3 lbs. (1.50 kg)			
56240	240' L x 1/8" W x .062" H (73 m L x 3 mm W x 1.5 mm H)	_	6.1 lbs. (2.77 kg)			

56001

1/4" (6 mm) Wide Steel Fish Tapes

Additional Features:

- Tempered, high quality tape keeps its stability as it glides between surfaces for effective pushing and pulling of wire under carpets, through insulated walls and over suspended ceilings.
- 25' length with no snag tip, is perfect for short wire runs associated with light commercial, residential and voice-data-video-audio installations (Cat. No. 56005).



56005 has a no snag plastic tip



1' permanent laser etched descending increments.



56005

Cat. No.	Tape Size	Reel Diameter	Weight
56005	25' L x 1/4" W x .030" H (7 m L x 6.3 mm W x .7 mm H)	7" (178 mm)	1.1 lbs. (0.50 kg)
56006	100' L x 1/4" W x .062" H (30 m L x 6.3 mm W x 1.5 mm H)	13" (330 mm)	6.8 lbs. (3.08 kg)

All dimensions are in inches and (millimeters) unless otherwise specified.









13" (330 mm) Flexible Leader for Steel Fish Tapes



- For use with 1/8" (3 mm) wide steel fish tapes.
- Heavy duty construction is strength rated up to 500 pulling pounds.
- High capacity eyelet holds up to five #12 unstripped wires and seven #10 bare wires.
- Retrofit instructions included.
- The 3/16" (5 mm) diameter tape has a rustproof inner steel cable core wrapped with a spiral cover for exceptional flexibility.
- Flexible leader guides steel tapes through 90° bends and makes pulling and pushing flat steel tapes easier.

Cat. No.	Length	Diameter	Weight
50350	13-1/2" (343 mm)	3/16" (5 mm)	.10 lbs. (0.04 kg)

6 Loop Wire Pulling Leader



- Save time by attaching leader to the end of a fish tape and pull up to six wires at once.
- Braided steel construction provides up to 450 lbs. pull strength on main eyelet.
- Flexible construction allows for easy navigation through multiple bends in conduit.
- Staggered loop lengths won't overlap and clog pipe.
- For use with 1/8" and 1/4" (3 mm and 6 mm) flat steel fish tapes.

Cat. No.	Length	Weight	
56107	11-1/4" (285 mm)	.2 lbs. (0.09 kg)	

Steel Fish Tape Swivel Eyelet

- For use with 1/8" (3 mm) wide steel fish tapes.
- Swivel head design helps prevent kinks and allows smoother, easier fishing in tight turns.
- High capacity eyelet holds up to five #12 unstripped wires or seven #10 bare wires.
- High strength steel construction allows for optimal performance over repeated uses.
- Retrofit instructions included.

Cat. No.	Length	Diameter	Weight
50351	1-1/2" (38 mm)	3/16" (5 mm)	.03 lbs. (0.01 kg)



50351

50350





Fish Rods & Accessories

Features: **Exclusive Splinter Guard™ protection** from painful fiberglass splinters Rods have threaded beveled connectors to attach to desired length and prevent snagging on obstructions.

LO flex – long, straight feeding; HIGH flex - tight bends in walls; MID flex – all needs in between.

Luminescent glow rods provide added visibility in dark work spaces.

Shines 2X brighter and lasts 2X longer than ordinary glow rods.



56326

Fish and Glow Rods

Additional Features:

- Variety of flexibilities and lengths for any application such as walls, drop ceilings, attics, crawl spaces, etc.
- Sets include bull nose and hook attachments to attach and grab wires.



Cat. No	. Description	Set Contains	Overall Length	Diameter	Weight
Fish Ro	Fish Rods				
56312	12' (3.7 m) Lo-Flex Set	(3) 1/4" (6 mm) diameter 4' (1.2 m) fish rods with bullet nose and hook attachments	12' (3.7 m)	1/4" (6.4 mm)	1.05 lbs. (0.48 kg)
56324	24' (7.3 m) Lo-Flex Set	(4) 1/4" diameter 6' (1.5 m) fish rods with bullet nose and hook attachments	24' (7.3 m)	1/4" (6.4 mm)	1.85 lbs. (0.84 kg)
56325	25' (7.6 m) Fish and Glow Set	(5) 1/4" diameter 4' (1.2 m) fish rods, (1) 3/16" (5 mm) diameter 5' (1.3 m) glow rod with bullet nose and hook attachments	25' (7.6 m)	1/4" and 3/16" (6.4 and 5 mm)	1.8 lbs. (0.82 kg)
Glow R	ods				
56406	6' Hi-Flex Rod	N/A	6' (1.8 m)	5/32" (3 mm)	0.2 lbs. (0.18 kg)
56409	9' (2.7 m) Mid-Flex Set	(6) 3/16" (5 mm) diameter 18" (457 mm) glow rods with bullet nose and hook attachments	9' (2.7 m)	3/16" (5 mm)	0.55 lbs. (0.25 kg)
56415	15' (4.6 m) Mid-Flex Set	(3) 3/16" (5 mm) diameter 5' (1.5 m) glow rods with bullet nose and hook attachments	15' (4.6 m)	3/16" (5 mm)	0.85 lbs. (0.39 kg)
56418	18' (5.5 m) Hi-Flex Set	(3) 5/32" (3 mm) diameter 6' (1.8 m) glow rods with bullet nose and hook attachments	18' (5.5 m)	5/32" (3mm)	0.85 lbs. (0.39 kg)



Additional Features:

- Heavy-duty storage case with fitted pockets and straps for organization.
- · Large handles fit over the shoulder for easy transport. Convenient zipper pocket for accessory storage.

Cat. No.	Description	Overall Length	Weight
56326	(2) 1/4" (6 mm) Dia. 6' (1.5 m) and (2) 1/4 (6 mm) Dia. 4' (1 m) Low Flex Fish Rods, (3) 3/16" (5 mm) Dia 5' (1.3 m)	75" (1,905 mm)	3.75 lbs.
	Míd-flex Glow Rods, (3) 5/32" (4 mm) Dia 6' (1.5 m) Hi-Flex Glów Rods, (1) hook and (1) bullet nose and custom zippered carrying case		(60 oz.)

Illuminated Fish Rod Tip

- Lights up for maximum visibility in dark spaces.
- Bright white, omni-directional LED light for long life.
- Threaded top for hook or bullet nose attachment (not included).
- Fits drilled holes as small as 5/8" (16 mm).
- Compatible with Lo, Mid and High flex rods.
- Replaceable batteries included.



56119

Cat. No.	Description	Dimensions	Weight
56119	illuminated fish rod tip	2.5" L (64 mm) x 9/16" (14 mm) diameter	5.0 oz. (142 g)

Fish Rod Accessories

- Attachments help guide, grab, attach and steer wire or cable.
- Compatible with Lo. Mid and High flex rods.



Cat. No.	Description	Set Contains	Weight
56104	3-piece fish and glow rod attachment set	(1 ea.) whisk attachment (1 ea.) bullet nose attachment (1 ea.) hook attachment	.2 oz. (5.7 g)

All dimensions are in inches and (millimeters) unless otherwise specified.





Wire Pulling Tools

WireSpanner TM – Telescopic Pole 18'





Extends to 18' (5.4 m) in 10 seconds!

SRS56036

- Easily retrieve cable from a distance without needing an extra pair of hands to shorten installation time.
- Large hook attachment pulls multiple wires easily.
- Friction-twist lock pole design stays locked in place.
- Lightweight resin slides easily over obstructions.
- Compact design retracts to 32" (813 mm) for easy storage.

Cat. No.	Compact Length	Extended Length	Weight
SRS56036	32" (813 mm)	18' (5.4 m)	2.75 lbs. (1.25 kg)

Polymer Fish Rod Set with Glow-in-the-Dark Leaders





- Non-conductive rods designed for working in confined spaces.
- Great for routing cables in wire racks and on short runs.
- Attachments glow in the dark for ease of use.
- Includes 14" (356 mm) rods of various flexibilities and illumination for a range of individual (or 56" (1.4 m) combined) wire pulling applications.
- Includes five Glow-in-the-Dark leaders (hook, bullet, mini-eyelet, domed-eyelet and Claw).
- Convenient storage tube protects the rods between use and fits easily into your bag or toolbox.



5 Attachments Included



Bullet







SRS56038

Cat. No.	Extended Length	Weight
SRS56038	56" (1.4 m)	.25 lbs. (0.11 kg)

Magnetic Wire Pulling System





- This system allows you to effortlessly pull cable behind walls by yourself.
- Navigates through insulation and other obstructions.
- Perfect for routing cable between drywall and insulation or fixture installations.
- Swivel leader eyelet securely connects to most wires and mesh wire pulling grips.
- Non-marring nylon leader-pull with 20' (6.1 m) of heavy-duty nylon rope eyelet for wire tie-on.





SRS56037

Cat. No.	Rope Length	Weight
SRS56037	20' (6.1 m)	.40 (0.18 kg)

Wire Pulling Lubricant

Wire Pulling Foam Lubricant

- NO DRIPS! NO STAINS! NO MESS!
- One can equals one gallon or 4 quarts of wax/gel lubricants*
- Foam lubricant is applied directly into the conduit. No need to pre-coat wires.
- No-mess formula stays where it is applied, even in vertical conduit!
- Dissolves clean from hands and clothing



Based on job site pulls with foam in 3/4" conduit when used as directed.





↑WARNING

- · Contents under pressure. Do not expose container to direct sunlight or temperatures above 120°F. Do not transport or store near heat sources. Keep cans dry and away from sources of ignition. If frozen, gradually warm to room temperature.
- Do not use wet product on live circuits. Compound is electrically conductive before it dries.

All dimensions are in inches and (millimeters) unless otherwise specified.













Wire Pulling Lubricant

One-Quart Premium Synthetic Clear™

- Designed for use primarily in finished workspaces (i.e. around painted walls and carpeted floors).
- The crystal clear formulation is easy to clean-up and will not stain.
- Excellent all purpose lubricant for electrical or datacom applications.
- Compatible with most types of cable jackets.
- Will not separate out in hot environments for when exposed to freezing temperatures.

Cat. No.	Container	Temperature Use Range	Weight
51028	one-quart squeeze bottle	20° F to 120° F (-5° C to 50° C)	2.3 lbs. (1.04 kg)





51028

Premium Synthetic Wax™

- High performance lubricant for general electrical and utility applications.
- Temperature stable and does not liquify and drop off after high temperature exposure.
- Compatible with most types of cable, including low density polyethylene.
- Superior "clingability" coats wires and conduit evenly.
- Exceptional lubricity.
- Non-staining, slow-drying, easy clean-up formula.

Cat. No.	Container	Temperature Use Range	Weight
51010	one-quart squeeze bottle	20° F to 122° F (-6° C to 50° C)	2.3 lbs. (1.0 kg)
51012	one-gallon pail	20° F to 122° F (-6° C to 50° C)	8.8 lbs. (3.9 kg)
51013	five-gallon pail	20° F to 122° F (-6° C to 50° C)	44 lbs. (19.9 kg)
56117	one-quart squeeze bottle - 6 pack	20° F to 122° F (-6° C to 50° C)	13.5 lbs. (6.12 kg)







- Excellent all-purpose lubricant for electrical, telecommunications and data applications.
- Easy-to-apply gel evenly clings instantly to the cable for easy handling and application.
- Compatible with most types of cable, including polyethylene and semi conducting jackets.
- · Superior "clingability" coats wires and conduit evenly.
- Non-staining, slow-drying, easy clean-up formula.

Cat. No.	Container	Temperature Use Range	Weight (lbs.)
51015	one-quart squeeze bottle	20° F to 140° F (-6° C to 60° C)	2.3 lbs. (1.1 kg)
51017	one-gallon pail	20° F to 140° F (-6° C to 60° C)	8.8 lbs. (3.9 kg)
51018	five-gallon pail	20° F to 140° F (-6° C to 60° C)	44 lbs. (19.9 kg)





51015

51017





CERTIFIED TO CSA



All dimensions are in inches and (millimeters) unless otherwise specified.

Wire Pulling Supplies

Poly Pull Line

- Use polypropylene line with manual or power fishing systems for light duty cable or rope pulling applications.
- Ready to use storage containers guickly dispense a tangle free line and also protects line from direct sunlight.
- Line is resistant to rot and mildew.
- Up to 210 lbs. average breaking strength.

Cat. No.	Description	Container Type	Weight
56108	500' (152 m) poly pull line with orange tracer	one-quart size w/locking lid	1 lbs. (0.45 kg)
56110	6500' (1981 m) poly pull line with orange tracer	five-gallon bucket	11 lbs. (4.9 kg)



Conduit Tools

Side-Cutting Pliers – Fish Tape Pulling

- Quickly and easily pulls 1/8" or 1/4" (3 mm or 6 mm) flat-steel fish tape without damaging the tape.
- High leverage design. Rivet is closer to the cutting edge for greater cutting and gripping power than other plier designs.
- Streamlined design with sure-gripping, cross-hatched knurled jaws.



Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Handle Finish	Handle Color	Weight
D213-9NETP	New England	9-3/8" (238 mm)	1-19/32" (41 mm)	1-1/14" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	plastic-dipped	dark blue	1.1 lbs. (0.5 kg)
Journeyman™	Series – Du	al-material hand	dles						
J213-9NETP	New England	9-1/2" (241 mm)	1-19/32" (41 mm)	1-1/14" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	Journeyman	dark blue/black	1.1 lbs. (0.5 kg)
2000 Series*	- Heavy-duty	y cutting knives	į.						
D2000-9NETP	New England	9-3/8" (238 mm)	1-19/32" (41 mm)	1-1/14" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	plastic-dipped	royal blue	1.1 lbs. (0.5 kg)
Journeyman™	2000 Series	s* – Dual-materi	ial handles						
J2000-9NETP	New England	9-1/2" (241 mm)	1-19/32" (41 mm)	1-1/14" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	Journeyman	light blue/black	1.1 lbs. (0.5 kg)
J2000-9NECRTP	New England	9-1/2" (241 mm)	1-19/32" (41 mm)	1-1/14" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	Journeyman	blue/black	1.1 lbs. (0.5 kg)
*Cute ACCD co	rowe naile ar	d most hardened	wire Features com	hingtion poliched	and black oxide fir	aich			

Cuts ACSR, screws, nails, and most hardened wire. Features combination polished and black-oxide finish.

Conduit Locknut Wrench

- Easily attach locknuts in tight or deep cut-in boxes.
- For 1/2" and 3/4" connectors.
- Direct-drive heads rotate each other when twisted.
- Heavy-duty steel construction enables needed torque to loosen or tighten connectors.
- · Perfect for remodel work where box is filled with existing wires.







US Patent pending

Cat. No.	Fitting Size	Overall Length	Weight
56999	1/2" and 3/4"	9" (228 mm)	70 lbs. (0.32 kg)

Conduit Pliers – Locknut and Reaming

- Tightens 1/2" (13 mm) and 3/4" (19 mm) EMT or 1/2" (13 mm) rigid locknuts.
- Fits liquid tight fittings and caps.
- · Reams and smooths both inside and outside of conduit.
- Knurled jaws at nose tip pull wire or fish tape.
- Machined nose fits snugly into locknut wings.



D333-8

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Point Thickness	Handle Finish	Handle Color	Weight
D333-8	7-3/4" (197 mm)	1-5/8" (41 mm)	15/16" (24 mm)	1/2" (13 mm)	3/16" (4.8 mm)	plastic-dipped	yellow	.55 lbs. (0.25 kg)

All dimensions are in inches and (millimeters) unless otherwise specified.





Conduit Tools

Conduit-Fitting and Reaming Screwdriver

- Hooded-blade design keeps tip from slipping out of screws, especially when tightening hard-to-reach conduit fittings. Thicker hood is designed for rugged use.
- Reams and smooths 1/2" (13 mm), 3/4" (19 mm), and 1" (25 mm) thin-wall conduit ends to protect wire and permit correct installation of fittings.
- Reams both the inside and outside of the conduit at the same time.
- Longer Cushion-Grip handle provides comfort and more torque for reaming.

Cat. No.	Shank Tip Width	Shank Length	Overall Length	Weight
85191	3/8" (10 mm)	2-1/2" (64 mm)	7-1/2" (191 mm)	.55 lbs. (0.25 kg)
19353	conduit reamer replacement blade kit			.01 lbs. (0.004 kg)



85191

Use Cat. No. 85091 Power Conduit Reamer to reduce time on projects with large quantities of conduit runs.

Conduit Benders

Features:




Aluminum Conduit Benders

Additional Features:

Lightweight die-cast aluminum construction.

Cat. No.	Description:	Thinwall/EMT	Rigid/IMC	Radius	Weight
56206	assembled aluminum conduit bender with #51427 handle	1/2" (13 mm)	-	4"	4.4 lbs. (2.00 kg)
56207	assembled aluminum conduit bender with #51427 handle	3/4" (19 mm)	1/2" (13 mm)	5"	5.4 lbs. (2.45 kg)









Conduit Benders

Iron Conduit Benders

Additional Features:

- High strength steel handle features a swaged end for inserting conduit to correct overbends (Cat. Nos. 56203 & 56204 only).
- Bright orange color handle is easy to spot on the jobsite.

Cat. No.	Description:	Thinwall/EMT	Rigid/IMC	Weight
56208	conduit bender head	1/2" (13 mm)	-	2.1 lbs. (0.95 kg)
56209	conduit bender head	3/4" (19 mm)	1/2" (13 mm)	3.2 lbs. (1.45 kg)
56210	conduit bender head	1" (25 mm)	3/4" (19 mm)	5.5 lbs. (2.49 kg)
56211	conduit bender head	1- 1/4" (32 mm)	1" (25 mm)	16.9 lbs. (7.67 kg)
56203	assembled conduit bender w/#51427 handle	1/2" (13 mm)	-	5.5 lbs. (2.49 kg)
56204	assembled conduit bender w/#51427 handle	3/4" (19 mm)	1/2" (13 mm)	6.6 lbs. (2.99 kg)
56205	assembled conduit bender w/#51428 handle	1" (25 mm)	3/4" (19 mm)	11.6 lbs. (5.26 kg)



56211

Conduit Bender Handles

Bender Handles



51427

- Available in multiple sizes and lengths and are compatible with all Klein Tools conduit bender heads.
- High-strength steel eliminates flex and provides excellent feel, control and leverage.
- Handle features an enlarged diameter hollow end for inserting conduit to correct overbends (Cat. No. 51427).
- · Bright orange color is easy to spot on the jobsite.

Cat. No.	Description:	Weight
51427	conduit bender handle - 38" L, 3/4" NPT tap size fits 1/2" and 3/4" bender heads and is replacement handle for #56208 and #56209.	3.5 lbs. (1.6 kg)
51428	conduit bender handle - 44" L, 1" NPT tap size fits 1" bender head for #56210.	6.0 lbs. (2.7 kg)
51429	conduit bender handle - 54" L, 1-1/4" NPT tap size fits 1-1/4" bender head for #56211.	8.9 lbs. (4.0 kg)

Armored Cable Cutter

BX and Armored Cable Cutter

- Cuts BX and 3/8" armored cable.
- Eliminates burrs.
- Does not nick cable.
- Easily cuts 3/8" flexible conduit and #10, 12, and 14 armored cables with up to 4 wires with a couple of turns of the handle.
- Depth of cut adjusts between standard MC and reduced diameter MC.
- Extra blade storage in handle.
- Use with Klein Tools replacement blade Cat. No. 53726-SEN.

Cat. No.	Length	Weight				
53725	7-1/4" (184 mm)	2.0 lbs. (0.9 kg)				
Replacement Parts						
53726-SEN	Replacement blade for use with Klein Tools cable	0.1 lbs. (0.04 kg)				









Conduit Scoring Tool

Electrician's Conduit Scoring Tool

- Durable zinc cast scoring tool eliminates spiraling.
- Used for scoring 1/2", 3/4" and 1"EMT conduit.
- Klein-designed, patented scoring wheel scores and allows clean conduit snaps without leaving burrs inside.
- 1" scoring wheel conveniently located in base of the handle; no tools required to replace scoring wheels.
- Four roller tracks specifically designed for professional use.
- Compact, enclosed design for use on job sites.

IIS Patent: D638451

			•• • • • • • • • • • • • • • • • • • •
Cat. No.	Length	Conduit Diameter	Weight
88906	6.02" (153mm)	scores 1/2", 3/4" and 1" EMT conduit	1.25 lbs. (0.6 kg)
Replacen	nent Parts		
88907		1/2" and 3/4" EMT replacement scoring wheel	
88908		1" EMT replacement scoring wheel	





PVC-Cutters

PVC-Cutter

- Cuts up to 3/4" schedule 40 PVC.
- Makes clean burr-free cuts in PVC and flexible pipe.
- Reversible blade doubles life.
- Cuts 1-3/8" outer diameter flexible plastic pipe.
- Steel construction for strength.
- Guide helps cut pipe squarely.
- Handle latch keeps tool closed.

Trandic later keeps tool closed.						
Cat. No.	PVC Cutting Capacity	Non-metallic Tubing Cutting Capacity	Length	Weight		
50506-SEN	3/4" (19 mm) schedule 40	1" (19 mm)	8-1/2" (215 mm)	1.0 lbs.(0.45 kg)		
Replacem	ent Parts					
50549	replacement blade		3-1/4" (83 mm)	.08 lbs. (0.03 kg)		





Ratcheting PVC-Cutters

- Provide straight cuts 1/2"-2" I.D. (13 mm-51 mm)
 0.D. 5/8" 2-1/2" (16 mm-64 mm) of white and gray schedule 40 and 80 PVC.
- Quick, one-handed blade release.
- Ratchet action allows easy, one-hand cutting.
- No tools required for instant blade change.
- Replacement blade and pin available.

		X		
				50031
ight		The same		
lbs. (0.5 kg)	AT'S			
lbs. (0.6 kg)	Robbit		•	
lbs. (0.08 kg)		- A - A - A - A - A - A - A - A - A - A	-	1000
lbs. (0.08 kg)	_			
C II (0 000 I)				

50032

	50031	O.D. 5/8" 1-5/8" (16 mm-41 mm) I.D. 1/2"— 1-1/4" (13 mm-32 mm)	9" (229 mm)	1.1 lbs. (0.5 kg)		
	50034	O.D. 5/8" 2-1/2" (16 mm-64 mm) I.D. 1/2"— 2" (13 mm-51 mm)	11" (280 mm)	1.3 lbs. (0.6 kg)		
Replacement Parts						
	50032	replacement blade for 50031	4" (102 mm)	.19 lbs. (0.08 kg)		
	50035	replacement blade for 50034	4" (102 mm)	.19 lbs. (0.08 kg)		
	50033	replacement pin for 50031 & 50034	2-3/8" (60 mm)	.006 lbs. (0.002 kg)		

Cat. No. PVC Cutting Capacity Length Wei

⚠WARNING: Do NOT cut cold PVC.

⚠WARNING: Do NOT use to cut metallic pipes, cable or wire.



All dimensions are in inches and (millimeters) unless otherwise specified.