

## LED OMNIDIRECTIONAL A-LAMP

### A19, A21 SERIES



6W, 9W, 11W  
A19



15W  
A21



6W, 9W, 11W  
A19-GU24



15W  
A21-GU24



### PRODUCT DESCRIPTION:

MaxLite's versatile, ENERGY STAR®-certified LED Omnidirectional A-Line lamps replicate true A19 and A21 incandescents with a 300-degree beam angle that produces even light in all directions. They are suited to a wide variety of residential and commercial applications, including chandeliers, pendants, wall sconces and table and floor lamps. The 6-, 9-, 11- and 15-watt lamps replace 40-, 60-, 75- and 100-watt incandescent bulbs, respectively, and yield more than 85 percent savings in energy. LED Omnidirectional A-Line lamps are dimmable down to 10 percent on a wide variety of dimming control systems. They are offered in a standard medium base, which enables convenient screw-in, as well as GU24-base installation into existing lamps and fixtures that are used for both residential and commercial applications.

### FEATURES:

- 25,000 hour life (L70 standards)
- CRI: ≥ 82
- Dimmable down to 10 percent
- Saves more than 80 percent on energy
- Power factor: > 0.9
- Standard E26 base & GU24 base
- Five year limited warranty

### APPLICATIONS

- Pendants
- Table and floor lamps
- Sconces
- Not for use in fully enclosed luminaires
- Suitable for use in damp locations

### COMPATIBLE DIMMERS:

MAKE	DIMMER MODEL
Lutron	CTCL-153P
Lutron	DVCL-153P
Lutron	LGCL-153P
Lutron	S-600

MAKE	DIMMER MODEL
Leviton	IPL06
Leviton	IP110
Leviton	6631-LW
Leviton	6683-IW

**SPECIFICATIONS:**

		6A19	9A19	9.5A19	11A19	15A21
ITEM	SPECIFICATION	DETAILS				
GENERAL PERFORMANCE	Power Consumption	6W	9W	9.5W	11W	15W
	Lumens Delivered	470	800	800	1100	1600
	Efficacy (lm/w)	78	89	84	100	107
	CRI	82	82	91	82	82
	Color Temperature (CCT)	2700K, 3000K, 4000K				
	Lumen Maintenance (L70)	25,000 Hours				
ELECTRICAL	Power Factor	≥0.9				
	Input Voltage	120V				
PHYSICAL	Base Type	E26, GU24				
	Operating Temperature	-4°F - 104°F				
CERTIFICATION	Environment	Dry, Damp				
	Warranty	5 Year Limited				

Lighting layouts and spacing criteria available upon request



# LED OMNIDIRECTIONAL A-LAMP

## A19, A21 SERIES

### ORDERING:

ORDER CODE	MODEL	WATTS	EQUIVALENCY	OUTPUT (LUMENS)	EFFICACY (LM/W)	CRI	DIMENSIONS (D" x L")	CCT
<b>E26 Base</b>								
76850	6A19DLED27/G2*	6	40W Inc.	470	78	82	2.50" x 4.54"	2700K
76851	6A19DLED30/G2*	6	40W Inc.	470	78	82	2.50" x 4.54"	3000K
76852	6A19DLED40/G2	6	40W Inc.	470	78	82	2.50" x 4.54"	4000K
74976	9A19DLED27*	9	60W Inc.	800	89	82	2.50" x 4.54"	2700K
74981	9A19DLED30*	9	60W Inc.	800	89	82	2.50" x 4.54"	3000K
76849	9A19DLED40*	9	60W Inc.	800	89	82	2.50" x 4.54"	4000K
76853	11A19DLED27/G2*	11	75W Inc.	1100	100	82	2.50" x 4.54"	2700K
76854	11A19DLED30/G2*	11	75W Inc.	1100	100	82	2.50" x 4.54"	3000K
76855	11A19DLED40/G2*	11	75W Inc.	1100	100	82	2.50" x 4.54"	4000K
76856	15A21DLED27/G2*	15	100W Inc.	1600	107	82	2.82" x 5.25"	2700K
76857	15A21DLED30/G2*	15	100W Inc.	1600	107	82	2.82" x 5.25"	3000K
76858	15A21DLED40/G2*	15	100W Inc.	1600	107	82	2.82" x 5.25"	4000K
<b>E26 Base 90+ CRI</b>								
76877	9.5A19DLED927/G2*	9.5	60W Inc.	800	84	91	2.50" x 4.54"	2700K
76859	9.5A19DLED930/G2*	9.5	60W Inc.	800	84	91	2.50" x 4.54"	3000K
<b>GU24 Base</b>								
77074	6A19GUDLED27/G2*	6	40W Inc.	470	78	82	2.50" x 4.40"	2700K
77075	6A19GUDLED30/G2*	6	40W Inc.	470	78	82	2.50" x 4.40"	3000K
77076	6A19GUDLED40/G2	6	40W Inc.	470	78	82	2.50" x 4.40"	4000K
77077	9A19GUDLED27/G2*	9	60W Inc.	800	89	82	2.50" x 4.40"	2700K
77078	9A19GUDLED30/G2*	9	60W Inc.	800	89	82	2.50" x 4.40"	3000K
77079	9A19GUDLED40/G2*	9	60W Inc.	800	89	82	2.50" x 4.40"	4000K
77080	11A19GUDLED27/G2*	11	75W Inc.	1100	100	82	2.50" x 4.40"	2700K
77081	11A19GUDLED30/G2*	11	75W Inc.	1100	100	82	2.50" x 4.40"	3000K
77082	11A19GUDLED40/G2*	11	75W Inc.	1100	100	82	2.50" x 4.40"	4000K
77083	15A21GUDLED27/G2*	15	100W Inc.	1600	107	82	2.82" x 5.25"	2700K
77084	15A21GUDLED30/G2*	15	100W Inc.	1600	107	82	2.82" x 5.25"	3000K
77085	15A21GUDLED40/G2*	15	100W Inc.	1600	107	82	2.82" x 5.25"	4000K

\*ENERGY STAR certified

