

Round Head Slotted Machine Screws Stainless Steel - PC 4010



- Machine Screws
- Round Head
- Slotted
- 18-8 Stainless Steel
- Invincibox™ Up To 2"

Stainless steel round head machine screws project above the material surface. This head style is used when clearance is not an important factor. Length is determined from the base of the fastener head. Stainless steel resists corrosion and is ideal for applications where chemical resistance is required.

CAT NO	UPC	SIZE	STD	SLEEVE	MSTR	WT/STD	UNIT
RMS63238	70104	6-32 x 3/8	100	500	4000	0.19#	C
RMS63212	70106	6-32 x 1/2	100	500	4000	0.22#	C
RMS63234	70108	6-32 x 3/4	100	500	4000	0.30#	C
RMS6321	70110	6-32 x 1	100	500	4000	0.37#	C
RMS632114	70112	6-32 x 1-1/4	100	500	4000	0.43#	C
RMS632112	70114	6-32 x 1-1/2	100	500	4000	0.51#	C
RMS6322	70116	6-32 x 2	100	500	3000	0.67#	C
RMS83238	70120	8-32 x 3/8	100	500	4000	0.30#	C
RMS83212	70122	8-32 x 1/2	100	500	4000	0.35#	C
RMS83234	70124	8-32 x 3/4	100	500	4000	0.46#	C
RMS8321	70126	8-32 x 1	100	500	4000	0.56#	C
RMS832114	70128	8-32 x 1-1/4	100	500	4000	0.67#	C
RMS832112	70130	8-32 x 1-1/2	100	500	3000	0.77#	C
RMS8322	70132	8-32 x 2	100	500	3000	1.01#	C
RMS102438	70140	10-24 x 3/8	100	500	4000	0.41#	C
RMS102412	70142	10-24 x 1/2	100	500	4000	0.49#	C
RMS102434	70144	10-24 x 3/4	100	500	4000	0.62#	C
RMS10241	70146	10-24 x 1	100	500	4000	0.75#	C
RMS103238	70160	10-32 x 3/8	100	500	4000	0.41#	C
RMS103212	70162	10-32 x 1/2	100	500	4000	0.49#	C
RMS103234	70164	10-32 x 3/4	100	500	4000	0.62#	C
RMS10321	70168	10-32 x 1	100	500	4000	0.75#	C
RMS1438	70180	1/4 x 3/8	100	500	4000	0.84#	C
RMS1412	70182	1/4 x 1/2	100	500	4000	0.97#	C
RMS1434	70184	1/4 x 3/4	100	500	3000	1.19#	C
RMS141	70186	1/4 x 1	100	500	3000	1.45#	C
RMS14114	70188	1/4 x 1-1/4	100	500	3000	1.69#	C
RMS14112	70190	1/4 x 1-1/2	50	250	1500	0.99#	C
RMS142	70192	1/4 x 2	50	250	1500	1.21#	C

Round Head Slotted Machine Screws Solid Brass - PC 4270



- Machine Screws
- Round Head
- Slotted
- Solid Brass
- Invincibox™ Up To 2"

Brass round head machine screws project above the material surface. This head style is used when clearance is not an important factor. Length is determined from the base of the fastener head. Brass has good corrosion and rust resistance, especially in salt water and salt air. It is non magnetic.

CAT NO	UPC	SIZE	STD	SLEEVE	MSTR	WT/STD	UNIT
RMB63212	55500	6-32 x 1/2	100	500	4000	0.22#	C
RMB63234	55502	6-32 x 3/4	100	500	4000	0.30#	C
RMB6321	55504	6-32 x 1	100	500	4000	0.37#	C
RMB632114	55506	6-32 x 1-1/4	100	500	4000	0.43#	C
RMB632112	55508	6-32 x 1-1/2	100	500	4000	0.51#	C
RMB6322	55510	6-32 x 2	100	500	3000	0.67#	C
RMB83212	55550	8-32 x 1/2	100	500	4000	0.35#	C
RMB83234	55552	8-32 x 3/4	100	500	4000	0.46#	C
RMB8321	55554	8-32 x 1	100	500	4000	0.56#	C
RMB832114	55556	8-32 x 1-1/4	100	500	4000	0.67#	C
RMB832112	55558	8-32 x 1-1/2	100	500	3000	0.77#	C
RMB8322	55560	8-32 x 2	100	500	3000	1.01#	C
RMB1412	55700	1/4 x 1/2	100	500	4000	0.97#	C
RMB1434	55702	1/4 x 3/4	100	500	3000	1.19#	C
RMB141	55704	1/4 x 1	100	500	3000	1.45#	C
RMB14114	55706	1/4 x 1-1/4	100	500	3000	1.69#	C
RMB14112	55708	1/4 x 1-1/2	50	250	1500	0.99#	C
RMB142	55710	1/4 x 2	50	250	1500	1.21#	C

* RMB10-24 and 10-32 available upon request.

See new products at lhdottie.com

Dottie

