



M400-UG-APS-LC  
(see next page for dwg. & chart)



U3251-O-200-CB

4 TERMINAL—1Ø3W—TYPE 3R—RING TYPE PLUG-IN SOCKETS—120/240 VAC

SERV	CATALOG NUMBER	PRIMARY DISCONNECT	SECONDARY DISCONNECT	BY-PASS	DIMENSIONS			CONCENTRIC K.O.'S					FIG.
					D"	W"	H"	1	2	3	4	5	
UG	M400-UG-APS-F ①	200 Amp / 2 Pole Circuit Breaker	See note ①	NONE	6 <sup>1</sup> / <sub>8</sub>	22 <sup>1</sup> / <sub>8</sub>	36	2 <sup>1</sup> / <sub>2</sub>	2 <sup>1</sup> / <sub>2</sub>	4	2 <sup>1</sup> / <sub>2</sub>	1 <sup>1</sup> / <sub>2</sub> , 3 <sup>3</sup> / <sub>4</sub>	1
UG	M400-UG-APS-F-BS ①	200 Amp / 2 Pole Circuit Breaker	See note ①	LINK	6	29	41 <sup>7</sup> / <sub>16</sub>	1 <sup>1</sup> / <sub>2</sub>	2 <sup>1</sup> / <sub>2</sub>	4	3 <sup>3</sup> / <sub>4</sub>	1	—
UG	M400-UG-APS-P ②	200 Amp 2 Pole—T-Fuse	200 Amp 2 Pole—T-Fuse	NONE	6 <sup>1</sup> / <sub>8</sub>	22 <sup>1</sup> / <sub>8</sub>	36	2 <sup>1</sup> / <sub>2</sub>	2 <sup>1</sup> / <sub>2</sub>	4	2 <sup>1</sup> / <sub>2</sub>	1 <sup>1</sup> / <sub>2</sub> , 3 <sup>3</sup> / <sub>4</sub>	1
UG	M400-UG-APS-LC ④	200 Amp / 2 Pole Circuit Breaker	200 Amp / 2 Pole Circuit Breaker	NONE	6	29	41 <sup>7</sup> / <sub>16</sub>	1 <sup>1</sup> / <sub>2</sub>	2 <sup>1</sup> / <sub>2</sub>	4	3 <sup>3</sup> / <sub>4</sub>	1	—
UG	M400-UG-APS-LC-BS ④	200 Amp / 2 Pole Circuit Breaker	200 Amp / 2 Pole Circuit Breaker	LINK	6	29	41 <sup>7</sup> / <sub>16</sub>	1 <sup>1</sup> / <sub>2</sub>	2 <sup>1</sup> / <sub>2</sub>	4	3 <sup>3</sup> / <sub>4</sub>	1	—
UG	U3251-O-200-CB ③	200 Amp / 2 Pole Circuit Breaker	200 Amp / 2 Pole Circuit Breaker	LINK	6 <sup>3</sup> / <sub>4</sub>	24	40 <sup>1</sup> / <sub>4</sub>	3	3	4	3	1 <sup>1</sup> / <sub>2</sub> , 3 <sup>3</sup> / <sub>4</sub>	2

**EUSERC:** Meets EUSERC requirements. Consult local utility for acceptability before ordering or installing.

**NEUTRAL:** Bonded neutral and ground factory Installed.

**LINE SIDE CONNECTORS:** Two 1/2" studs per phase on 1 3/4" centers.

**LOAD SIDE CONNECTORS:** 1/0-300

**FLUSH MOUNT:** Flush mount kit included with M400-UG-APS-F, M400-UG-APS-BS, M400-UG-APS-LC and M400-UG-APS-LC-BS. Available for other underground units. Order catalog number FK-M400-UG separately.

**SHORT CIRCUIT CURRENT WITHSTAND RATING:** 22K AIC standard, 200K AIC standard on T-fuse models.

**LUG KIT:** Mechanical lug kit available, order K4920 (#2-500).

**CONVERSION KIT:** To field convert M400 UG units to OH, order K4787-R. Includes connectors (#2-600).

- ① 200 amp primary disconnect factory installed. Order secondary disconnect separately. Specify UQFPH-100, 125, 150, 175 or 200.
- ② Two 200 amp T-fuse pull-outs factory installed as primary and secondary disconnects.
- ③ Two 200 amp 2-pole bolt-on UQFBH main breakers factory installed.
- ④ **BREAKERS:** Two 200 Amp 2-pole main breakers factory installed, and semi-flush flange kit packed inside meter section. Universal Copper 24/40 Circuit interior accepts Challenger, GE, Murraray, Siemens / ITE, and Cutler-Hammer / Westinghouse universal type plug-in branch circuit breakers.

Utility requirements for this equipment may vary. Always consult the serving utility for their requirements before ordering or installing equipment in this catalog.

