

Bus Drop | Closed Mesh Single Eye & Locking Bale Grips

Support Grips - Bus Drop - Closed Mesh

Features & Applications

- Bus drop grips are woven of galvanized steel wire
- Relieve any direct tension from the critical connection and absorb vibration and flexing
- Offered with either the single eye or locking bale attachment
- Bus drop grips are used as cable support from bus duct
- Optional bus drop safety spring can be used with single eye type of disassembling draw bar from coil, placing through eye loop and replacing draw bar
- Single eye for use when cable is vertical and for applications where cable bends
- Locking bale attachment fits around beam or pipe and can be locked in place



BDS53

Single Eye Grips

Cord Diameter	Bale Length	Mesh Length	Approx. Break Strength†	Catalog No.*	
0.22-0.32" (5.6-8.1mm)	9" (228.6mm)	3.5" (88.9mm)	1,100 lbs.	<input type="checkbox"/> BDS22	•
0.30-0.43" (7.6-10.9mm)	9" (228.6mm)	4.5" (114.3mm)	1,100 lbs.	<input type="checkbox"/> BDS30	•
0.41-0.56" (10.4-14.2mm)	9" (228.6mm)	5.0" (127.0mm)	1,100 lbs.	<input type="checkbox"/> BDS41	•
0.53-0.73" (13.5-18.5mm)	9" (228.6mm)	6.5" (165.1mm)	1,100 lbs.	<input type="checkbox"/> BDS53	•
0.70-0.85" (17.8-21.6mm)	9" (228.6mm)	8.5" (215.9mm)	1,900lbs.	<input type="checkbox"/> BDS70	•
0.82-1.00" (20.8-25.4mm)	9" (228.6mm)	8.5" (215.9mm)	1,900lbs.	<input type="checkbox"/> BDS82	•
0.96-1.25" (24.4-31.8mm)	9" (228.6mm)	11.0" (279.4mm)	1,900lbs.	<input type="checkbox"/> BDS96	•



BDU53

Locking Bale Grips

Cord Diameter	Bale Length	Mesh Length	Approx. Break Strength†	Catalog No.*	
0.22-0.32" (5.6-8.1mm)	12" (304.8mm)	3.5" (88.9mm)	1,100 lbs.	<input type="checkbox"/> BDU22	•
0.30-0.43" (7.6-10.9mm)	12" (304.8mm)	4.5" (114.3mm)	1,100 lbs.	<input type="checkbox"/> BDU30	•
0.41-0.56" (10.4-14.2mm)	12" (304.8mm)	5.0" (127.0mm)	1,100 lbs.	<input type="checkbox"/> BDU41	•
0.53-0.73" (13.5-18.5mm)	15" (381.0mm)	6.5" (165.1mm)	1,100 lbs.	<input type="checkbox"/> BDU53	•
0.70-0.85" (17.8-21.6mm)	16" (406.4mm)	8.5" (215.9mm)	1,900lbs.	<input type="checkbox"/> BDU70	•
0.82-1.00" (20.8-25.4mm)	16" (406.4mm)	8.5" (215.9mm)	1,900lbs.	<input type="checkbox"/> BDU82	•
0.96-1.25" (24.4-31.8mm)	17" (431.8mm)	11.0" (279.4mm)	1,900lbs.	<input type="checkbox"/> BDU96	•

Accessories for Support Grips: Service Drop & Bus Drop, Closed Mesh Grips

Description	<input type="checkbox"/>	
Safety Spring, 40 lbs. load	<input type="checkbox"/> B2001	•
Safety Spring, 80 lbs. load	<input type="checkbox"/> B2002	•



B2001



B2002

* For stainless steel support grips, add "SS" suffix to the catalog number (example, SGS50SS).

† To determine workload safety factor, divide approximate break strength by 10. See Page 34 for strength information. Consult Factory for price and availability.

Specifications and availability are subject to change without notice.

Icon Key

NAFTA Compliant