

## DS300H2



## Field Installation Rainproof Conduit Hubs

## Description

Group 1—for use with 70, 100 and 125A MLO and MCB loadcenters and circuit breaker enclosures and the following 150 and 200A panels: BR48B200RF

Group 2—for use with 150, 200 and 225A MLO and MCB loadcenters and circuit breaker enclosures except for the following 200A loadcenters: BR48B200RF. Also for use with 400 and 600A loadcenters and New York City loadcenters manufactured after November 1, 2005

Type H conduit hubs for loadcenters PL0724R and S3100RN

Adapter kit—Allows installing a Group 1 hub on devices arranged for Group 2 hubs

Group 1 small blank hub plate with bump

Group 2 Large blank hub plate with bump

| Conduit Size<br>Inches (mm) | Ordering<br>Quantity <sup>①</sup> | Catalog<br>Number |
|-----------------------------|-----------------------------------|-------------------|
| 0.75 (19.1)                 | 1                                 | DS075H1           |
| 1.00 (25.4)                 | 1                                 | DS100H1           |
| 1.25 (31.8)                 | 1                                 | DS125H1           |
| 1.50 (38.1)                 | 1                                 | DS150H1           |
| 2.00 (50.8)                 | 1                                 | DS200H1           |
| 2.00 (50.8)                 | 1                                 | DS200H2           |
| 2.50 (63.5)                 | 1                                 | DS250H2           |
| 3.00 (76.2)                 | 1                                 | DS300H2           |
| 0.75 (19.1)                 | 1                                 | RH75P             |
| 1.00 (25.4)                 | 1                                 | RH100P            |
| 1.25 (31.8)                 | 1                                 | RH125P            |
| 1.50 (38.1)                 | 1                                 | RH150P            |
| —                           | 1                                 | DS900AP           |
| —                           | 1                                 | DS900CP1          |
| —                           | 1                                 | DS900CP2          |

## GBK14



## BRGBK39512



## Ground Bar Kits

| Description<br>(See Legend) | Length<br>Inches (mm) | Ordering<br>Quantity <sup>①</sup> | Catalog<br>Number        |
|-----------------------------|-----------------------|-----------------------------------|--------------------------|
| ●○○○○●○                     | 2.54 (64.5)           | 1                                 | GBK5 <sup>②</sup>        |
| ●○○○○●●■                    | 3.59 (91.2)           | 1                                 | GBK520 <sup>②</sup>      |
| ●○○○○●○○○○○                 | 4.29 (109.0)          | 1                                 | GBK10 <sup>②</sup>       |
| ●○○○○●○○○○○■                | 5.34 (135.6)          | 1                                 | GBK1020 <sup>②</sup>     |
| ●●●●●■●●●●●●                | 4.61 (117.1)          | 1                                 | GBK13 <sup>②</sup>       |
| ●○○○○●○○○○○○○○○             | 5.69 (144.5)          | 1                                 | GBK14 <sup>②</sup>       |
| ●○○○○●○○○○○○○○○■            | 6.74 (171.2)          | 1                                 | GBK1420 <sup>②</sup>     |
| ●○○○○●○○○○○○○○○○○○○         | 8.14 (206.8)          | 1                                 | GBK21 <sup>②</sup>       |
| ●○○○○●○○○○○○○○○○○○○■        | 9.19 (233.4)          | 1                                 | GBK2120 <sup>②</sup>     |
| ●●●●●■●●●●●●●●●●●●          | 5.78 (146.8)          | 1                                 | BRGBK39512 <sup>③④</sup> |
| ○○○○○                       | 1.84 (46.7)           | 1                                 | GB4NM <sup>⑤</sup>       |

## Ground Bar Legend

- (3) #14–10 Cu/Al or (1) #14–4 Cu/Al
- (1) #6–2/0 Cu/Al
- (1) #14–1/0 Cu/Al or (3) #14–10 Cu/Al
- (1) #14–6 Cu/Al or (2) #14–12 Cu/Al
- Mounting Hole

## Notes

- <sup>①</sup> Must be purchased in multiples of ordering quantities indicated.
- <sup>②</sup> Distance between mounting holes is 1.75 inches (44.5 mm).
- <sup>③</sup> For single- and three-phase 400 and 600A applications.
- <sup>④</sup> Distance between mounting holes is 2.34 inches (59.5 mm).
- <sup>⑤</sup> For non-metallic enclosures. Snaps into molded base.