


“U” Bolt

- Includes: hardware shown
- Material: SAE J429 steel
- Finish: Yellow Zinc (YZ)


Part Number	‘A’		‘B’		‘C’		Thread Size	Weight Per 100	
	In.	(mm)	In.	(mm)	In.	(mm)		Lbs.	(kg)
SB1001A	3”	(76)	1 1/4”	(32)	3 1/8”	(79)	1/2”-13	18	(8.1)
SB1001B	4 1/2”	(114)	1 1/2”	(38)	3 1/8”	(79)	1/2”-13	23	(10.4)
SB1001E	5 1/2”	(140)	1 1/2”	(38)	1 19/32”	(40)	3/8”-16	34	(15.4)
SB1001M	5”	(127)	1 1/2”	(38)	4 1/8”	(105)	1/2”-13	75	(34.0)
SB1001S	5”	(127)	1”	(25)	5 1/4”	(133)	1/2”-13	84	(38.1)
SB1001U	4”	(101)	1”	(25)	1 9/16”	(39)	1/2”-13	54	(24.5)



“V” Bolt

- Designed for use with angle iron.
- Includes: hardware shown
- Material: SAE J429 steel
- Finish: Yellow Zinc (YZ)

Part Number	‘A’		‘B’		‘C’		‘D’		Thread Size	Weight Per 100	
	In.	(mm)	In.	(mm)	In.	(mm)	In.	(mm)		Lbs.	(kg)
SB100203A	3”	(76)	2 1/16”	(52)	1 1/8”	(28)	1 1/4”	(32)	3/8”-16	21	(9.5)
SB100203B	4”	(101)	2 1/16”	(52)	1 1/8”	(28)	1 1/2”	(32)	3/8”-16	26	(11.8)
SB100203C	6”	(152)	2 1/16”	(52)	1 1/8”	(28)	1 1/2”	(32)	3/8”-16	36	(16.3)
SB100204B	3”	(76)	2 1/8”	(54)	2”	(51)	13/16”	(20)	1/2”-13	44	(19.9)
SB100204D	4”	(101)	2 1/8”	(54)	2”	(51)	1 1/2”	(32)	1/2”-13	52	(23.6)
SB100204G	5”	(127)	2 1/8”	(54)	2”	(51)	2”	(51)	1/2”-13	62	(28.1)
SB100204H	6”	(152)	2 1/8”	(54)	2”	(51)	2”	(51)	1/2”-13	71	(32.2)



“J” Bolt

- Includes: hardware shown
- Material: SAE J429 steel
- Finish: Yellow Zinc (YZ)

Part Number	‘A’		‘B’		‘C’		‘D’		Thread Size	Weight Per 100	
	In.	(mm)	In.	(mm)	In.	(mm)	In.	(mm)		Lbs.	(kg)
SB1003A	2”	(51)	1/4”	(6)	1/2”	(13)	1”	(25)	5/16”-18	13	(5.9)
SB1003F	4 1/4”	(108)	1/2”	(13)	3/4”	(19)	1 1/4”	(32)	3/8”-16	31	(14.0)
SB1003G	3 1/2”	(89)	13/16”	(20)	3/4”	(19)	1 1/4”	(32)	5/16”-18	20	(9.1)
SB1003J	2 3/4”	(68)	7/16”	(11)	3/4”	(19)	1”	(25)	5/16”-18	16	(7.2)
SB1003K	5”	(127)	1/2”	(13)	3/4”	(19)	1 1/4”	(32)	5/16”-18	25	(11.3)
SB1003M	3 3/4”	(95)	7/16”	(11)	3/4”	(19)	1 1/4”	(32)	5/16”-18	20	(9.1)

