

SUMMARY OF BRANCH BREAKERS AVAILABLE

Breaker Frame	No. of Poles	Ampere Rating	Voltage	kAIC Rating	Example	Panel Type
BAB	1	15 – 60	120 Vac	10	BAB1020	PRL1a
	2	15 – 100	120/240 Vac	10	BAB2020	PRL1a
BAB H	2	15 – 100	240 Vac	10	BAB2040H	PRL1a
	3	15 – 100	240 Vac	10	BAB3030H	PRL1a
QBGF	1	15 – 30	120 Vac	10	QBGF1020	PRL1a
	2	15 – 40	120/240 Vac	10	QBGF2040	PRL1a
QBHW	1	15 – 60	120 Vac	22	QBHW1020	PRL1a
	2	15 – 100	120/240 Vac	22	QBHW2020	PRL1a
	2	15 – 100	240 Vac	22	QBHW2040H	PRL1a
	3	15 – 100	240 Vac	22	QBHW3030H	PRL1a
GHQ	1	15 – 20	277 Vac	14	GHQ1020	PRL2a
GHB	1	15 – 100	277 Vac	14	GHB1020	PRL2a
	2	15 – 100	480V/277 Vac	14	GHB2040	PRL2a
	3	15 – 100	480V/277 Vac	14	GHB3060	PRL2a

Circuit Breaker Kits — Unassembled Panelboards

KITS — MAIN CIRCUIT BREAKER OR SUB-FEED CIRCUIT BREAKER (INCLUDES CIRCUIT BREAKER AND TERMINALS)

Max. Voltage	Ampere Rating	Service	Catalog Number	Breaker Frame	Mounting Location	Wire Range Al/Cu
240 Vac	100	1 or 3-Ph	BKED100T	ED	Top	(1) #14 – 1/0
	125	1 or 3-Ph	BKED125T	ED	Top	(1) #4 – 4/0
	150	1 or 3-Ph	BKED150T	ED	Top	(1) #4 – 4/0
	175	1 or 3-Ph	BKED175T	ED	Top	(1) #4 – 4/0 ①
	200	1 or 3-Ph	BKED200T	ED	Top	(1) #4 – 4/0 ①
	225	1 or 3-Ph	BKED225T	ED	Top	(1) #4 – 4/0 ①
240 Vac	100	1 or 3-Ph	BKED100B	ED	Bottom	(1) #14 – 1/0
	125	1 or 3-Ph	BKED125B	ED	Bottom	(1) #4 – 4/0
	150	1 or 3-Ph	BKED150B	ED	Bottom	(1) #4 – 4/0
	175	1 or 3-Ph	BKED175B	ED	Bottom	(1) #4 – 4/0 ①
	200	1 or 3-Ph	BKED200B	ED	Bottom	(1) #4 – 4/0 ①
	225	1 or 3-Ph	BKED225B	ED	Bottom	(1) #4 – 4/0 ①
480 Vac	100	1 or 3-Ph	BKFD100T	FD	Top	(1) #14 – 1/0
	125	1 or 3-Ph	BKFD125T	FD	Top	(1) #4 – 4/0
	150	1 or 3-Ph	BKFD150T	FD	Top	(1) #4 – 4/0
	175	1 or 3-Ph	BKFD175T	FD	Top	(1) #4 – 4/0 ①
	200	1 or 3-Ph	BKFD200T	FD	Top	(1) #4 – 4/0 ①
	225	1 or 3-Ph	BKFD225T	FD	Top	(1) #4 – 4/0 ①
480 Vac	100	1 or 3-Ph	BKFD100B	FD	Bottom	(1) #14 – 1/0
	125	1 or 3-Ph	BKFD125B	FD	Bottom	(1) #4 – 4/0
	150	1 or 3-Ph	BKFD150B	FD	Bottom	(1) #4 – 4/0
	175	1 or 3-Ph	BKFD175B	FD	Bottom	(1) #4 – 4/0 ①
	200	1 or 3-Ph	BKFD200B	FD	Bottom	(1) #4 – 4/0 ①
	225	1 or 3-Ph	BKFD225B	FD	Bottom	(1) #4 – 4/0 ①

① Order optional lug kit Catalog No. 3TA225FDK for 175 – 225 ampere ED- and FD-Frame 3-pole circuit breakers to provide terminations for (1) #6 – 300 kcmil.

KITS — MAIN CIRCUIT BREAKER (INCLUDES CIRCUIT BREAKER AND TERMINALS)

Max. Voltage	Ampere Rating	Service	Catalog Number	Breaker Frame	Mounting Location	Wire Range Al/Cu
480 Vac	250	1 or 3-Ph	BKKD250T	KD	Top	(1) 250 – 500 kcmil
	300	1 or 3-Ph	BKKD300T	KD	Top	(1) 250 – 500 kcmil
	350	1 or 3-Ph	BKKD350T	KD	Top	(1) 250 – 500 kcmil
	400	1 or 3-Ph	BKKD400T	KD	Top	(2) 3/0 – 250 kcmil or (1) 3/0 – 500 kcmil
480 Vac	250	1 or 3-Ph	BKKD250B	KD	Bottom	(1) 250 – 500 kcmil
	300	1 or 3-Ph	BKKD300B	KD	Bottom	(1) 250 – 500 kcmil
	350	1 or 3-Ph	BKKD350B	KD	Bottom	(1) 250 – 500 kcmil
	400	1 or 3-Ph	BKKD400B	KD	Bottom	(2) 3/0 – 250 kcmil or (1) 3/0 – 500 kcmil

KITS — MAIN LUGS OR THROUGH-FEED LUGS

Ampere Rating	Service	Catalog Number	Wire Range Al/Cu
100	1 or 3-Ph	LUGKIT100	(1) #14 – 1/0
225	1 or 3-Ph	LUGKIT225	(1) #6 – 300 kcmil
400	1 or 3-Ph	LUGKIT400	(2) #2 – 500 kcmil

KITS — SERVICE ENTRANCE

Ampere Rating	Service	Catalog Number	Panel Type
100/225	1 or 3-Ph	SEK1/2	PRL1a or PRL2a
400	1 or 3-Ph	SEK4/6	PRL1a or PRL2a

KITS — INSULATED/ISOLATED GROUND (CARTON QTY OF 5)

Ampere Rating	Service	Catalog Number	Panel Type
100/225/400	1 or 3-Ph	ISOGROUND	PRL1a or PRL2a

KITS — 200% NEUTRAL

Ampere Rating	Service	Catalog Number	Panel Type
100	1 or 3-Ph	2NK100	PRL1a or PRL2a
225	1 or 3-Ph	2NK225	PRL1a or PRL2a

EZ is a trademark of Eaton Corporation. NEMA is the registered trademark and service mark of the National Electrical Manufacturers Association.

Eaton Corporation
 Electrical Sector
 1111 Superior Ave.
 Cleveland, OH 44114
 United States
 877-ETN-CARE (877-386-2273)
 Eaton.com

© 2009 Eaton Corporation
 All Rights Reserved
 Printed in USA
 Publication No. SA01413001E / Z9046
 August 2009

