


# DRD2

## General Recessed LED Downlight



## Specs at a Glance

Application	New Construction, Remodel, Retrofit
Housing	4" Shallow, 5", 6", 6" Shallow, Junction Box, Surface Mount
Lumen Output (Power)	750 lm (10.8W), 1000 lm (12.8W)
Color Quality	93+ CRI, 2-step SDCM
CCT Options	2700K, 3000K, 3500K, 4000K
Lifetime (L70)	50,000 hrs
Input Voltage	120/277V
Dimming	Dimming down to less than 5% for TRIAC/ELV at 120V, 10% for 0-10V at 120/277V, 1% for Lutron® Hi-lume® 1% at 120/277V
Emergency Lighting	Optional Emergency LED Driver for lighting up to 90 minutes in event of power failure
Trim Shape	Round, Square, Square on Round, Deep
Trim Style	Smooth, Baffle, Wall Wash
Trim Finish	White, Black, Silver (silver reflector, white flange), Alzak (low iridescent reflector, white flange), Custom
Listings	cULus Listed, ENERGY STAR® qualified, California Title 24 2016 JA8 compliant, UL Listed for Wet Location, IC rated, ASTM E283 certified Air Tight
Warranty	5 years

# Product Selection Guide

## FRAME-IN KIT (Product Code Example: **DRDH** + **N** + **IC** + **4** = **DRDHNIC4**)

PRODUCT CODE	APPLICATION	IC/NON-IC	APERTURE	DRIVER	OPTION
<b>DRDH</b> Housing	<b>N</b> New Construction <b>R</b> Remodel	<b>IC</b> Insulation Contact	<b>4</b> 4" Aperture <b>4S</b> 4" Aperture, Shallow <b>5</b> 5" Aperture <b>6</b> 6" Aperture <b>6S</b> 6" Aperture, Shallow	<b>[Blank]</b> Integrated TRIAC/ELV <b>7O</b> 0-10V, 750 lm <b>10O</b> 0-10V, 1000 lm <b>7C</b> Lutron LDE1, 750 lm <b>10C</b> Lutron LDE1, 1000 lm <b>7W</b> Lutron L3DA3W, 750 lm <b>10W</b> Lutron L3DA3W, 1000 lm	<b>[Blank]</b> None <b>EM</b> Emergency Driver <i>Only available for new construction application; 0-10V and Lutron Hi-Lume 1% Driver</i>

## LIGHT ENGINE (Product Code Example: **DRD2M** + **7** + **9** + **27** = **DRD2M7927**)

PRODUCT CODE	LUMENS (WATTS)	CRI	CCT	DRIVER
<b>DRD2M</b> Module	<b>7</b> 750 lm (10.8W) <b>10</b> 1000 lm (12.8W)	<b>9</b> 93+ CRI	<b>27</b> 2700K <b>30</b> 3000K	<b>35</b> 3500K <b>40</b> 4000K
				<b>[Blank]</b> Integrated TRIAC/ELV <b>A</b> Alternate Dimming <i>Must be selected if 0-10V, Lutron Hi-Lume 1% or EM Driver is selected for frame-in kit</i>

## TRIM (Product Code Example: **DRD2T** + **R** + **4** + **S** + **WH** = **DRD2TR4SWH**)

PRODUCT CODE	SHAPE	APERTURE	STYLE	FINISH	OPTION
<b>DRD2T</b> Trim	<b>R</b> Round <b>S</b> Square <i>Only available in 4" aperture; smooth style; new construction application</i> <b>Q</b> Square on Round <i>Only available in 4" aperture; smooth style; new construction application</i> <b>D</b> Deep <i>Only available in 6" aperture; smooth or baffle style; white, low iridescent or custom finish</i>	<b>4</b> 4" Aperture <b>5</b> 5" Aperture <b>6</b> 6" Aperture	<b>S</b> Smooth <b>B</b> Baffle <b>W</b> Wall Wash <i>Only available in white finish</i>	<b>WH</b> White <b>BK</b> Black <b>SW</b> Silver Reflector w/ White Flange <b>AZ</b> Low Iridescent Reflector w/ White Flange <i>Only available in deep shape</i> <b>CC</b> Custom Color	<b>[Blank]</b> None <b>DF</b> Dead Front <i>Only available in round shape; 4" aperture; smooth style; Compatible with 750 lm light engine only</i>

## Dimensions



**DRD2M**  
LED Module

