


Residential & Small Business **Generators**



POWER YOU CONTROL

GENERAC[®]







Imagine your life **without** power?

- Refrigeration/freezer for food and medicines
- Furnace
- Air conditioning
- Lighting – inside and outside
- Clean water for drinking and bathing
- Sump pump
- Kitchen appliances
- Contact with the outside world; Internet, cell phone chargers, TV, radio and more
- Washing and drying clothes
- Security system
- Garage door opener
- Fans
- Medical equipment
- Charging power tools for use during the emergency and post-outage cleanup
- Monetary loss from temporary relocation, hotel costs, dining out, property damage, etc.

GENERAC®

TOP CAUSES FOR POWER OUTAGES

Source: Generac Power Outage Explorer



Power. Our lives depend on it

From essentials like heating, cooling and lights, to daily necessities like cooking, laundry and the kid's bath-time, our lives run on electricity. Unfortunately, our modern lifestyles are in ever-greater jeopardy; power outages are occurring more frequently than ever and lasting longer, with devastating effects. Protect your home and family with a Generac automatic standby generator and keep life going without disruption.

The #1 choice in standby power

At Generac, we protect the things that power your life by providing quality, affordable power solutions. Since 1959, we've focused primarily on power generation, and we now offer more generator solutions than any other manufacturer. That heritage has helped make us the number one choice in residential standby power, chosen seven to one over the closest competition. When you choose Generac, you're choosing to have peace of mind and the power to live.

5-Year Limited Warranty for automatic standby generators.

True Power™ Technology delivers best-in-class power quality with less than 5 percent total harmonic distortion for clean, smooth operation of sensitive electronics and appliances.

Generac Generators and engines are engineered and Built in the USA*
**Built in the USA using domestic and foreign parts.*

The Generac G-Force Engines are purpose-built, pressure-lubricated engines capable of handling the rigors of generator use, resulting in power that's more reliable and requiring less routine maintenance than any competitive engine.

7 OUT-OF 10 HOMEOWNERS CHOOSE GENERAC

Source: Frost & Sullivan, SBI, TraQline

**24-7
POWER
PROTECTION**



GENERAC

POWER
YOU CONTROL

AUTOMATIC STANDBY GENERATORS

When inclement winter weather left Greg and Ellen's family without power for five straight days, they knew they had to do something to keep their home and family protected from the negative effects of extreme cold.

"We're always one of the last neighborhoods to have our power restored. So, after that last storm... we invested in a Generac generator.

We always have power now."

REAL
GENERAC
OWNER

-Greg & Ellen L.

POWER
YOU CONTROL

THE GENERAC
PROMISE



* Built in the USA using domestic and foreign parts.

The Generac Promise means that our 9–22 kilowatt Guardian® Series home backup generators will give you peace of mind and the power to live. It means that we engineer and build them here in America*. It means we stand behind them with a strong 5-year limited warranty. We promise to continue to innovate, like our Mobile Link™ cellular monitoring system, so you'll know the status of your generator, no matter where you are. And if you ever need to call, we're standing by 24/7, every minute of every day, ready to pick up the phone right here in Wisconsin.

Reliable. Dependable. We promise.

This is how a generator **works**

1 Utility power is lost.


Maybe it's a storm. Maybe a grid failure. Maybe one of those cyberterrorists finally broke through. Whatever the cause, the power is out and you need a solution.

2 Your generator turns on. Automatically.

Within seconds, your Generac generator senses the problem, turns on, and your house is fully powered--whether you're home or not. And it keeps the power on, whether the outage lasts hours or weeks.

3 Your generator turns off. Automatically.

When your Generac generator senses that utility power is restored, it shuts itself off and returns to standby mode waiting to answer the call the next time you lose power.



“MY FAMILY’S GOING TO BE SAFE AND SECURE
IN MY HOUSE BECAUSE OF THIS GENERATOR.”

- Greg Beappler

Sizing a generator is based on **your needs**

By sizing your generator according to your needs instead of your home’s square footage, you won’t overspend or be surprised by inadequate coverage. Generac has the solution; essential circuit coverage for the basics, managed whole-house for average coverage, and true whole-house coverage to protect it all.

How much power do you need?

With the broadest product line in the industry, Generac ensures the best possible backup power system for every homeowner, and one that is right for you.



Essential Circuit Coverage



Managed Whole-house



Complete Whole-house

Essential Circuit Coverage

ECONOMICAL SOLUTIONS COVER THE BASICS.

Many homeowners choose to cover only their essential circuits during an outage. Choose from options that create a simple, economical solution that keeps basics covered during an emergency.

Managed Whole-House

POWER MANAGEMENT GAINS MORE COVERAGE FROM A SMALLER GENERATOR.

Gain up to whole-house coverage through smart power management. If it is unlikely you will turn on every appliance at the same time (most people don’t), a smaller generator paired with a Generac power-management switch provides whole-house coverage through a managed power solution by managing the power requirements of individual appliances.

Complete Whole-House

WHEN THE POWER GOES OUT, EVERYTHING COMES ON AND STAYS ON.

Generac’s full line of backup power solutions includes larger generators capable of covering every circuit in any size home for complete whole-house protection. Never wait for an appliance to take its turn being powered. When the power goes out, everything goes on and stays on — no matter how many circuits need to be backed up.

“ I DON'T HAVE TO DO ANYTHING, IT'S GREAT. ”

- Jerald Grupp



Generac offers a wide **range of sizes**

Consumers choose Generac automatic generators not only for their proven reliability, but for the innovative features, engineered with home and business owners in mind.

PowerPact™ 7.5 kW unit



Generac's 7.5 kW Powerpact home standby generator is the affordable, automatic alternative to portable backup power. Features incorporate the quality and reliability of the best selling Guardian Series, while remaining the most affordable home standby generator available. Runs on LP or natural gas.

- Prepackaged system available with a 50 Amp transfer switch featuring an eight circuit load center including breakers
- Generac OHV engine is designed for reliability and long life
- True Power™ technology provides clean, smooth operation of sensitive electronics and appliances
- Digital controller with LED light status and fault indicators
- Three of the four sides are easily removable for simple service and maintenance access



Guardian Series® 9–22 kW units



Generac's Guardian Series offers a wide range of solutions, so you can get the level of coverage that is appropriate to your needs. Choose from a pre-packaged system or have your dealer or contractor help design the best system for you.

- 5 Year Limited Warranty for automatic standby generators
- True Power™ Technology delivers best-in-class power quality with less than 5 percent total harmonic distortion for clean, smooth operation of sensitive electronics and appliances.
- Generac Generators and engines are Engineered and Built in the USA*
*Built in the USA using domestic and foreign parts
- The Generac G-Force Engine is purpose-built, pressure-lubricated engine capable of handling the rigors of generator use, resulting in power that's more reliable and requiring less routine maintenance than any competitive engine
- 24/7/365 Customer Support Team standing by all-day every-day from our headquarters in Wisconsin to answer any questions you might have



Synergy 20 kW unit



Protect your home with the industry's most advanced back-up power technology. The Generac Synergy™ automatic home standby generator delivers cleaner power than competitive units, our G-Flex™ Technology allows variable-speed operation based on your electrical demand.

- 5 Year Limited Warranty for automatic standby generators.
- G-Flex™ Technology delivers power with less than 2% total harmonic distortion (THD) for clean, smooth operation of sensitive electronics and appliances.
- Generac Generators and engines are Engineered and Built in the USA*
*Built in the USA using domestic and foreign parts.
- The Generac G-Force Engine is purpose-built, pressure-lubricated engine capable of handling the rigors of generator use, resulting in power that's more reliable and requiring less routine maintenance than any competitive engine.



EcoGen 15 kW unit



Generac offers the only automatic standby generator engineered specifically for off-grid applications. The EcoGen eliminates the expense and unreliability previously associated with alternative energy backup power options, instead providing affordable, reliable, low emission, off-grid standby power.

- Engineered to easily integrate into the existing inverter and battery storage system
- Runs on environmentally friendly, energy-efficient propane gas, an alternative fuel that stores easily and indefinitely, and is freely available at many off-grid locations



Tough. Reliable. Purpose-Built.

Generators are often required to run for hours, days or even weeks at a time. Continuous use can cause a lot of strain on engines not specifically engineered to withstand extended run times. We have developed robust engine solutions to ensure our generators provide the reliability necessary to power through even the most demanding situations.



5-Year Limited Warranty

For all automatic standby generators.



True Power™ Technology

Delivers best-in-class power quality with less than 5 percent total harmonic distortion for clean, smooth operation of sensitive electronics and appliances.



Built in the USA

Generac Generators and engines are engineered and Built in the USA*
*Built in the USA using domestic and foreign parts.



24/7/365 Customer Support Team

Standing by all-day every-day from our headquarters in Wisconsin to answer any questions you might have.



Quiet-Test™ Self-Test Mode

Runs at a lower RPM for a five or twelve minute test, is significantly quieter than other brands, and consumes less fuel. (16–22 kW only)

When Hurricane Sandy knocked out utility power across eastern regions of the United States, Jimmy's family was forced to wait out the storm without electricity or the protection of their home security system. To ensure this never happened again, Jimmy decided to purchase an automatic standby generator from Generac.

“The lights went out, and we had nothing. I said to myself that I was never going to live that way again. Now that we have a Generac generator, **our life has become easier.**”

REAL
GENERAC
OWNER

-Jimmy M.

POWER
YOU CONTROL



The Generac G-Force Engine

The heart of the Guardian Series 9-22 kW residential generators is the Generac G-Force engine, purpose-built for the rigors of power generation. The G-Force engine utilizes the same type of pressurized oil lubrication used to give automobile engines long and trouble-free lives. It also requires fewer scheduled maintenance checkups than some competitor's engines, and provides the reliability you need for the long run-times that emergency backup can require.



Tough, Durable Enclosures

Sturdy all weather enclosures made from corrosion-resistant aluminum.



Smart, User-friendly Controls.

Generac's Evolution™ Controller features a dual-line, multilingual LCD display allowing for easy monitoring of history and maintenance logs and manage your generator.



Mobile Link™ Remote Monitoring

Connects you to your generator allowing you to access information such as the current operating status, maintenance schedule, and more directly from your smart phone, tablet or computer. (Sold Separately) (7.5-150 kW)



Intelligent and Affordable

DPM™ Technology intelligently manages household loads for a more affordable standby solution. (Available on 11 kW and larger units bundled with a 200 Amp transfer switches).



Convenient Installation

Certified for optimal placement 18" away from a building.



When more power is needed

As the world's #1 manufacturer of home standby systems, Generac identified and responded to the need for affordable, higher kW units for larger residences and smaller businesses. Through innovative engineering, Generac has eliminated the noise, cost, and environmental issues that once made standby power impractical for these applications. When more power is necessary, install a quiet, clean and affordable solution from Generac.

Protector™ Series – Diesel 15, 20, 30, 48/50 kW

Generac's Protector Series diesel units raise the bar for residential and light commercial diesel generators. Building and zoning codes can vary greatly from one region to another. In the past, the only answer was to order expensive, custom-configured solutions. Until now.

To address the variances in code, Generac's diesel-powered Protector Series is the only automatic standby generator to feature Code Ready, a set of common options that are preconfigured to ensure that the generator will be adaptable to a variety of municipal codes. A wide range of code-driven accessories are available to address any further code conformance requirements.

- External vent and fill
- UL 142 / ULC SG01-listed, double-walled base tank
- UL/CUL 2200-listed generator
- Aluminum, weather-resistant enclosures



Protector™ Series – Gaseous 25, 30, 45, 60 kW

The higher kW nodes of Generac's Protector Series are ideal for larger homes and small businesses.

- The solid reliability of an automotive-style, liquid-cooled engine provides whole-house power protection for larger homes, and small-to-medium-size businesses such as convenience stores, restaurants and offices
- Continuous fuel choices in LP and natural gas offer cleaner-burning fuel solutions than traditional diesel engines
- Premium 5-Year Limited Warranty is best in class for automatic standby generators. Includes parts and labor.
- True Power Technology delivers best-in-class power quality with less than 5% total harmonic distortion for clean, smooth operation of sensitive electronics and appliances.
- Generac Generators and engines are engineered and Built in the USA*
**Built in the USA using domestic and foreign parts*
- Aluminum, weather-resistant enclosures



Protector™ Series – Gaseous 22, 27, 36, 48 kW

Premium features are standard on the ultimate residential standby generator. For discerning homeowners with larger residences, these units are powered by a low-speed engine for extra-quiet operation and come standard with an aluminum enclosure. Protector generators also include all the features of the Protector Series 25 – 60 kW

- Ideal for homes requiring higher kW backup for amenities such as additional living areas, garages and air conditioners, pools, greenhouses, guest houses, mother-in-law suites, medical needs, and more
- The low-speed, liquid-cooled engine is engineered to run at only 1800 RPM for a substantially quieter generator, consuming less fuel, and giving both the engine and the alternator a longer life



Need single or three-phase options up to 150 kW? Ask your dealer about Generac's commercial generators.



“ MY BUSINESS ACTUALLY MAKES
MORE MONEY
DURING A POWER OUTAGE . . . I'M THE
ONLY PLACE OPEN! ”

- Steven Beck



Transfer switches

Because Generac understands the transfer switch is the core of the generator system, we offer more options than any other manufacturer to ensure coverage requirements are met. All switches are UL listed.

Power Just the Basics



Some homeowners prefer a simple, economical approach. Essential coverage protects only your most important circuits — such as lights, furnace, water heater, refrigerator/freezer and sump pump.

Finding the generator that's right for you depends on your needs and your budget — not just your square footage. Generac offers the broadest line of home standby generators in the industry. So we can help you find the perfect match to protect your home.

Pre-wired, Limited Circuit Switches

Generac's Pre-Wired Switch is an automatic transfer switch and distributed load center that backs up selected circuits for essential circuit coverage. Pre-wired for the easiest and least expensive installation on the market, they are an excellent value when whole house coverage is unnecessary.

GenReady

Generac's 200 amp GenReady Panel serves as a replacement to your home's main panel, as well as the transfer switch needed for automatic operation. This solution features a 40-circuit capacity when tandem breakers are properly utilized. Ideal for new home construction, or electrical service upgrades, this switch is a space saver, and can be used with systems up to 30kW in size.

100 Amp, NEMA 3R, 16 Circuit Switch

Generac's limited circuit automatic transfer switches are a great option for homes where the electrical panel is located outside. These switches are compatible with breakers manufactured by Eaton, Siemens or Squared D; with the use of tandem breakers, these switches can be expanded to 24 circuits.

100-800 Amp, Non-service Rated, NEMA 3R Switches

If your personal application and backup power needs require a custom-built sub panel, Generac's non-service rated automatic transfer switches provide an option for both indoor and outdoor installation. When a limited circuit switch, and/or the combination of breakers on an alternative switch are insufficient, utilize these models.

Power Where You Need it



Whole-house coverage may not fit every budget. With a power management system, your generator can work smarter. It protects all your home's circuits by cycling power on and off as needed for different appliances. And you decide what gets priority.

A Generac power management system protects all the circuits in your home — without the higher cost of whole-house coverage.

Chances are you won't need to turn on every appliance at the same time during an outage. (Most people don't.) Generac power management systems monitor power needs throughout your house — automatically cycling power on and off where it's needed.

The way it works is simple. You decide which circuits are most essential to your home. Whenever the generator approaches its power limit, the system turns off non-essential circuits to prevent an overload. Once essential circuits are satisfied, it cycles non-essential circuits back on.

Power it All, All The Time



Most homeowners want the peace of mind that comes with whole-house coverage. Whenever there's an outage, you don't have to worry — because the power stays on at all times throughout your entire home.

A Generac whole-house power system backs up every electrical circuit in your home whenever the power goes out.

There's no waiting for an appliance to take its turn being powered — everything comes on and stays on. So you don't have to decide which circuits are most important. They'll all be available, automatically, around the clock.

The full line of Generac whole-house power systems includes larger generators and transfer switches capable of covering every circuit in any size home. It's a comprehensive approach for complete peace of mind.

100-400 Amp Service-Rated

Generac's service rated automatic transfer switches offer whole-house coverage for your back-up power needs. Featuring a NEMA 3R enclosure, these particular switches can be installed either indoors or outdoors.

100-800 Amp Non-Service Rated

Generac's non-service rated automatic transfer switches enable full-circuit coverage, when an additional main disconnect is properly installed in the field. Featuring a NEMA 3R enclosure, these particular switches can be installed either indoors or outdoors.

100-200 Amp CSA Service-Rated

CSA models are approved for use in Canada. Featuring a NEMA 3R enclosure, these particular switches can be installed either indoors or outdoors.

100-200 Amp GenReady™ Whole House Service Equipment Rated Transfer Switch

This panel integrates a main breaker, transfer switch, and load center. Comes in 24 space, 40 Circuit and 42 space, 60 Circuit options.

200 Amp Service Rated with Integrated Load Center

The 200 amp open transition switch is a single phase service entrance rated configuration with 8 Circuit Load Center.

Smart Management Module

Meet the brains that make smart power possible. These modules are essential to a Generac power management system. They work with your transfer switch, monitoring each selected circuit and automatically supplying power where it's needed so you can get the most from your generator.



A Generac power management system can use up to eight individual Smart Management Modules, depending on your needs. Just as important, you can set the load priority for each — putting you in control of which circuits matter most.

Accessories

Generac offers more accessory options than any other generator manufacturer to ensure coverage requirements are met.



Mobile Link™ Remote Monitoring

This affordable remote monitoring system gives customers peace of mind by allowing them to know the status of their generator anywhere, anytime, using their computer, tablet or smart phone.

Generator Status Updates

Mobile Link provides you with notifications on the status of your home standby generator. Link multiple email addresses and phone numbers to receive email and text message alerts or push notifications if you're using the Mobile Link app. You can even have information sent directly to your authorized service provider so they can proactively offer professional support.

- View current generator status and status of scheduled self-test
- Receive system notifications regarding needed maintenance, including battery status or any faulty conditions, by email, text or push notifications
- Local weather updates
- Compatible air-cooled standby generators with an LCD display or generators equipped with a Nexus or an Evolution controller, as well as PowerPact, Synergy and Protector Series
- Free mobile app for iOS® and Android™ devices available on iTunes® App Store, GooglePlay™, and Amazon AppStore

Log onto MobileLinkGen.com to learn more.

“MY FAMILY'S GOING TO BE SAFE AND SECURE
IN MY HOUSE BECAUSE OF THIS GENERATOR.”

- Greg Beappler



Remote Monitor

No need to go outside during inclement weather to check your generator's status. Completely wireless and battery powered, Generac's Wireless Monitor provides you with instant status information without ever leaving the house. Basic features include:

- Red, yellow and green status indicator lights with buzzer function to alert owners when the generator needs attention
- Audible alert when battery is low
- Compact sleek design and magnetic backed for refrigerator mounting
- 600-foot line of sight communication



Cold Weather Kit

If the temperature falls below 0° F, install a cold weather kit to maintain optimal battery and engine oil temperature. Kit contains a thermostat-controlled battery pad and engine-block warmer.

Scheduled Maintenance Kits

A scheduled maintenance program ensures the generator system is always in top operating condition and warranty requirements are being met. Generac's scheduled maintenance kits provide all the hardware necessary to perform complete routine maintenance on a Generac automatic standby generator. Oil must be purchased separately based upon manufacturer recommendations listed below. Maintenance is recommended at every 200 hours or 2 years.

Kit contents may vary by model. Kits Include:

- Air Filter
- Oil Filter
- Spark Plugs
- Oil Funnel
- Chamois
- Reminder Sticker



Extended Warranty

Up to five years extended warranty coverage available through Generac Industrial and Residential/Commercial Dealers, on generators ranging from 9 to 150 kW (7 and 10 year options available).

For more accessories, visit Generac.com or see the table on page 23.

Specifications

Enhance your Generac standby generator's performance with accessories from the leader in standby power. Products are available to maximize convenience and simplify maintenance for years of reliable standby power.

Automatic Standby Generators - Air-Cooled

	PowerPact		Guardian Series				Synergy EcoGen	
Pre-packaged models	6998 / 6999	7030	7032	7036	N/A	N/A	7040	N/A
Non pre-packaged models	N/A	7029	7031	7035	7038	7042	N/A	7034
Rated Power (LPG/NG)	7.5 / 6 kW	9 / 8 kW	11 / 10 kW	16 / 16 kW	20 / 18	22/19.5	20/18kW	15 / 15KW
Voltage (Single Phase)	240V	240V	240V	240V	240V	240V	240V	240V
Amps @ 240V LPG	31.25	33.3	45.8	66.6	83.3	91.6	83.3	62.5
Amps @ 240V NG	25.0	29.2	41.7	66.6	75	781.25	75	62.5
Engine/Alternator RPM	3600 / 3600	3600 / 3600	3600 / 3600	3600 / 3600	3600 / 3600	3600 / 3600	2700-3600	2700-3600
Engine	OHV / 420cc	G-Force / 426c	G-Force / 530cc	G-Force / 999cc	G-Force / 999cc	G-Force / 999cc	G-Force / 999cc	G-Force / 999cc
Fuel Consumption @ full load LPG cu. ft/hr (gal. hr)	51.6 (1.42)	51.6 (1.42)	70 (1.92)	130 (3.57)	140 (3.85)	133 (3.68)	116 (3.19)	116 (3.19)
Fuel Consumption @ Full Load NG cu. ft/hr (gal. hr)	117	120	159	309	301	310	312	312 (8.83)
Quiet-Test Mode	No	No	No	Yes	Yes	Yes	Yes	No
db(A) at Exercise	69	62	63	60	60	58	57	63
db(A) at Normal Operating Load	67	62	63	66	66	67	63	63
Automatic Transfer Switch	50 Amp	100 Amp	100 Amp	100 Amp	NA	NA	200 Amp	NA
Circuits Included	8	16	16	16	16	16	16	16
Enclosure	Aluminum	Aluminum	Aluminum	Aluminum	Aluminum	Aluminum	Aluminum	Aluminum
Enclosure Color	Bisque	Bisque	Bisque	Bisque	Bisque	Bisque	Bisque	Bisque
Warranty	3 Year Limited	5 Year Limited	5 Year Limited	5 Year Limited	5 Year Limited	5 Year Limited	5-Year Limited	3-Year 2000 Hour Limited
Dimensions (L" x W" x H")	36 x 27 x 25	48 x 25 x 29	48 x 25 x 29	48 x 25 x 29	48 x 25 x 29	48 x 25 x 29	48 x 25 x 29	48 x 25 x 29
Generator Weight (lbs.)	280	360	407	471	451	476	471	526
CARB Compliant	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes
Transfer Switch Weight (lbs.)	N/A	53.5	57 / 39	68	39	39	39	NA

* Rating definitions - Standby: Applicable for supplying emergency power for the duration of the charging period. No overload capability is available for this rating. (All ratings in accordance with BS5514, ISO3046 and DIN6271). * Maximum wattage and current are subject to and limited by such factors as fuel Btu content, ambient temperature, altitude, engine power and condition, etc. Maximum power decreases about 3.5 percent for each 1,000 feet above sea level; and also will decrease about 1 percent for each 12° C (10° F) above 15.5° C (60°F). Not for sale in California.

Automatic Standby Generators - Protector Series Liquid-Cooled

Model Number	RG02515ANAX	RG03015ANAX	RG03624ANAX	RG04524ANAX	RG04524ANAX	RG06024ANAX	RG06024AVAX
Rated Power (LPG/NG)	25/25 kW	30/30 kW	36/36	45/45 kW	45/45 kW	60/60 kW	60/60 kW
Voltage (Single Phase)	240V	240V	2400	240V	240V	240V	240V
Amps @ 240V LPG	104	125	150	188	188	N/A	250
Amps @ 240V NG	104	112.5	150	188	188	250	N/A
Engine/Alternator RPM	3600 / 3600	3600 / 3600	3600 / 3600	3600 / 3600	3600 / 3600	3600 / 3600	3600 / 3600
Engine	In-line 4-Cyl.	In-line 4-Cyl.	In-line 4-Cyl.	In-line 4-Cyl.	In-line 4-Cyl.	In-line 4-Cyl.	In-line 4-Cyl.
Fuel Consumption @ full load - LPG cu. ft/hr (gal/hr)	155 (4.3)	187 (5.1)	231 (5.4)	290 (8.0)	290 (8.0)	N/A	327 (9.0)
Fuel Consumption @ full load - NG cu. ft/hr	390	470	626	730	730	862	N/A
Quiet-Test Mode	Yes	Yes	Yes	Yes	Yes	Yes	Yes
db(A) at Exercise	62	62	61	61	61	65	65
db(A) at Normal Operating Load	72	72	70	73	73	72	72
Automatic Transfer Switch	Not Included	Not Included	Not Included	Not Included	Not Included	Not Included	Not Included
Enclosure	Aluminum	Aluminum	Alum	Aluminum	Aluminum	Aluminum	Aluminum
Enclosure Color	Bisque	Bisque	Bisque	Bisque	Bisque	Bisque	Bisque
Warranty	5 Year Limited	5 Year Limited	5-Year Limited	5 Year Limited	5 Year Limited	5 Year Limited	5 Year Limited
Dimensions (L" x W" x H")	62.2 x 29 x 33.5	62.2 x 29 x 33.5	77 x 33.5 x 45	77 x 33.5 x 45	77 x 33.5 x 45	77 x 33.5 x 45	77 x 33.5 x 45
Generator Weight (lbs.)	875	935	1414	1414	1414	1441	1441
SCAQMD Model	•	•	•		•		

Automatic Standby Generators - Protector Series Liquid-Cooled

Model Number	RG02224ANAX	RG02724ANAX	RG03224ANAX	RG03624ANAX	RG03824ANAX	RG04842ANAX	RG04842ANAX
Rated Power (LPG/NG)	22/22 kW	27/25 kW	32/32	36/35 kW	32/32	48/48 kW	48/48 kW
Voltage (Single Phase)	240V	240V	2400	240V	2400	240V	240V
Amps @ 240V LPG	92	112	133	150	158	200	200
Amps @ 240V NG	92	104	133	146	158	192	192
Engine/Alternator RPM	1800/1800	1800/1800	1800/1800	1800/1800	1800/1800	1800/1800	1800/1800
Engine	In-line 4-Cyl.	In-line 4-Cyl.	In-line 4-Cyl.	In-line 4-Cyl.	In-line 4-Cyl.	V-6	V-6
Fuel Consumption @ full load - LPG cu. ft/hr (gal/hr)	125 (3.4)	143 (3.9)	166 (4.6)	200 (5.5)	192 (5.4)	260 (7.20)	260 (7.20)
Fuel Consumption @ full load - NG cu. ft/hr	316	359	380.6	503	444	655	655
Quiet-Test Mode	Yes	Yes	Yes	Yes	Yes	Yes	Yes
db(A) at Exercise	61	62	58	58	58	60	60
db(A) at Normal Operating Load	70	75	64	64	64	65	65
Automatic Transfer Switch	Not Included	Not Included	Not Included	Not Included	Not Included	Not Included	Not Included
Enclosure	Aluminum	Aluminum	Aluminum	Aluminum	Aluminum	Aluminum	Aluminum
Enclosure Color	Bisque	Bisque	Bisque	Bisque	Bisque	Bisque	Bisque
Warranty	5 Year Limited	5 Year Limited	5 Year Limited	5 Year Limited	5-Year Limited	5 Year Limited	5 Year Limited
Dimensions (L" x W" x H")	62.2 x 29 x 33.5	62.2 x 29 x 33.5	77x33.5x45	77 x 33.5 x 45	77x33.5x45	77 x 33.5 x 45	77 x 33.5 x 45
Generator Weight (lbs.)	843	891	1225	1271	1235	1360	1360
SCAQMD Model	•	•					•

*Units not designated as meeting South Coast Air Quality Management District (SCAQMD) emission requirements are not available for sale in CA or MA.

Protector Series Generators - Diesel

60 Hz Model	RD015	RD020	RD030	RD048*/RD050
Rated Power	15 kW	20 kW	30 kW	48 / 50 kW
Engine Alternator RPM	1800/1800	1800/1800	1800/1800	1800/1800
Engine	In-line 4-Cyl.	In-line 4-Cyl.	In-line 4-Cyl.	In-line 4-Cyl.
Fuel Type	Diesel	Diesel	Diesel	Diesel
Output Amperage 120/240 V, 1 ϕ 1.0 pf	62	83	125	200
Output Amperage 120/208 V, 3 ϕ 0.8 pf	52	69	104	173
Output Amperage 120/240 V, 3 ϕ 0.8 pf	45	60	90	150
Output Amperage 277/480 V, 3 ϕ 0.8 pf	n/a	n/a	45	75
Fuel Consumption @ 1/2 load - gal/hr (L/hr)	0.79 (2.99)	1.05 (3.97)	1.45 (5.5)	2.15 (8.14)
Fuel Consumption @ full load - gal/hr (L/hr)	1.48 (5.58)	1.98 (7.48)	2.74 (10.4)	3.98 (15.07)
Quiet-Test Mode	Yes	Yes	Yes	Yes
db (A) at exercise	65	65	65	65
db (A) at normal operating load	70	70	70	70
Enclosure	Aluminum	Aluminum	Aluminum	Aluminum
Enclosure Color	Bisque	Bisque	Bisque	Bisque
Warranty	5 Year Limited	5 Year Limited	5 Year Limited	5 Year Limited
Dimensions L"x W"x H" (in)	63 x 31 x 51	63 x 31 x 51	77 x 35 x 54	77 x 35 x 54
Weight (lbs.)	1449	1474	1685	2066

*1 ϕ

Transfer Switches

	AMPS	MODEL	240V, 2-POLE PHASE / DESCRIPTION	RATING
SMART SWITCHES	100	RTSC100A3	Non-service rated transfer switch	UL / CUL
	100	RTSW100A3	Service rated transfer switch	UL
	150	RTSW150A3	Service rated transfer switch	UL
	200	RTSP200A3	Non-service rated transfer switch	UL / CUL
	200	RTSW200A3	Service rated transfer switch	UL
	200	RTSW200A3F	200 amp service rated with integrated load center	UL
	300	RTSW300A3	Service rated transfer switch	UL
	400	RTSC400A3	Non-service rated transfer switch	UL / CUL
	400	RTSW400A3	Service rated transfer switch	UL
	600	RTSC600A3	Non-service rated transfer switch	UL / CUL
800	RTSC800A3	Non-service rated transfer switch	UL / CUL	
CSA SWITCH	100	RTSE100A3CSA	CSA approved service-rated	CSA
	200	RTSE200A3CSA	CSA approved service-rated	CSA
LIMITED CIRCUIT	50	RTG10EZA1	10 circuit load center, includes all wire, circuit breakers, and conduit for installation, NEMA 1 rated	UL / CUL
	100	RTG16EZA1	16 circuit load center, includes all wire, circuit breakers, and conduit for installation, NEMA 1 rated	UL / CUL
	100	RTG16EZA3	16 circuit load center, expandable to 24 with use of tandem breakers, NEMA 3 rated	UL / CUL
GENREADY	100 / 200	RTG24SHA1 / RTG42SHA1 Whole House SER Transfer Switch and Load Center	100 Amp NEMA 1 with 24 space, 40 Circuit / 200 Amp NEMA 1 with 42 space, 60 Circuit	UL
	N/A	5447 GenReady EZ Transfer Operator	EZ Operator install into 5448 to give automatic switch functionality	UL
	200 / 125	5449 GenReady with EZ Transfer Operator	200 Amp, 40 circuit combination electrical panel / transfer switch with the EZ Operator already installed	UL
	200 / 125	5454 GenReady with EZ Operator NEMA 3R	200 Amp, 40 circuit combination electrical panel / transfer switch with the EZ Operator already installed	UL
	200 / 125	5453 GenReady with EZ Operator NEMA 3R	200 Amp, 40 circuit combination electrical panel / transfer switch with the EZ Operator already installed	UL

.....

For more information, such as
FAQ's, visit us online at
www.generac.com

.....

THE | GENERAC
PROMISE



* Built in the USA using domestic and foreign parts.

Generac Power Systems, Inc.
S45 W29290 Hwy. 59, Waukesha, WI 53189
1-888-GENERAC (1-888-436-3722)

0200680SBY 04/2017 ©2017 Generac Power Systems, Inc.
All rights reserved. Specifications are subject to change without notice.



generac.com