

INSTRUMENTATION CABLE

Multiconductor -300 Volt
Overall Aluminum Shield
Polyethylene Insulation



CONSTRUCTION

Conductor	- Stranded tinned copper
Insulation	- Polyethylene Insulated, twisted Pair
Shield	- 100% aluminum foil/polyester with stranded tinned copper drain wire
Jacket	- Chrome PVC

COLOR CODE CHART

Cond. #	Color
1	Black
2	Clear

Applications:

- Paired cables allow balanced signal transmission which results in lower crosstalk through common mode rejection Due to the improved noise immunity of twisted pairs, they generally permit higher data speeds than multi-conductor cables

Standards:

- CEC CM
- NEC type CM
- 300 Volt rated
- 60C rated

Part #	AWG	Pairs	Stranding	Insulation Thickness	Jacket Thickness	Nom. O.D.	Lbs./M'
D12202	22	1	7 \times 0 TC	.016"	.025"	.167"	17
D12202-BS	22	1	7 \times 0 TC	.016"	.026"	.180"	21

Note: The data shown is approximate and subject to standard industry and manufacturer tolerances.