

PAR38 17W 277V TITANIUM CRI^{SP} LED SERIES 4.0



CRI^{SP}



17W REPLACES



120W
Hal.

80% Energy Savings

\$331 Savings
per lamp*

- Direct line voltage 120-277V - Not compatible with ballasts
- Exceptional color rendering CRI 90
- Richer reds and natural skin tones (R9 50, R13 90)
- Tight LED binning for consistent CCT across all lamps
- Suitable for use in totally enclosed fixtures
- Wet location rated for outdoor use



LM 79

LM 80

TM 21



PATENT PENDING REFINE OPTIC

The innovative REFINE optic provides a high candela to lumen ratio, optimizing light usage for directional applications.



REFLECTOR
Directs light



FOCUS LENS
Focuses center beam

SHAPING LENS
Refines beam pattern




WATCH THE VIDEO

PAR38 17W 277V TITANIUM CRI^{SP} LED SERIES 4.0




ILLUMINANCE & CANDELA DISTRIBUTION


17PAR38G4/930FL40/277V



17PAR38G4/940FL40/277V



Base: E26
Voltage: 120-277V
Dimmable: No
PF: 0.9
Lifetime: 40,000 hrs
Weight: 0.75lb / 340g



SPECIFICATIONS

Model	Product	Power (W)	CCT	CRI (typ.)	R9 / R13 (typ.)	Lumens	LPW	Beam Angle	CBCP (cd)
17PAR38G4/930FL40/277V	16161	17	Warm White 3000K	90	50 / 90	1150	68	FL 40°	2500
17PAR38G4/940FL40/277V	16164	17	Natural White 4000K	90	50 / 90	1200	71	FL 40°	2650

* Savings per lamp based on \$0.11 / kw energy cost, 12 hrs / day lamp usage, \$8 halogen with 1500-hr lifetime, \$32 LED with 40,000-hr lifetime

** Suitable for use in totally enclosed fixtures

*** Suitable for wet locations