



The right vertical solution for any situation.

## Bring Wire & Cable Down to Business

Routing power, data, and A/V – neatly and simply – from up there to down here; that's what Tele-Power® Poles are all about. Their sole purpose is to get the business end of your wire and cabling needs down to your workstation, equipment, or modular furniture. Specifically, in away-from-the-wall locations in open commercial office areas, schools, labs, stores and other sites.

Whatever power, data, or A/V wiring you need to bring down to the desk, workstation, or cash registers, Wiremold Tele-Power Poles handle all of your needs effortlessly. For modular office furniture – our poles easily provide the hook up to feed office partitions. The poles are also available with specialized electrical circuits such as dedicated/isolated ground. Vertical drop poles give you the flexibility and capacity to devote both sides of the pole for single or dual service feeds. Legrand/Wiremold offers the broadest selection of open space solutions. With standard, custom and configurable products, you can rest assured that the right solution is readily available and adaptable to your current and future work environments.

## Features & Benefits

- **Promotes sustainable design.** Allowing services to be routed to the center of an open space rather than by building a wall increases the use of natural daylight and reduces energy consumption.
- **Bring power, data, and A/V services into open space environments quickly & easily.** Easy to install. Reduces costs for moves, adds and changes.
- **Wide selection of standard options.** Stocked in a variety of materials, finishes, sizes, and device configurations. Provides what you want, when you need it.
- **Relocatable.** Ready for service in 30 minutes or less. Can be quickly reconfigured or relocated as work space uses and service needs change.
- **Dual-channel.** Allows a single drop point for access to multiple services.
- **Accessory packs included.** Furnished with feed fittings, ceiling trim plates, T-Bar mounting hardware, and carpet/floor grippers. Everything you need for a complete and stationary installation accommodating a variety of installation scenarios.
- **Multiple color options.** Available in four aesthetic colors: white (WH), black (BK), ivory and gray (DG).
- **Custom capabilities.** Modify receptacle type and location, change color finish, alter pole heights, add fixture whips and more. Affording you more choice in appearance and configuration.
- **On-site configurability.** In-field modifications, including adding devices and changing the height, make Tele-Power poles even more flexible.
- **A/V Compatibility.** 30TP Series are now compatible with A/V devices to allow for a full range of services to your work stations.
- **Datacom connectivity options.** Accepts industry standard and proprietary devices from a wide range of manufacturers to provide a seamless, aesthetically pleasing interface for voice, data, audio, and video applications at the point of use.
- **New TPP-E Series Tele-Power Pole Extenders combine quick installation with easy job-site handling.** Snap together 5' sections to create a pole or extend the length of your existing 25TP & 25DTC Series poles. These new extenders accommodate a variety of ceiling heights, can ship UPS or air freight for quick & reliable delivery.

## Vertical Markets

- Commercial
- Education
- Retail



Download this product's PEP ecosport® environmental product declaration at [www.legrand.us/resources-and-downloads](http://www.legrand.us/resources-and-downloads). This declaration conforms with ISO 14025 and 14040 and is in alignment with EN 15804.

## Compliance



cULus Listed, Multioutlet Assemblies: File E15191, E178348. Guide RJPR. Meets Articles 380 & 386 of NEC  
Raceway Fittings: File E41751. Guide RJPR  
Accessories: File E53857, Guide RVUR.

## Field Modifications for Tele-Power Poles

MODIFICATION	TELE-POWER POLE SERIES									
	30TP-4V	30TC-4V	30TP-2V	30TC-2V	25DTP-4	25DTP-4D	25DTC-4	AMDTP-4	AMDTP-4D	AMTC-4
Can the receptacles in the standard pole be rewired in order to have a two circuit pole with standard duplexes?	Yes	N/A	Yes	N/A	No	Yes	N/A	No	Yes	N/A
Can the receptacles in the standard pole be replaced with other types? (i.e. Hospital Grade, TVSS, GFCI, etc.)	Yes – Using the proper device cover	N/A	Yes – Using the proper device cover	N/A	Yes – with 2507C Bracket & only with NEMA duplex receptacles	Yes – Only with NEMA duplex receptacles	N/A	Yes – With 2507C Bracket & only with NEMA duplex receptacles	Yes – Only with NEMA duplex receptacles	N/A
Can receptacles be added to blank poles?	N/A	Yes	N/A	Yes – Using the proper device cover	N/A	N/A	Yes	N/A	N/A	Yes
Can blank poles be used for furniture feed applications by field punching KOs on poles for power and voltage?	N/A	Yes	N/A	Yes	N/A	N/A	Yes	N/A	N/A	Yes
Can more than one add-on device cover be used?	N/A	N/A	N/A	N/A	Yes	Yes	N/A	Yes	Yes	N/A
Can receptacles be installed in both sides of the pole?	Yes – Power only on both sides	Yes – Power only on both sides	N/A	N/A	No	No	N/A	No	No	N/A
Can poles be field cut for use in lower ceiling applications?	Yes*	Yes*	Yes*	Yes*	Yes*	Yes*	Yes*	Yes*	Yes*	Yes*
Can poles be mounted to hard or open ceilings?	Yes**	Yes**	Yes**	Yes**	Yes**	Yes**	Yes**	Yes**	Yes**	Yes**

\* Review instruction sheet for instructions for cutting poles.

\*\* Pole housing cannot be penetrated. Ceiling mounting hardware must provide firm support and must be supplied by installer.


**NOTE:** All receptacles, additions, rewiring and other electrical modifications must be made by a qualified electrician in accordance with the NEC or other applicable local codes and adhering to the wire fill capacity charts for the respective pole.



Specially-designed Tele-Power Poles can be fitted with lighted signage while also bringing power and data to cash wraps and counter areas, or used to feed services to display cases, photo kiosks and price check stations.

## Steel Tele-Power Poles

Steel Tele-Power Poles are the workhorse of vertical wire and cable management solutions. They are available either prewired with electrical devices or as blanks to feed services to other wire and cable management systems, such as electrified modular furniture. As the long time industry standard, steel Tele-Power Poles are available with an ivory enamel finish and are available in a variety of lengths. They also offer the flexibility of field configuration or can be customized to customer specifications.



**NOTE:** For the 25DTP custom colors, other lengths (20' (6.1m) max.) or additional circuits are available on custom orders. Consult factory for more information. Can be factory or field wired with many commercially available devices.

For the 30TP-2V and 30TP-4V custom colors or additional circuits are available on custom orders. Consult factory for more information. Can be factory or field wired with many commercially available devices.

**25DTP & 30TP Series Tele-Power Poles Wire Fill Capacities**


CATALOG NUMBER	NUMBER & TYPE OF POWER OUTLETS	POLE HEIGHT Inches (mm)	FINISH	Wire Size		Cat 5		Cat 6		RG58/U		RG62A/U		RG6/U	
				THHN/THWN #10	THHN/THWN #12	0.22" (5.6mm) 20%*	0.22" (5.6mm) 40%**	0.25" (6.3mm) 20%*	0.25" (6.3mm) 40%**	0.195" (5.0mm) 20%*	0.195" (5.0mm) 40%**	0.242" (6.1mm) 20%*	0.242" (6.1mm) 40%**	0.270" (6.9mm) 20%*	0.270" (6.9mm) 40%**
25DTP-4	Two Duplex Receptacles (20A, 125V)	10' 5" (3.175m)	Ivory, Gray, White, Black	10	15	10	19	9	17	13	25	8	16	7	13
25DTP-412		12' 5" (3.780m)		10	15	10	19	9	17	13	25	8	16	7	13
25DTP-415		15' 5" (4.700m)		10	15	10	19	9	17	13	25	8	16	7	13
25DTP-E10		10' 5" (3.175m)	Ivory, Gray	10	15	10	19	9	17	13	25	8	16	7	13
25DTP-4D	Two Duplex Receptacles (20A, 125V), One Dedicated/ Isolated & One Standard Branch Circuit	10' 5" (3.175m)	Ivory, Gray	10	15	10	19	9	17	13	25	8	16	7	13
25DTP-4ACT	Two Duplex Receptacles (20A, 125V), One Communications Insert Mounting Adapter, Three Blank Inserts	10' 5" (3.175m)	Ivory, Gray	10	15	10	19	9	17	13	25	8	16	7	13
30TP-2V	Two Duplex Receptacles (20A, 125V)	10' 5" (3.175m)	Ivory	8	12	16	31	13	26	20	40	13	25	10	20
30TP-212V		12' 5" (3.780m)	Ivory	8	12	16	31	13	26	20	40	13	25	10	20
30TP-215V		15' 5" (4.700m)	Ivory	8	12	16	31	13	26	20	40	13	25	10	20
30TP-4V	Two Duplex Receptacles (20A, 125V)	10' 5" (3.175m)	Ivory	30	48	19	37	15	30	24	47	15	30	12	24
30TP-412V		12' 5" (3.780m)	Ivory	30	48	19	37	15	30	24	47	15	30	12	24
30TP-4V3S2		10' 5" (3.175m)	Ivory	30	48	19	37	15	30	24	47	15	30	12	24
30TP-412V3S2		12' 5" (3.780m)	Ivory	30	48	19	37	15	30	24	47	15	30	12	24

\* 20% cable fill is calculated to approximate reduction in cable capacity due to connectors mounted within pole section that may restrict cross-sectional areas.

\*\* 40% cable fill is the maximum designed cable fill based on a proposed revision to TIA/EIA 569-A.


## Steel Tele-Power Poles Ordering Information

Catalog No./Item	Description/Specifications
<b>25DTP-4</b> <b>25DTP-4WH</b> <b>25DTP-4BK</b> <b>25DTP-4DG</b> <b>25DTP-412</b> <b>25DTP-412WH</b> <b>25DTP-412BK</b> <b>25DTP-412DG</b> <b>25DTP-415</b> <b>25DTP-415WH</b> <b>25DTP-415BK</b> <b>25DTP-415DG</b>	<p><b>Tele-Power Pole – Two-compartment pole (power and communications).</b> Nominal material thickness .030" (0.8mm). Ivory, white, black or gray bootbase. Factory wired with fed-spec general grade 20A125V duplex style receptacles. An 8" (203mm) cover at top front of pole is removable for making power wiring connections. KOs provided in removable cover for RJ11/RJ45 and modular furniture communication connectors. Mounting hardware, entrance end plate and two ceiling trim plates furnished. Available in standard lengths of 10' 5" (3.2m) (25DTP-4), 12' 5" (3.8m) (25DTP-412) and 15' 5" (4.7m) (25DTP-415). Also increase the length of any 25 Series pole with the 25DTC-E5 Tele-Power Pole Extender.</p>



**Country of Origin: USA**


**25DTP-4ACT**  
**25DTP-4ACT-DG**



**Tele-Power Pole – Tele-Power Pole – Two-compartment pole (power and communications).** Nominal material thickness .030" (0.8mm). Ivory, white, black or gray bootbase. Factory wired with fed-spec general grade 20A125V duplex style receptacles. An 8" (203mm) cover at top front of pole is removable for making power wiring connections. KOs provided in removable cover for one (1) communications insert and three (3) blank inserts. Mounting hardware, entrance end plate and two ceiling trim plates furnished. Available in standard lengths of 10' 5" (3.2m) (25DTP-4), 12' 5" (3.8m) (25DTP-412) and 15' 5" (4.7m) (25DTP-415). Also increase the length of any 25 Series pole with the 25DTC-E5 Tele-Power Pole Extender.


**Country of Origin: USA**

Catalog No./Item	Description/Specifications
<b>25DTP-4D</b> <b>25DTP-4D-DG</b>	<p><b>Tele-Power Pole – Two-compartment pole (power and communications).</b> Nominal material thickness .030" (0.8mm). Ivory, white, black or gray bootbase. Factory wired with one (1) 20A 125V dedicated/isolated ground duplex receptacle and one (1) 20A 125V standard duplex receptacle. An 8" (203mm) cover at top front of pole is removable for making power wiring connections. KOs provided in removable cover for oRJ11/RJ45 and modular furniture communication connectors. Mounting hardware, entrance end plate and two ceiling trim plates furnished. Available in standard lengths of 10' 5" (3.2m) (25DTP-4), 12' 5" (3.8m) (25DTP-412) and 15' 5" (4.7m) (25DTP-415). Also increase the length of any 25 Series pole with the 25DTC-E5 Tele-Power Pole Extender.</p>



**Country of Origin: USA**

**25DTP-E10**  
**25DTP-E10-DG**






**Blank Steel Express Pole –** Two sections of a two-compartment (power and communication) pole (5' 4" [1.626m] base + 5' [1.524m] extender) assemblies to form a 10' 4" [3.148m] pole. Nominal material thickness .040" [1.0mm]. Ivory or gray boot base. Factory-wired with fed-spec general grade 20A 125V duplex style receptacles. An 8" [203mm] cover at top front (power side) of pole is removable for making power wiring connections. KOs provided in removable cover for RJ11/RJ45 and modular furniture communication connectors. Mounting hardware, entrance end plate and two ceiling trim plates furnished.

**Country of Origin: USA**


**NOTE:** Custom colors, custom lengths (20' (6.1m) max.) or additional circuits are available on custom order. Consult factory for more information. Can be factory or field-wired with many commercially available devices.

## Steel Tele-Power Poles Ordering Information

Catalog No./Item	Description/Specifications	Catalog No./Item	Description/Specifications
<b>30TP-2V</b> <b>30TP-212V</b> 	<p><b>Tele-Power Pole</b> – Two-30TP-212V compartment pole (power and communications). Nominal material thickness .040" (1.0mm). Factory wired with two specification grade 20A, 125V duplex receptacles. Mounting hardware, entrance end fitting, and ceiling trim plate furnished. Available in standard lengths of 10' 5" (3.2m) (30TP-2V) and 12' 5" (3.8m) (30TP-212V).</p> <p><b>Country of Origin: USA</b></p>	<b>30TP-4V3S2</b> <b>30TP-412V3S2</b> 	<p><b>Tele-Power Pole</b> – Two duplex 30TP-412V3S2 receptacles (20A, 125V). One Ortronics® Series II adapter. One Ortronics® Series II dual Cat. 5e insert, two blank inserts and labeling supplies. Available in standard lengths of 10' 5" (3.2m) (30TP-4V3S2) and 12' 5" (3.8m) (30TP-412V3S2).</p> <p><b>Country of Origin: USA</b></p>
<b>30TP-4V</b> <b>30TP-412V</b> 	<p><b>Tele-Power Pole</b> – Two-30TP-412V compartment pole (one power; one communication with crossover below power devices). Nominal material thickness .040" (1.0mm). Factory wired with two specification grade 20A, 125V duplex receptacles. Mounting hardware, entrance end fitting, and ceiling trim plate furnished. Available in standard lengths of 10' 5" (3.2m) (30TP-4V) and 12' 5" (3.8m) (30TP-412V).</p> <p><b>Country of Origin: USA</b></p>		

**NOTE:** Custom colors, custom lengths (20' (6.1m) max.) or additional circuits are available on custom order. Consult factory for more information. Can be factory or field-wired with many commercially available devices.

## Steel Blank Tele-Power Poles








**NOTE:** For the 25DTC custom colors, other lengths (20' (6.1m) max.) or additional circuits are available on custom orders. Consult factory for more information. Can be factory or field wired with many commercially available devices.

For the 30TC-2V and 30TC-4V custom colors or additional circuits are available on custom orders. Consult factory for more information. Can be factory or field wired with many commercially available devices.

25DTC & 30TC Series Vertical Drop Poles Communications Fill Capacities													
CATALOG NUMBER	POLE HEIGHT Inches (mm)	FINISH	Cat 5 0.22" (5.6mm)		Cat 6 0.25" (6.3mm)		RG58/U 0.195" (5.0mm)		RG62A/U 0.242" (6.1mm)		RG6/U 0.270" (6.9mm)		
			Sm. Comp.	Lg. Comp.	Sm. Comp.	Lg. Comp.	Sm. Comp.	Lg. Comp.	Sm. Comp.	Lg. Comp.	Sm. Comp.	Lg. Comp.	
25DTC-4	10' 5" (3.175m)	Ivory, Gray,	19	26	16	22	25	33	16	21	12	17	
25DTC-412	12' 5" (3.780m)	Black,	19	26	16	22	25	33	16	21	12	17	
25DTC-415	15' 5" (4.700m)	White	19	26	16	22	25	33	16	21	12	17	
25DTC-E10	10' 5" (3.175m)	Ivory, Gray	19	26	16	22	25	33	16	21	12	17	
30TC-2V	10' 5" (3.175m)	Ivory	n/a	33	n/a	30	n/a	47	n/a	30	n/a	24	
30TC-212V	12' 5" (3.780m)	Ivory	n/a	33	n/a	30	n/a	47	n/a	30	n/a	24	
30TC-215V	15' 5" (4.700m)	Ivory	n/a	33	n/a	30	n/a	47	n/a	30	n/a	24	
30TC-4V	10' 5" (3.175m)	Ivory	37	37	30	30	47	47	30	30	24	24	
30TC-412V	12' 5" (3.780m)	Ivory	37	37	30	30	47	47	30	30	24	24	
30TC-415V	15' 5" (4.700m)	Ivory	37	37	30	30	47	47	30	30	24	24	
30TC-3S2	10' 5" (3.175m)	Ivory	37	37	30	30	47	47	30	30	24	24	
30TP-412V3S2	12' 5" (3.780m)	Ivory	37	37	30	30	47	47	30	30	24	24	



## Steel Tele-Power Poles Ordering Information

Catalog No./Item	Description/Specifications	Catalog No./Item	Description/Specifications
<b>25DTC-4</b> <b>25DTC-4WH</b> <b>25DTC-4BK</b> <b>25DTC-4DG</b> <b>25DTC-412</b> <b>25DTC-412WH</b> <b>25DTC-412BK</b> <b>25DTC-412DG</b> <b>25DTC-415</b> <b>25DTC-415WH</b> <b>25DTC-415BK</b> <b>25DTC-415DG</b>	 <p><b>Blank Steel Pole</b> – Two-compartment pole. Nominal material thickness .040" (1.0mm). Ivory, white, black or gray boot base. Furnished unwired without outlets. Mounting hardware, entrance end plate and ceiling trim plates furnished. Available lengths: 10' 5" (3.2m) (25DTC-4), 12' 5" (3.8m) (25DTC-412) and 15' 5" (4.7m) (25DTC-415).</p> <p><b>Country of Origin: USA</b></p>	<b>25DTC-E10</b> <b>25DTC-E10-DG</b>	 <p><b>Blank Steel Express Pole</b> – Two sections of a two-compartment pole (5' 4" (1.626m) base and 5' (1.52m) extender) assemblies to form a 10' 4" (3.148m) pole. Nominal material thickness .040" (1.0mm). Ivory or gray boot base. Furnished unwired without outlets. Mounting hardware, entrance end plate and ceiling trim plate furnished. An 8" (203mm) cover at top of pole is removable for making power wiring connections.</p> <p><b>Country of Origin: USA</b></p>
<b>30TC-2V</b> <b>30TC-212V</b> <b>30TC-215V</b>	 <p><b>Blank Steel Pole</b> – Single-compartment pole. Furnished unwired without outlets. Nominal wall thickness .040" (1.0mm). Mounting hardware, entrance end fitting, and ceiling trim plate furnished. Available lengths: 10' 5" (3.2m) (30TC-2V), 12' 5" (3.8m) (30TC-212V) and 15' 5" (4.7m) (30TC-215V).</p> <p><b>Country of Origin: USA</b></p>	<b>25DTC-E5</b> <b>25DTC-E5WH</b> <b>25DTC-E5BK</b> <b>25DTC-E5DG</b>	<p><b>Blank Steel Pole Extender</b> – Two-compartment extender mounts onto existing 25DTP or 25DTC series pole. Nominal material thickness .040" (1.0mm). Furnished unwired without outlets. Uses existing pole mounting hardware, entrance end plate and ceiling trim plate. Available in 5' (1.524m) length. Can be cut to desired length.</p> <p><b>Country of Origin: USA</b></p>
<b>30TC-4V</b> <b>30TC-412V</b> <b>30TC-415V</b>	 <p><b>Blank Steel Pole</b> – Two-compartment pole. Furnished unwired without outlets. Nominal wall thickness .040" (1.0mm). Mounting hardware, entrance end fitting, and ceiling trim plate furnished. Available lengths: 10' 5" (3.2m) (30TC-4V), 12' 5" (3.8m) (30TC-412V) and 15' 5" (4.7m) (30TC-415V).</p> <p><b>Country of Origin: USA</b></p>	 <p>Front    Side    Back</p>	




New Tele-Power Pole Extenders make transporting and installing power poles a snap, literally.

**NOTE:** All poles have removable cover sections with KOs for modular jacks and openings to accept modular furniture adapters for communication devices.


## Aluminum Tele-Power Poles

When looking to dress up a vertical solution, Tele-Power Poles with a satin anodized aluminum finish in either rectangular or round styles can provide the answer. Light weight aluminum construction makes these poles easy to install and maneuver on the job site. Available prewired with electrical devices or blank to drop services feeding another wire and cable management system, such as electrified modular furniture. A full range of accessories enables field configurability, or have them delivered to your specifications.

**AMDTP-4**



**ALTP**



**NOTE:** Custom colors, other lengths (20' (6.1m) max.) or additional circuits are available on custom order. Consult factory for more information. Can be factory or field wired with many commercially available devices.

### Aluminum Tele-Power Poles Wire Fill Capacities

CATALOG NUMBER	NUMBER & TYPE OF POWER OUTLETS	POLE HEIGHT Inches (mm)	FINISH	Wire Size THHN/THWN		Cat 5 0.22" (5.6mm)		Cat 6 0.25" (6.3mm)		RG58/U 0.195" (5.0mm)		RG62A/U 0.242" (6.1mm)		RG6/U 0.270" (6.9mm)	
				#10	#12	20%*	40%**	20%*	40%**	20%*	40%**	20%*	40%**	20%*	40%**
AMDTP-4	Two Duplex Receptacles (20A, 125V)	10' 5" (3.175m)	Satin Anodized Aluminum	10	15	10	19	8	16	13	25	8	16	7	13
AMDTP-412		12' 5" (3.780m)		10	15	10	19	8	16	13	25	8	16	7	13
AMDTP-415		15' 5" (4.700m)		10	15	10	19	8	16	13	25	8	16	7	13
AMDTP-4D	Two Duplex Receptacles (20A, 125V), One Dedicated/ Isolated & One Standard Branch Circuit	10' 5" (3.175m)	Satin Anodized Aluminum	10	15	10	19	8	16	13	25	8	16	7	13
ALTP-2S	Four Single Receptacles	10' 4" (3.150m)	Satin Anodized Aluminum	—	—	2	5	2	4	3	6	2	4	1	3

\* 20% cable fill is calculated to approximate reduction in cable capacity due to connectors mounted within pole section that may restrict cross-sectional areas.

\*\* 40% cable fill is the maximum designed cable fill based on a proposed revision to TIA/EIA 569-A.

### Aluminum Vertical Drop Poles Communications Fill Capacities





CATALOG NUMBER	POLE HEIGHT Inches (mm)	FINISH	Cat 5 0.22" (5.6mm)		Cat 6 0.25" (6.3mm)		RG58/U 0.195" (5.0mm)		RG62A/U 0.242" (6.1mm)		RG6/U 0.270" (6.9mm)	
			Sm. Comp.	Lg. Comp.	Sm. Comp.	Lg. Comp.	Sm. Comp.	Lg. Comp.	Sm. Comp.	Lg. Comp.	Sm. Comp.	Lg. Comp.
AMDTP-4	10' 5" (3.175m)	Satin	10	19	8	16	13	25	8	16	7	13
AMDTP-412	12' 5" (3.780m)	Anodized	10	19	8	16	13	25	8	16	7	13
AMDTP-415	15' 5" (4.700m)	Aluminum	10	19	8	16	13	25	8	16	7	13
ALTP-2S	10' 4" (3.150m)	Aluminum	10		8		13		8		6	
NP800C-12-2B	10' 2" (3.098m)	Aluminum	<div>Please see Chart on the next page for Wire &amp; Cable Capacities of the various configurations of the NP800 Series Poles.</div>									
NP800C-12-8B	12' 8" (3.860m)											
NP800C-15-2B	15' 2" (4.620m)											



Wiremold Tele-Power Poles offer relocation flexibility to support open office designs. Quickly and easily reconfigure poles to meet changes in floor plans or capacity needs.






## Aluminum Tele-Power Poles Ordering Information

Catalog No./Item	Description/Specifications	Catalog No./Item	Description/Specifications
<b>AMDTP-4</b> <b>AMDTP-412</b> <b>AMDTP-415</b>	<p><b>Tele-Power Pole – Two-compartment pole (power and communications).</b> Nominal material thickness .050" (1.8mm). Length: 10' 5" (3.2m). Factory wired with fed-spec general grade 20A125V duplex style receptacles. An opening for communications and a 1/2" (12.7mm) hole for power is provided at top. The 8" (203mm) cover at the top front of the pole is removable for making power wiring connections. Communication KOs provided for RJ11/RJ45 and modular furniture connectors. Mounting hardware, entrance end plate and two ceiling trim plates furnished. Available in standard lengths of: 10' 5" (3.2m) (25DTP-4), 12' 5" (3.8m) (25DTP-412) and 15' 5" (4.7m) (25DTP-415).</p> <p><b>Country of Origin: USA</b></p>	 <p>Front Back</p>	<p><b>ALTP-2S</b></p>  <p>Front Back</p> <p><b>Round Tele-Power Pole – Satin anodized extruded aluminum pole.</b> Nominal wall thickness .060" (1.5mm). Length 10' 5" (3.2m). Two-compartment (power and communication channels). Factory wired with four 15A 125V NEMA 5-15R devices. Provided with one 1/2" trade size KO in cover at base for communications. T-Bar mounting hardware, ceiling trim kit, and feed box furnished.</p> <p><b>Country of Origin: USA</b></p>
<b>AMDTP-4D</b>	<p><b>Tele-Power Pole – Two-compartment pole (power and communications).</b> Nominal material thickness .050" (1.8mm). Length: 10' 5" (3.2m). Factory wired with one (1) dedicated/isolated ground duplex receptacle and one (1) 20A 125V standard duplex receptacle. An opening for communications and a 1/2" (12.7mm) hole for power is provided at top. The 8" (203mm) cover at the top front of the pole is removable for making power wiring connections. Communication KOs provided for RJ11/RJ45 and modular furniture connectors. Mounting hardware, entrance end plate and two ceiling trim plates furnished. Available in standard lengths of: 10' 5" (3.2m) (25DTP-4), 12' 5" (3.8m) (25DTP-412) and 15' 5" (4.7m) (25DTP-415).</p> <p><b>Country of Origin: USA</b></p>	 <p>Front Back</p>	<p> <b>AMDTP-4-C</b> 🇺🇸  <b>AMDTP-412-C</b> 🇺🇸  <b>AMDTP-415-C</b> 🇺🇸         </p>  <p>Front Back</p> <p><b>Tele-Power Pole – Available in Canada Only. Two-compartment pole (power and communications).</b> Nominal material thickness .050" (1.8mm). AMDTP-4-C Length: 10'5" (3.2m), AMDTP-412-C Length: 12'5" (3.8m), AMDTP-415-C Length: 15'5" (4.7m). Factory wired with 15A 125V fed-spec general grade duplex style receptacles. An opening for communication and a 1/2" (12.7mm) hole for power is provided at top. The 8" (203mm) cover at top front of pole is removable for making power wiring connections. Communication KOs provided for RJ11/RJ45 and modular furniture connectors. Mounting hardware, entrance end fitting, and ceiling trim plates furnished. Anodized aluminum finish. Maximum ceiling height 10' (3m). Comes with a 10' (3.0m) cord.</p> <p><b>Country of Origin: USA</b></p>

**NOTE:** Custom colors, custom lengths (20' (6.1m) max.) or additional circuits are available on custom order. Consult factory for more information. Can be factory or field wired with many commercially available devices.

## Aluminum Tele-Power Poles Ordering Information

Catalog No./Item	Description/Specifications	Catalog No./Item	Description/Specifications
<b>AMTC-4</b> <b>AMTC-412</b> <b>AMTC-415</b>	 <p><b>Blank Aluminum Pole – Two-compartment pole.</b> Nominal material thickness .050" (1.8mm). Furnished unwired without outlets. Two 8" (203mm) removable covers with KOs for modular jacks and modular furniture communication outlets. Mounting hardware, entrance end plate, and ceiling trim plates furnished.</p> <p>Available lengths:            AMTC-4 – 10' 5" (3.2m) ,            AMTC-412 – 12' 5" (3.8m)            AMTC-415 – 15' 5" (4.7m)</p> <p><b>CUSTOM OPTIONS:</b> Features such as colors or other lengths (20' (6.1m) maximum) available on custom orders.</p> <p><b>Country of Origin: USA</b></p>	<b>ALTC-2S</b>	 <p><b>Blank Round Aluminum Pole –</b> Satin anodized extruded aluminum pole. Nominal wall thickness .060" (1.5mm), length 10'3" (3.1mm). Provided with one 1/2" (12.7mm) trade size KO at base. T-bar mounting hardware, ceiling trim kit, foot assembly, and grommet included. Feed box not furnished.</p> <p><b>Country of Origin: USA</b></p>
<b>NP800C-10-2B</b> <b>NP800C-12-B</b> <b>NP800C-15-B</b>	 <p><b>Blank Aluminum Pole – Two-compartment large capacity pole.</b> Furnished unwired without outlets. Box ended with industry sized knockouts. Standard heights:</p> <p>NP800C-10-2B – 10'2" (3.1m)            NP800C-12-8B – 12'8" (3.9m)            NP800C-15-2B – 15'2" (4.6m)</p> <p><b>CUSTOM OPTIONS:</b> Other heights available – consult factory. 30" (762mm) communication cover with industry standard knockouts.</p> <p><b>Country of Origin: USA</b></p>		




Use Wiremold Tele-Power Poles to deliver multiple services to your desired point-of-use or simply as a feeder system for modular furniture.

## Aluminum Tele-Power Poles Ordering Information

### NP600

**Jumbo Tele-Power Pole** – Two separate compartments can accommodate up to 60A devices (#6 AWG maximum). Snap-in divider permits up to six channels of varying sizes.



Country of Origin: USA

#### General Specifications:

**Receptacles:** Each pole compartment may be wired with up to 12 receptacles, with the number of circuits limited by the feed method.

**Feed method:** All poles are provided with a utility box (4" x 4" x 2 1/8" (102mm x 102mm x 54mm)) for all poles with a cord up to 10' (3m).

**Accessories:** Ceiling trim plates, pole clamp, and non-adjustable foot with carpet gripper/adhesive pad furnished.

### NP800 SERIES WIRE FILL CAPACITIES FOR COMMUNICATIONS

CABLE TYPE Description Nom. O.D. Inches	UNSHIELDED TWISTED PAIR (24 AWG)					SHIELDED TWISTED PAIR				COAXIAL CABLE				TWINAX	FIBER*
	Cat 3 2 Pair 0.14	Cat 3 3 Pair 0.15	Cat 3 4 Pair 0.19	Cat 5 4 Pair 0.22	Cat 6 4 Pair 0.25	Cat 3 4 Pair 0.41	Type 1 22 AWG 0.39	Type 2 22 AWG 0.465	Type 3 22 AWG 0.245	RG58/U 20 AWG 0.195	RG58/U 22 AWG 0.242	RG6/U 22 AWG 0.242	RG6/U 18 AWG 0.27	100 OHM 0.33	0.19
Capacity of Cross-Section (IN²)															
2.4	62	54	33	25	19	7	8	5	20	32	20	20	16	11	33
2.8	72	63	39	29	22	8	9	6	23	37	24	24	19	13	39
3.2	83	72	45	33	26	9	10	7	27	42	27	27	22	14	45
4.2	109	95	59	44	34	12	14	9	35	56	36	36	29	19	59
4.3	111	97	60	45	34	13	14	10	36	57	37	37	30	20	60
4.8	124	108	67	50	38	14	16	11	40	64	41	41	33	22	67
5.0	129	113	70	52	40	15	16	11	42	66	43	43	34	23	70
5.2	135	117	73	54	42	15	17	12	44	69	45	45	36	23	73
5.8	150	131	81	61	46	17	19	13	49	77	50	50	40	27	81
6.2	161	140	87	65	50	18	20	14	52	83	53	53	43	28	87
7.0	181	158	98	73	56	21	23	16	59	93	60	60	48	32	98
7.7	200	174	108	81	62	23	25	18	65	103	66	66	53	36	108
8.0	207	181	112	84	64	24	26	18	67	107	69	69	55	37	112
12.0	311	271	169	126	96	36	40	28	101	160	104	104	83	56	169









\* Two Strand (Duplex) Multimode, 625/125µm. Capacity range is calculated at 40% of raceway areas as stated in the Commercial Buildings Standard for Telecommunication Pathways and Spaces, EIA/TIA 569-A.

### NP800 SERIES WIRE FILL CAPACITIES FOR POWER

	WIRE SIZE THHN/THWN	40% FILL	CIRCUITS
POWER WIRING	10 AWG	12	4
	12 AWG	13	4
	14 AWG	15	5

**NOTES:** Wire fill capacities calculated for a pole with a 4" x 4" x 2 1/8" (102mm x 102mm x 54mm) box. Larger boxes can be used if higher capacity is needed.

All of the standard profiles can be easily modified. Contact the factory or the field sales representative for specifics.



## Accessories for Tele-Power Poles Ordering Information

### Catalog No./Item

### Description/Specifications

**AMDTP-A  
25DTP-A**



**Add-On Power Cover** – Add power receptacles or devices to existing modular Tele-Power Poles. Includes receptacle mounting bracket. Face diameter of single receptacle: 1.38" - 1.40" (35mm - 36mm).

**Country of Origin: USA**

	COLOR	DIMENSIONS
<b>25DTP-A</b>	Ivory Steel (25DTP-4)	1" x 2 1/4" x 28"
<b>AMDTP-A</b>	Anodized Aluminum (AMDTP-4)	(25mm x 57mm x 711mm)

**AMDTP-B  
25DTP-B**



**Add-On Power Cover** – Add power receptacles or devices to existing modular Tele-Power Poles. Includes receptacle mounting bracket.

**Country of Origin: USA**

	COLOR	DIMENSIONS
<b>25DTP-B</b>	Ivory Steel (25DTP-4)	1" x 2 1/4" x 28"
<b>AMDTP-B</b>	Anodized Aluminum (AMDTP-4)	(25mm x 57mm x 711mm)

**AMDTP-L  
25DTP-L**



**Add-On Power Cover** – Add power receptacles or devices to existing modular Tele-Power Poles. Includes receptacle mounting bracket.

**Country of Origin: USA**

	COLOR	DIMENSIONS
<b>25DTP-L</b>	Ivory Steel (25DTP-4)	1" x 2 1/4" x 28"
<b>AMDTP-L</b>	Anodized Aluminum (AMDTP-4)	(25mm x 57mm x 711mm)

**30TP-A**



**Single Receptacle Cover** – Single receptacle cover for field installation of receptacles with face diameters of 1.38" - 1.40" (25mm - 36mm). G3007C Device Bracket included. Ivory finish.

**Country of Origin: USA**

### Catalog No./Item

### Description/Specifications

**30TP-B**



**Duplex Receptacle Cover** – For installations of 15A and 20A duplex receptacles. G3007C Device Bracket included. Ivory finish.

**Country of Origin: USA**

**30TP-C**



**Single Gang Cover** – Accepts up to 30A shallow-style device and flush plate. G3007 Device Bracket included. Ivory finish. Used to mount industry standard straight and angled communication faceplates.

**Country of Origin: USA**

**30TP-J**



**Single Receptacle Cover** – For field installation of single receptacles with face diameters of 1.56" (40mm) diameter. G3007 Device Bracket included. Ivory finish.

**Country of Origin: USA**


**30TP-L**



**Rectangular Device Cover** – Rectangular faceplate to accommodate Sentrex surge receptacles, GFCI and other decorator style devices. G3007 Device Bracket included. Ivory finish.

**Country of Origin: USA**


**25DTC-3S2**



**Data & A/V Add-On Cover for 25DTP Series Poles** – Accepts Ortronics® Series II Modular Connectivity Solutions.

**Country of Origin: USA**









**2507C**




**Receptacle Mounting Bracket** – Enables mounting of a duplex receptacle to 25DTP and AMDTP Series Tele-Power Poles.

**Country of Origin: USA**

## Accessories for Tele-Power Poles Ordering Information

Catalog No./Item	Description/Specifications	Catalog No./Item	Description/Specifications
25DTC-CVR	 <b>Data &amp; A/V Add-On Cover for 25DTP Series Poles</b> – Accepts discrete jacks.  <b>Country of Origin: USA</b>	CM-SFP	 <b>Data &amp; A/V Add-On Cover for 30TC Series Poles</b> – Single-gang faceplate accepts CM Series Connectors. (Requires 30TP-C Mounting Plate.)  <b>Country of Origin: USA</b>
30TC-CVR	 <b>Data &amp; A/V Add-On Cover for 30TC Series Poles</b> – Accepts discrete jacks.  <b>Country of Origin: USA</b>	CM-SAP	 <b>Data &amp; A/V Add-On Cover for 30TC Series Poles</b> – Single-gang, angled faceplate accepts CM Series Connectors. (Requires 30TP-C Mounting Plate.)  <b>Country of Origin: USA</b>
AMTC-CVR	 <b>Data and A/V Add-On Cover for AMDTP-4 and AMTC-4 Series Poles</b> – Accepts discrete jacks.  <b>Country of Origin: USA</b>	25AM10FO	 <b>Data &amp; A/V Add-On Cover for 25DTP Series Poles</b> – 2" (51mm) radius control Entrance End Fitting.  <b>Country of Origin: USA</b>
30TP-AAP	 <b>Add-On A/V Cover</b> – Accepts three (3) Extron® Electronics AAP plates 12" L x 2.75" W (305mm x 70mm). Includes three adapters to accommodate Ortronics® or Wiremold Open System devices.  <b>Country of Origin: USA</b>	25AM-AP	<b>Replacement Accessory Pack</b> – For 25DTP and 25DTC Series Poles. Includes: ceiling trim plate, end cap, bracket and grommet.  <b>Country of Origin: USA</b>
30TP-MAAP	 <b>Add-On A/V Cover</b> – Accepts five (5) Extron® Electronics MAAP plates 12" L x 2.75" W (305mm x 70mm). Includes three adapters to accommodate Ortronics® or Wiremold Open System devices.  <b>Country of Origin: USA</b>	20TP-AP	<b>Replacement Accessory Pack</b> – For 30TP-2 and 30TP-4 Series Poles. Includes: ceiling trim plate, bracket and grommet.  <b>Country of Origin: USA</b>

\*\* Also includes junction box attached to the 3/4" conduit.



Wiremold Tele-Power Poles offer a wide variety of custom and service configuration options to accommodate most installation requirements.







**NOTE:** All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.

---



**NOTE:** The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act complaint. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.



**Legrand, North America**  
60 Woodlawn Street  
West Hartford, CT 06110  
1.877.BY.LEGRAND (295.3472)  
[www.legrand.us](http://www.legrand.us)

**Canada**  
905.738.9195  
[www.legrand.ca](http://www.legrand.ca)

