
Essentia® Series Flat Panel

LED Flat Panel - 2' x 2'

Product Description

 $The \; Essentia ^{@} \; Series \; LED \; Flat \; Panel \; troffer \; transforms \; any \; space \; into \; a \; modern, \; visually \; comfortable \; and \; comfortable \; comfortable$ environment with superior 90 CRI light quality. The remarkably thin 2.8" (70mm) depth of the flat panel easily accommodates narrow plenums or can be suspended for a more stylish look. The 2' x 2' flat panel delivers up to 5,000 lumens of highly efficacious 100 lumens per watt light with great color quality. The enhanced optics enable the flat panel troffer to meet spaces with low glare requirements and improve the customer experience by reducing lighting fatigue.

Applications: Office, retail, education, petroleum



Initial Delivered Lumens: 3,400 - 5,000 lumens

Input Power: 34-50 watts Efficacy: Up to 100 LPW

CRI: Minimum 90

CCT: 3500K, 4000K, 5000K Input Voltage: 120-277 VAC

L₇₀ Lifetime: 79,500 hours at 25°C

Limited Warranty[†]: 5 years

Dimming: 0/1-10V dimming down to 10%

Limited Warranty Emergency Back Up (EB) Battery: 1 Year Battery Back Up. Test regularly in

accordance with local codes

Mounting: Recessed* or Suspended w/surface mount kit accessory

[†]See http://lighting.cree.com/warranty for warranty terms
*Not intended for use with 9/16" T-Bar grids unless used with a 9/16" accessory clip like "Armstrong® LFC- Fixture Clip" which can be purchased through distribution. Consult factory for non-standard grid applications.



Field-Installed

Suspension Kit FPAC-45-1

- Suspension Kit with canopy kit and cables

Surface Mount Kit SMK-CR22


Drywall Grid Adaptor DGA22-WHT

- Above ceiling access required

Chicago Plenum Field Kit CPLFP

- Fits all FP types to be installed in the field





Ordering Information

Example: FP22-34L-35K-10V

| FP22 | | | 10V | | |
|---|--|--|--------------|-----------------------------|---|
| Product | Initial Delivered Lumens | сст | Control | Voltage | Options |
| FP22 Essentia Series Flat Panel 2' x 2' | 34L 34W, 3,400 lumens, 100 LPW 50L 50W, 5,000 lumens, 100 LPW | 35K 3500K 40K 4000K 50K 5000K | 10V 0-10V | Blank - 120-277 volt | EB14 Emergency Backup - 1,400 lumens |

NOTE: Price adder may apply depending on configuration







Rev. Date: V7 05/01/2018



Product Specifications

CONSTRUCTION & MATERIALS

- · Solid aluminum frame provides strength and uniformity
- · Ultra-thin 2.8" (70mm) luminaire height and design effectively target a broad range of plenum spaces and allow for easy installations
- · Luminaire is post-painted with a soft matte white paint
- Compatible with standard 15/16" and 9/16" T-Bar ceilings¹
- Compatible with drywall ceilings via accessory kit2
- · Surface or cable mounting via accessory kits
- Frosted polycarbonate lens for non-pixelated appearance

OPTICAL SYSTEM

- Edge-lit flat panel optics produce soft balanced low glare illumination
- Components work together to optimize distribution, balancing the delivery of high illuminance levels on horizontal surfaces with an ideal amount of light on walls and vertical surfaces

ELECTRICAL SYSTEM

- Integral, high-efficiency driver
- Power Factor: > 0.9
- Input Power: Stays constant over life
- Input Voltage: 120-277V, 50/60Hz
- Operating Temperature Range: 0°C + 35°C (32°F + 95°F)
- Total Harmonic Distortion: < 20%

- Continuous dimming to 10% with 0-10V DC control protocol
- 10V Source Current: 0.10mA
- For use with Class 2 dimming systems only. Reference www.creelink.com/exLink.asp?70982140Z58R34I26620963 for recommended dimming controls and wiring diagrams

REGULATORY & VOLUNTARY QUALIFICATIONS

- · cULus Listed
- DLC qualified. Please refer to www.designlights.org/QPL for most current information
- RoHS compliant. Consult factory for additional details
- Suitable for damp locations
- Designed for indoor use
- Ingress Protection: IP40
- Type IC rated for direct contact with insulation
- UL924 (EB14 option)
- Meets FCC Part 15, Subpart B, Class A standards for conducted and radiated emissions-fixtures/results for most current information

| Electrical Data* | | | | | |
|--------------------------------|-----------------------------|-------------------|------|------|------|
| Initial Delivered Lumens | System Watts 120-277V | Total Current (A) | | | |
| | | 120V | 208V | 240V | 277V |
| 34L | 34 | 0.35 | 0.20 | 0.18 | 0.15 |
| 50L | 50 | 0.52 | 0.30 | 0.26 | 0.22 |

^{*} Electrical data at 25° C (77° F). Actual wattage may differ by +/- 10% when operating between 120-277V +/- 10%

| Recommended Essentia® Series Flat Panel Lumen Maintenance Factors (LMF)¹ | | | | | | |
|--|----------------|---|------------------------------|------------------------------|-------------------------------|--|
| Ambient | Initial LMF | 25K hr Projected ² LMF | 50K hr Calculated³ LMF | 75K hr Calculated³ LMF | 100K hr Calculated³ LMF | |
| 25°C (77°F) | 1.00 | 0.91 | 0.81 | 0.72 | 0.64 | |

¹Lumen maintenance values at 25°C are calculated per TM-21 based on LM-80 data and in-situ luminaire testing ²In accordance with IESNA TM-21-11, Projected Values represent interpolated value based on time durations that are within six times (6X) the IESNA LM-80-08 total test duration (in hours) for the device under testing ([DUT] i.e. the packaged LED chip)

Application Reference

| Open Spa | Open Space | | | | | | |
|-----------------|--------------------------------|--------|---------|-----|-------|------------|--|
| Spacing (ft) | Initial Delivered Lumens | Lumens | Wattage | LPW | w/ft² | Average FC | |
| 8x8 | 34L | 3,400 | 34 | 100 | 0.51 | 50 | |
| | 50L | 5,000 | 50 | 100 | 0.75 | 73 | |
| 8x10 | 34L | 3,400 | 34 | 100 | 0.43 | 41 | |
| | 50L | 5,000 | 50 | 100 | 0.63 | 61 | |
| 10x10 | 34L | 3,400 | 34 | 100 | 0.34 | 33 | |
| | 50L | 5,000 | 50 | 100 | 0.50 | 48 | |
| 10x12 | 34L | 3,400 | 34 | 100 | 0.27 | 26 | |
| | 50L | 5,000 | 50 | 100 | 0.40 | 39 | |

^{9&#}x27; Ceiling, 80/50/20 Reflectances, 2.5 workplane. LLF: 1.0 Initial. Open Space: 50' x 40' x 9' $\,$


 $^{^{\}rm I}$ Installation in 9/16" T-bar ceilings requires that fixture be aligned to grid aperture by securing four integral hanging clips to T-bar $^{\rm 2}$ Above ceiling access required

In accordance with IESNA TM-21-11, Calculated Values represent time durations that exceed six times (6X) the IESNA LM-80-08 total test duration (in hours) for the device under testing ((DUT) i.e. the packaged LED chip)

Photometry

FP22-34L-35K-10V BASED ON DTC REPORT TEST #: PL07123-001

Luminaire photometry has been conducted in accordance with IESNA LM-79-08. IESNA LM-79-08 specifies the entire luminaire as the source resulting in a luminaire efficiency of 100%.



Initial Delivered Lumens: 3,189 Efficacy: 98.0 LPW

S/M: 1.28

| Coefficients Of Utilization – Zonal Cavity Method | | | | | |
|--|-----|-----|-----|-----|--|
| RC %: | 80 | | | | |
| RW %: | 70 | 50 | 30 | 10 | |
| RCR: 0 | 119 | 119 | 119 | 119 | |
| 1 | 109 | 104 | 99 | 95 | |
| 2 | 99 | 90 | 83 | 77 | |
| 3 | 90 | 79 | 71 | 64 | |
| 4 | 82 | 70 | 61 | 54 | |
| 5 | 75 | 62 | 53 | 47 | |
| 6 | 70 | 56 | 47 | 41 | |
| 7 | 64 | 51 | 42 | 36 | |
| 8 | 60 | 46 | 38 | 32 | |
| 9 | 56 | 42 | 34 | 29 | |
| 10 | 53 | 39 | 31 | 26 | |
| - | 53 | 39 | 31 | | |

Effective Floor Cavity Reflectance: 20%

| Average Luminance Table (cd/m²) | | | | | | |
|---------------------------------|------------------|-------|-------|-------|--|--|
| | Horizontal Angle | | | | | |
| | | 0° | 45° | 90° | | |
| ngle | 45° | 2,823 | 2,820 | 2,823 | | |
| cal A | 55° | 2,732 | 2,731 | 2,726 | | |
| Vertical Angle | 65° | 2,583 | 2,579 | 2,572 | | |
| | 75° | 2,284 | 2,270 | 2,258 | | |
| | 85° | 1,780 | 1,718 | 1,697 | | |

| Zonal Lumen Summary | | | | | |
|---------------------|--------|--------|-----------|--|--|
| Zone | Lumens | % Lamp | Luminaire | | |
| 0-30 | 852 | N/A | 26.7% | | |
| 0-40 | 1,400 | N/A | 43.9% | | |
| 0-60 | 2,493 | N/A | 78.2% | | |
| 0-90 | 3,190 | N/A | 100% | | |
| 0-180 | 3,469 | N/A | 100% | | |

Reference http://lighting.cree.com/products/indoor/troffers/essentia-series-flat-panel for detailed photometric data