
PRE-TERMINATED CABLES AND SEGMENT

NETWORK WIRE

Pre-terminated LMRJ cables for DLM local networks in lengths up to 100 feet

UL and cUL listed and labeled

Wattstopper LM-MSTP wire required for wired segment networks. This wire is not needed for wireless DLM networks using the wireless bridge (LMBC-600).



LMRJ & LM-MSTP

Standard green color and markings for DLM provide easy identification of LMRJ cables in plenum

Cables and wire available in a choice of colors for use in exposed locations

LMRJ cables available in plenum and non-plenum rating

5 year warranty



Description

LMRJ Series cables connect Digital Lighting Management (DLM) components without the need for tools or point-to-point discrete wiring. Cables are pre-terminated with industry standard RJ45 connectors compatible with any RJ45 port on DLM components. LMRJ cables utilize B to B wiring.

Plenum-rated LM-MSTP Segment Network wire carries the MS/TP (RS485) signal. Wire is 1.5 pair (twisted pair + 1 conductor) + shield, white/black/green. Use of LM-MSTP is mandatory for wired DLM network projects. Another option is to avoid the need for LM-MSTP wire through the use of wireless bridges (model LMBC-600).

Operation and Applications

LMRJ cables can be plugged into any available RJ45 port on a DLM device and connected to any other DLM device. These cables facilitate the creation of a local network of DLM components that automatically configure and function together. While LMRJ series cables are rated Cat 5e, they are not recommended for general data use in other than DLM network applications.

LM-MSTP wire is used to create a linear topology (daisy-chain) segment network for control by a segment manager or building automation system.

Ordering Information

Catalog #	Non-Plenum Rated Local Network Cables		Plenum Rated Local Network Cables				
	Green cable with white stripe		Catalan #	Croop poble with block etring		Catalan #	White coble
☐ LMRJ-01	Six-i	inch Jumper	Catalog #	Green cable with black stripe		Catalog #	White cable
☐ LMRJ-03	3' Cable		☐ LMRJ-P03	3' Cabl	le	☐ LMRJ-P03-W	3' Cable
LMRJ-10	10' Cable		☐ LMRJ-P10	10' Cal	Cable LMRJ-P		10' Cable
LMRJ-15	15' Cable		☐ LMRJ-P15	15' Cal	ole	☐ LMRJ-P15-W	15' Cable
☐ LMRJ-25	25' Cable		☐ LMRJ-P25	25' Cal	ole	☐ LMRJ-P25-W	25' Cable
☐ LMRJ-35	35' Cable		☐ LMRJ-P35	35' Cal	ole	☐ LMRJ-P35-W	35' Cable
☐ LMRJ-50	50' Cable		☐ LMRJ-P50	50' Cal	ole	☐ LMRJ-P50-W	50' Cable
☐ LMRJ-75	75' Cable		☐ LMRJ-P75	75' Cal	ole	☐ LMRJ-P75-W	75' Cable
☐ LMRJ-100	100' Cable		☐ LMRJ-P100	100' Ca	able	☐ LMRJ-P100-W	100' Cable
Catalog # Unterminated Plenum Rated Segment Network Wire							
☐ LM-MSTP		Green-jacketed segment network wire, 1.5 pair, max diameter 0.185", available by the foot		LM	1-MSTP-S1000	Green-jacketed LM-MSTP wire; 1000' reel	
LM-MSTP-W		White-jacketed segment network wire, 1.5 pair, max diameter 0.185", available by the foot			1-MSTP-S2000	Green-jacketed LM-MSTP wire; 2000' reel	
☐ LM-MSTP-B		Black-jacketed segment network wire, 1.5 pair, max diameter 0.185", available by the foot			1-MSTP-S4000	Green-jacketed LM-MSTP wire; 4000' reel	
		Segment network wire, 1.5 pair, max diameter 0.185", rated for direct burial		*PEP designation applies to LMRJ cables or			
PROJECT				OCATION/ YPE			

WWW.LEGRAND.US/WATTSTOPPER Pub. No. 27402r1 1/2018