

A-Shape LED

LA19/9/827/ECO/D

9 Watt LED A19

- Dimmable down to 10%*
- 85% energy savings compared to 60W incandescent



Item #	LA19/9/827/ECO/D-78
Product Code	78010
UPC	751338000452
Watts	9
Volts	120
Lamp Shape	A19
Base	E26 Medium
CRI	80
Color Temp	2700K
Initial Lumens	675
Beam Spread	240°
Average Rated Life	15,000
Temp Range	-20°C to 40°C
MOL	4.4"
Equivalent Wattage	60
Warranty	3 years

Specifications are subject to change without prior notice.

*Compatible with most leading edge or incandescent style dimmers.

Not Rated for use in totally enclosed fixtures.



A-Shape LED

LA19/9/830/ECO/D

9 Watt LED A19

- Dimmable down to 10%*
- 85% energy savings compared to 60W incandescent



Item #	LA19/9/830/ECO/D-78
Product Code	78012
UPC	751338000469
Watts	9
Volts	120
Lamp Shape	A19
Base	E26 Medium
CRI	80
Color Temp	3000K
Initial Lumens	700
Beam Spread	240°
Average Rated Life	15,000
Temp Range	-20°C to 40°C
MOL	4.4"
Equivalent Wattage	60
Warranty	3 years

Specifications are subject to change without prior notice.

*Compatible with most leading edge or incandescent style dimmers.

Not Rated for use in totally enclosed fixtures.



A-Shape LED

LA19/9/840/ECO/D

9 Watt LED A19

- Dimmable down to 10%*
- 85% energy savings compared to 60W incandescent



Item #	LA19/9/840/ECO/D-78
Product Code	78014
UPC	751338000476
Watts	9
Volts	120
Lamp Shape	A19
Base	E26 Medium
CRI	80
Color Temp	4000K
Initial Lumens	725
Beam Spread	240°
Average Rated Life	15,000
Temp Range	-20°C to 40°C
MOL	4.4"
Equivalent Wattage	60
Warranty	3 years

Specifications are subject to change without prior notice.

*Compatible with most leading edge or incandescent style dimmers.

Not Rated for use in totally enclosed fixtures.



A-Shape LED

LA19/9/850/ECO/D

9 Watt LED A19

- Dimmable down to 10%*
- 85% energy savings compared to 60W incandescent



Item #	LA19/9/850/ECO/D-78
Product Code	78016
UPC	751338000483
Watts	9
Volts	120
Lamp Shape	A19
Base	E26 Medium
CRI	80
Color Temp	5000K
Initial Lumens	750
Beam Spread	240°
Average Rated Life	15,000
Temp Range	-20°C to 40°C
MOL	4.4"
Equivalent Wattage	60
Warranty	3 years

Specifications are subject to change without prior notice.

*Compatible with most leading edge or incandescent style dimmers.

Not Rated for use in totally enclosed fixtures.

