

Brighten



Application illustration only, subject lamps not used in photo.



LED MR16/MRX16 lamps

For high-output in decorative lighting applications, GE's dimmable 7-watt LED MR16/MRX16 lamp is the perfect solution.

LOW-COST OPERATION

- For example, using only 7 watts of energy, save over \$118 in energy costs over the rated life of a lamp versus a standard 50-watt halogen lamp based on \$0.11 per kWh
- Energy efficiency and long life mean fewer lamp replacements versus halogen MR16/MRX16 light sources

EXCELLENT COLOR RENDERING

- Available with a CRI of 80 - 95

COLOR TEMPERATURE

- Halogen-like color
- Available in 2700K, 3000K and 4000K

LONG LIFE

- Up to 25,000 hours rated life (L70)

DIMMABLE

- Dims from 100% to 10%

BEAM PATTERNS

- Available in 15°, 25° and 35° beam patterns

TRANSFORMER COMPATIBILITY

- A lamp-transformer compatibility table has been developed and is available at www.gelighting.com/LED-MR16

ENVIRONMENTALLY CONSCIOUS

- These lamps are energy efficient, contain no lead or mercury, and are compliant with material restriction requirements of RoHS

GE QUALITY AND RELIABILITY

- 3-year limited warranty

ecomaginationSM

To learn more about saving money and energy, go to: <http://products.currentbyge.com>.




Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

current
powered by GE



LED MR16/MRX16 lamps

Directional Lamps (MR16/MRX16)

Bulb Shape	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information				
12 Volt AC/DC MR16																					
	GU5.3	7	93412	LED7DMR16S830/15	12	6	2.3	460	3800	3000	80	35W	25,000	Yes		Damp	Spot 15° beam, Silver				
			35195	LED7XDMRX1683025	12	6	2.2	500	2350	3000	80	50W	25,000	Yes	★	Damp	Narrow Flood 25° beam, White				
			35196	LED7XDMRX1683035	12	6	2.2	500	1350	3000	80	50W	25,000	Yes	★	Damp	Flood 35° beam, White				
			35206	LED7XDMRX1682725	12	6	2.2	500	2350	2700	80	50W	25,000	Yes	★	Damp	Narrow Flood 25° beam, White				
			35214	LED7XDMRX1682735	12	6	2.2	500	1350	2700	80	50W	25,000	Yes	★	Damp	Flood 35° beam, White				
			35529	LED7DMRX16827/15	12	6	2.2	400	3400	2700	80	35W	25,000	Yes		Damp	Spot 15° beam, White				
	GU5.3	7	21359	LED7MRX16R930/10	12	6	2.01	350	8000	3000	95	50W	25,000	-		Damp	Spot, 10° beam, Reveal				
			Value 12 Volt AC/DC MR16																		
				GU5.3	5.5	35542	LED5.5DMR1684035	12	6	1.8	460	1100	4000	80	35W	25,000	Yes	★	Damp	Flood, 35° beam, White	
						35535	LED5.5DMR1683035	12	6	1.88	420	1000	3000	80	35W	25,000	Yes	★	Damp	Flood, 35° beam, White	
						35540	LED5.5DMR1682735	12	6	1.88	400	1000	2700	80	35W	25,000	Yes	★	Damp	Flood, 35° beam, White	
						7	35546	LED7XDMR16-22725	12	6	1.8	500	2350	2700	80	50W	25,000	Yes	★	Damp	Flood 25° beam, White
35543	LED7XDMR16-28325	12				6	1.8	500	2350	3000	80	50W	25,000	Yes	★	Damp	Narrow Flood, 25° beam, White				
35544	LED7XDMR16-28335	12				6	1.8	500	1350	3000	80	50W	25,000	Yes	★	Damp	Flood 35° beam, White				

Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

* The life rating is based on the hours of operation the lamp will provide before reaching 70% of its original rating (L70)

** Minimum order quantity = 6

★ ENERGY STAR® status: ENERGY STAR® certified. Lamps without a "★" are not ENERGY STAR® certified.

UL 1993 Environmental Requirements for LED LAMPS

Location, damp - Exterior or interior location that is normally or periodically subject to condensation of moisture in, on, or adjacent to, electrical equipment, and includes partially protected locations.

Location, dry - Location not normally subject to dampness, may include a location subject to temporary dampness, i.e., building under construction, provided ventilation is adequate to prevent an accumulation of moisture.

Location, wet - Location in which water or other liquid can drip, splash, or flow on or against electrical equipment.

Notes: 1) Product descriptions ending in "/TP" indicate a carded blister or clamshell package nested in a tray for shelf display. Cards also designed for hook display.



Product is compliant with material restriction requirements of RoHS

ENERGY STAR® is a registered U.S. mark



<http://products.currentbyge.com>

GE and the GE Monogram are trademarks of the General Electric Company. All other trademarks are the property of their respective owners. Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions. GE Lighting and GE Lighting Solutions, LLC are businesses of the General Electric Company. © 2016 GE.

