369-613a 1 05.15.12

Maestro_® C•L_® Dimmer

Dimmer for CFL and LED dimmable bulbs.

Features

- Large tapswitch with a rocker-style dimmer for a standard designer wallplate opening
- Advanced dimming technology designed for compatibility with a broader range of high efficacy bulbs
- UL Listed to control:
 - Dimmable Compact Fluorescent Lamps (CFL) with integrated ballast
 - Dimmable LED with integrated driver
 - Halogen
 - Incandescent
- Low-end adjustment to accommodate a wide range of bulbs
- No neutral required for retrofit applications
- Tapswitch returns load to previous level
- Can be used in single-pole, multi-location (using MA-R), or 3-way mechanical switch¹ applications
- Coordinating Claro® and Stainless Steel wallplates available separately
- 100% factory tested

Colors and Finishes

Gloss Finishes

WH	White	IV	Ivory
AL	Almond	LA	Light Almond
GR	Gray	BR	Brown
BL	Black		
Satin (Colors®		

HT	Hot	MR	Merlot	
PL	Plum	TQ	Turquoise	
SG	Sea Glass	TP	Taupe	
ES	Eggshell	BI	Biscuit	
SW	Snow	PD	Palladium	
MN	Midnight	TC	Terracotta	
SI	Sienna	GB	Green Briar	
BG	Bluestone	MS	Mocha Stone	
GS	Goldstone	DS	Desert Stone	
ST	Stone	LS	Limestone	



Wallplate sold separately

Product Specific Features

 Capable of controlling up to 150 W Dimmable CFL/LED or 600 W Incandescent/Halogen or Mixed bulb type per Multigang and Mixed Bulb Type Ratings table (see page 3)

Model Number

MACL-153M-XX² Single pole/3-way¹/Multi-location³

Notes:

- ¹ An additional wiring and programming step is required for 3-way mechanical switch applications. Not for use in 4-way mechanical switch applications
- ² XX Color codes, see section "Colors and Finishes" at left
- ³ For 3-way and 4-way dimming, use Maestro_® companion dimmers

3/1/2	ITPON	SPECIFICATION	CHEMITTAL
2.5		SPECIFICATION	SUBMITTAL

EUTRON: SPECIFICATION SUBMITTAL		Page
Job Name:	Model Numbers:	
Joh Number		

369-613a 2 05.15.12

Specifications

Regulatory Approvals

- UL Listed to U.S. and Canadian safety requirements (UL 1472 / CSA C22.2 184.1)
- NOM

Power and Ratings

- 120 V∼ 60 Hz
- Maximum Load
 - 150 W Dimmable CFL/LED

or

- 600 W Incandescent/Halogen

or

- Mixed bulb type per Multigang and Mixed Bulb
 Type Ratings table (see page 3)
- Minimum Load
 - See approved lamp list for CFL/LED

or

- 10 W Incandescent/Halogen

Environment


- For indoor use only
- Operating temperatures 32 °F (0 °C) to 104 °F (40 °C)

Performance

- Power-failure memory
- Raise/Lower Rocker
- Electrostatic discharge tested
- Precise color matching
- Includes a Front Accessible Service Switch (FASS™) for safe bulb replacement

Application Requirements

- When using CFLs or LEDs, only bulbs marked or rated as Dimmable can be used.
- For a complete list of approved DIMMABLE CFLs and LEDs please call 1.800.523.9466 or visit www.lutron.com/dimcflled



Note: Requires a U.S. wallbox 2 ¼ in (57 mm) deep minimum.

Warranty

1 Year Limited Warranty
 For additional Warranty information, please visit
 http://www.lutron.com/TechnicalDocumentLibrary/
 369-119_Wallbox_Warranty.pdf

31/2	ITRON	SPECIFICATION	SHEMITTAL
2.5		SECHEILAIION	JUDIVITI I AT

** SF LOIT TO ATTO	raye	
Job Name:	Model Numbers:	
Job Number:		


Page

369-613a 3 05.15.12

Multigang and Mixed-Bulb-Type Ratings

Total CFL•LED Wattage Installed CFL LED		Maximum Allowa Incandescent/Ha		INC/HAL
(Watts per bulb X # of bulbs)		No sides removed	1 side removed	2 sides removed
0 W	+	600 W	500 W	400 W
1 W – 25 W	+	500 W	400 W	300 W
26 W - 50 W	+	400 W	300 W	200 W
51 W – 75 W	+	300 W	200 W	100 W
76 W – 100 W	+	200 W	100 W	50 W
101 W – 125 W	+	100 W	50 W	0 W
126 W – 150 W	+	0 W	0 W	0 W

Operation



LUTRON SPECIFICATION SUBMITTAL


Page

Job Name:	Model Numbers:
Job Number:	

369-613a 4 05.15.12


Wiring Diagrams

Single-Pole Wiring




Note: Dimmer can be installed on the line side or load side of the circuit.

3-Way Wiring (Using 3-Way Mechanical Switch)



^{*}Note: Screw terminal positions on 3-way mechanical switches may vary.

3-Way Wiring (Using MA-R Companion Dimmer)



Continued on next page...

LUTRON SPECIFICATION SUBMITTAL


Page

Job Name:	Model Numbers:
Job Number:	

369-613a 5 05.15.12

Wiring Diagrams (continued)

4-Way Wiring (Using MA-R Companion Dimmer)



Note: Dimmer can be installed on the line side, load side, or in the middle of the circuit.

LUTRON SPECIFICATION SUBMITTAL

Job Number:

Model Numbers: