



NEW PRODUCTS

TICK™

TOOL AND EQUIPMENT TRACKER



TICK™ Tool and Equipment Tracker (48-21-2000)

Attach with glue, screws or rivets to anything. Survives everything with weather, water, dust and impact protection. 1 year runtime with replaceable coin cell battery. Tracking Powered by the ONE-KEY™ App. Over 100 ft signal range. Location signal wakes up a sleeping or backgrounded app



M18™ FORCE LOGIC™ 1590 ACSR Cable Cutter 2777-21

Cuts up to 1590 Falcon ACSR, and 1/2" EHS Guy Wire. Jaw design enables opening with just two fingers, enhancing alignment while delivering easiest operation with Class 3 Gloves.



M18™ FORCE LOGIC™ 3" Underground Cable Cutter 2776-21 / 2776R-21

Cut up to 1500MCM Copper 15kV WIRELESSLY. The wireless remote communicates with the tool via a mutually exclusive connection.



M18 FUEL™ String Trimmer 2725-21HD / 2725-20

Power to clear thick brush, reaches full throttle in under 1 second, and provides up to 1 hour of run-time per charge. Designed to meet landscape maintenance professional needs.



M18 FUEL™ Hedge Trimmer 2726-21HD / 2726-20

Power to cut 3/4" branches, cuts up to 30% faster, and provides up to 2 hours of run-time per charge. Designed to meet landscape maintenance professional needs.



M18 FUEL™ Blower 2728-21HD / 2728-20

Power to clear from 15 ft, generates up to 30% less noise than gas, and provides the longest, max CFM run-time. Designed to meet landscape maintenance professional needs.



M18™ Utility Bucket Light 2122-20 / 2122-21HD / 2122-22HD

2500 Lumens with 500 yard beam distance. Dual Light head design with 180 degrees of vertical and horizontal head rotation. 3 output modes: Spot, Flood, Spot/Flood.



M18™/M12™ Wireless Jobsite Speaker 2891-20

Industry's Loudest, Clearest Sound System. Stream high definition music wirelessly with Bluetooth® from over 100ft. Compatible with the M18™ and M12™ systems



M18™ Short Throw Press Tool w/ Viega PureFlow™ Jaws 2674-22P

Designed for One Handed Use. Auto Cycle ensures full press every time. 40% Faster Press.



M18 FUEL™ SURGE™ 1/4" Hex Hydraulic Driver 2760-20 / 2760-22CT / 2760-22

New FLUID-DRIVE™ Hydraulic Powertrain features up to 50% quieter operation, 3X less vibration for smoother operation, and faster driving speeds compared to standard impacts.



M18 FUEL™ Dual Bevel Sliding Compound Miter Saw 2734-20 / 2734-21HD / 2734-21HDP

Delivering greater capacity than many corded 10" sliding miter saws and the 9.0 Battery battery pack delivers up to 400 cuts per charge.



M18 FUEL™ SAWZALL® Reciprocating Saw w/ ONE-KEY™ 2721-20 / 2721-22 / 2721-22HD

Delivers faster than corded cutting speed and the durability of a corded saw. ONE-KEY™ Compatible: Customize, Track and Manage tool's performance and location.



M18™ Transfer Pump 2771-20 / 2771-21

With a self-priming pump, you can connect and go quicker than ever. Pump moves water at up to 480 gallons per hour, generates up to 18' of lift and produces up to 75' of head height.



M18™ Compact Vacuum 0882-20 / 49-90-1951 HEPA Filter

Features high performance motor, 40 CFM, removable HEPA filter, and clear view and easy to empty canister. Adapts from Handheld to Stationary.



M18 FUEL™ 1/2" Mid-Torque Impact Wrench with Pin Detent 2860-20 / 2860-22

Delivers 450 ft-lbs Fastening torque and 600 ft-lbs Nut-Busting torque. 3-Mode DRIVE CONTROL™ provides greater control over output speed and power with a max RPM of 2,400.



M18 FUEL™ 1/2" Mid-Torque Impact Wrench with Friction Ring 2861-20 / 2861-22

Delivers 450 ft-lbs Fastening torque and 600 ft-lbs Nut-Busting torque. 3-Mode DRIVE CONTROL™ provides greater control over output speed and power with a max RPM of 2,400.



M18 FUEL™ Drywall Screw Gun 2866-20 / 2866-22CT / 2866-22

Features AUTO START functionality and delivers UP TO 3X LONGER RUN TIME than other cordless competitors. The POWERSTATE™ Brushless motor spins at 4,500 RPM's resulting in faster productivity.



M18™ Cut Out Tool 2627-20 / 2627-22CT / 2627-22

Most compact tool in the market. With our 4-Pole motor this tool delivers up to 20% faster cuts than other tools in the market. Provides up to 120 cuts per charge.



NEW PRODUCTS

M18™ ROCKET™ LED Tower Light/Charger 2135-20 / 2135-21HD

Can be setup in seconds to a max height of 7', and collapses to less than 4' for easy transport and storage. Delivering 3,000 lumens, it fills up large areas with TRUEVIEW™ High Definition Light.



M18™ RADIUS™ LED Compact Site Light w/ONE-KEY™ 2146-20

With 4,400 lumens, it provides enough light to illuminate large work areas, and can be turned down to as low as 1,000 lumens for working in confined areas.



M12™ Compact Flood Light 2364-20

As bright as a 250w halogen. Multiple hanging features: 2 powerful magnets, spring loaded clamp, key hole hanger, wire hanger. 3 output modes for optimal brightness and runtime.



M18™ Search Light 2354-20 / 2354-21

Features 1,250 Lumens with 700 yard beam distance, 198 Degree head rotation, and 4 output modes: Spot, Flood, Spot/Flood, & Strobe. Its IP54 rating provides water and dust resistance for all weather use.



100Ft Closed Reel Long Tape 48-22-5101

Features Grime Guard™ - industry's first blade wiper, heavy duty metal frame, 3:1 reinforced planetary gears, nylon coated steel blade, and 100ft folding hook.



100Ft Open Reel Long Tape 48-22-5201

Features Grime Guard™ - industry's first blade wiper, 1/2" nylon bond steel blade, 3:1 metal planetary gears, metal reinforced handle, and kink resistant blade.



300Ft Open Reel Long Tape 48-22-5230

Features Grime Guard™ - industry's first blade wiper, 3/8" nylon bond steel blade, 3:1 metal planetary gears, metal reinforced handle, and kink resistant blade.



12" Measuring Wheel 48-22-5012

Designed for extreme durability, increased ergonomics, and productivity. Features a Debris-Cleaning Wheel Flap that easily clears away contamination while rolling.



12" Engineer's Measuring Wheel 48-22-5013

Designed for extreme durability, increased ergonomics, and productivity. Features a Debris-Cleaning Wheel Flap that easily clears away contamination while rolling.



6" Measuring Wheel 48-22-5006

Durable locking pivot points help quickly fold the units for transportation and storage. The pistol grip handles, designed to provide similar ergonomics to that of a power tool handle.



SHOCKWAVE™ Conduit Reaming Bit Holder 48-32-2350 / 48-32-2351

Made for use with 1/2", 3/4" and 1" EMT, the thick, hardened tool steel blade provides up to 5X life vs. the competition. The slim profile allows access for common electrical fastening applications.



The AX™ with Carbide Teeth SAWZALL® Blade 48-00-5221 (6") / 48-00-5226 (9") / 48-00-5227 (12")

These new blades will deliver 30X longer life over standard bi-metal blades and 2X faster cutting than other carbide blades.



24" Hard Top Rolling Bag 48-22-8220

Hardtop construction designed for stacking. 6" metal-rimmed all terrain wheels for rough jobsite environments. Carry loads up to 250 lbs.



18" Jobsite Rolling Bag 48-22-8221

6" all terrain metal rimmed wheels with strong extension handle. Carry loads up to 200 lbs.



Laser Distance Meters

48-22-9801
Functions: Linear Distance
Range: 65ft
Accuracy: 1/8"
Read Outs: ft-in, m



48-22-9802
Functions: Linear Distance, Add/Subtract, Surface Area, Total Area, Volume
Range: 150ft
Accuracy: 1/16"
Read Outs: ft-in, in, .ft, m



48-22-9803
Functions: Linear Distance, Add/Subtract, Surface Area, Total Area, Volume, Indirect H/L, Indirect Height, Auto Level
Range: 330ft
Accuracy: 1/16"
Read Outs: ft-in, in, .ft, m