

Adjustable Torque Screwdriver



- *Used for assembly and maintenance applications in accordance to 2017 NEC.*
- *Simple torque adjustment*
- *Clutch releases automatically when preset torque is attained*
- *Adjustable torque from 0-36 in. lbs.*
- *Bi-directional accuracy (+/- 6%)*
- *Dual metric and imperial scale for versatility*
- *1/4 in. hex drive accepts many bits, sockets and adapters*
- *Kit includes:*
 - Adjustable Torque Screwdriver*
 - #1 and #2 Phillips Power Bits*
 - #1 and #2 Square Power Bits*
 - 1/4 in. and 3/16 in. Slotted Power Bits*

NEW



Adjustable Torque Screwdriver

The IDEAL Adjustable Torque Screwdriver is a quality control device used to provide consistent user-settable torque in varying assembly or maintenance applications. The screwdriver includes a variable torque range of up to 36 in. lbs. and unique torque limiting clutch that will disengage once the preset torque has been reached. This feature prevents over-tightening which can cause possible damage to components and final products.



7-Pc. Kit contains:

- Torque Screwdriver
- #1 and #2 Phillips Bits
- #1 and #2 Square Bits
- 1/4 in. and 3/16 in. Slotted Bits



1375 Park Avenue, Sycamore, IL 60178, USA / 815-895-5181 • 800-435-0705 in USA

International offices:
Australia • Brazil • Canada • China • France • Germany • India • Mexico • UK

For complete sales office contact information, visit us at:
www.idealind.com