


Power Limited Tray Cable, Tinned Copper Shield



300 Volts



Product Construction

Conductor:

- Annealed Tinned copper
- 19 strands Class C
- 2 conductors

Insulation:

- Polyvinyl Chloride (PVC)

Shield:

- Aluminum Mylar tape
- 100% coverage

Drain Wire:

- 7 strand tinned copper

Jacket:

- Polyvinyl Chloride (PVC)

Applications

- Cable is suitable for use in Class I Division II hazardous locations
- Cable is UL approved for sunlight resistant and direct burial applications
- Recommended Operating Voltage: 300V

Standards

- UL listed as type PLTC & CL3 per UL standard 13
- Type ITC per UL standard 2250
- IEEE 1202 available upon request
- RoHS compliant

COLOR CODE CHART

Cond. #	Color
1	Black, Red & Numbered
2	Black, Red & Numbered

Part #	AWG	Pairs	Insulation Thickness	Jacket Thickness	Nom. O.D.	Lbs./M'	Jacket Color
KT32202	22	1	.013"	.037"	.191"	20	Gray
KT32002	20	1	.016"	.037"	.220"	26	Chrome Gray
KT31802	18	1	.016"	.037"	.242"	38	Gray
KT31602	16	1	.016"	.037"	.256"	43	Chrome Gray

Note: The information in this specification sheet is approximate and subject to standard industry and manufacturer tolerances.