

# Circuit Breakers

UQFP Plug-In & UQFB Bolt-On Series | 120/240 VAC



**UQFP**  
**UQFPH**



**UQFP-M**  
**UQFPH-M**



**UQFB-X1**



**UQFB-X**



**UQFB**



**UQFB-X-MOD**

**200 Amp Frame | Plug-In | 10,000 AIC & 22,000 AIC | Two-Pole - Common Trip**

| Amps | 10K AIC Plug-In | 22K AIC Plug-In | 10K AIC Plug-In | 22K AIC Plug-In | Wire Range |         |
|------|-----------------|-----------------|-----------------|-----------------|------------|---------|
|      |                 |                 |                 |                 | CU         | AL      |
| 100  | UQFP-100        | UQFPH-100       | UQFP-M-100      | UQFPH-M-100     | #3-#1      | #1-1/0  |
| 125  | UQFP-125        | UQFPH-125       | UQFP-M-125      | UQFPH-M-125     | #3-#1      | #1-1/0  |
| 150  | UQFP-150        | UQFPH-150       | UQFP-M-150      | UQFPH-M-150     | 1/0-300    | 2/0-300 |
| 175  | UQFP-175        | UQFPH-175       | UQFP-M-175      | UQFPH-M-175     | 1/0-300    | 2/0-300 |
| 200  | UQFP-200        | UQFPH-200       | UQFP-M-200      | UQFPH-M-200     | 1/0-300    | 2/0-300 |

**200 Amp Frame | Bolt-On | 10,000 AIC & 22,000 AIC | Two-Pole - Common Trip**

| Amps | 10K AIC Bolt-On | 22K AIC Bolt-On | 10K AIC Bolt-On | 22K AIC Bolt-On | Wire Range |         |
|------|-----------------|-----------------|-----------------|-----------------|------------|---------|
|      |                 |                 |                 |                 | CU         | AL      |
| 100  | UQFB-100        | UQFBH-100       | UQFB-100-X1     | UQFBH-M-100     | #3-#1      | #1-1/0  |
| 125  | UQFB-125        | UQFBH-125       | UQFB-125-X1     | UQFBH-M-125     | #3-#1      | #1-1/0  |
| 150  | UQFB-150        | UQFBH-150       | UQFB-150-X1     | UQFBH-M-150     | 1/0-300    | 2/0-300 |
| 175  | UQFB-175        | UQFBH-175       | UQFB-175-X1     | UQFBH-M-175     | 1/0-300    | 2/0-300 |
| 200  | UQFB-200        | UQFBH-200       | UQFB-200-X1     | UQFBH-M-200     | 1/0-300    | 2/0-300 |

## Notes

- **UL Listed:** For use with 60°C or 75°C wire.
- **UQFP:** For parallel main circuit breaker applications.
- **UQFP-M:** For series main circuit breaker applications Split load tab features allow for feed-through capability.
- **UQFB:** (2) 1/0-300 lugs provided on load and line side (cable-in, cable-out).
- **UQFB3:** Three-pole available. Consult factory.
- **UQFB-X:** (2) 1/0-300 lugs provided on load side and (2) line bar bus connections on line side.
- **UQFB-M:** For series main circuit breaker applications. Split load tab features allow for feed-through capability.
- **UQFB-X-MOD:** Replacement circuit breaker with line barriers removed.

Utility requirements for this equipment may vary. Always consult the serving utility for their requirements before ordering or installing equipment.

