



Type LA

A flexible steel conduit which is both listed by Underwriters Laboratories Inc. and certified by Canadian Standards Association. It offers outstanding protection against wet, oily conditions and is permitted for use in exposed or concealed locations.

Construction:

Inner Core:

- Hot Dipped Galvanized Steel
- 3/8" 1-1/4" Squarelock Profile with continuous bonding strip
- 1-1/2" 4" Fully Interlocked Profile

Liquidtight Jacket:

- Flexible PVC.
- Resistant to Oils and Mild Acids
- Flame Retardant
- Sunlight Resistant (UV)

Application:

This conduit is intended for installation in accordance with Article 350 of the NEC (ANSI/NFPA-70) and in section 14.5.4 of the ANSI/NFPA-79 Standard for Industrial Machinery:

- Listed and marked for Direct Burial and in Poured Concrete
- For containment of 1000 volt and lower potential circuits
- Suitable as a grounding conductor when used for circuits rated up to 20A for the 3/8 & 1/2 inch trade sizes and 60A for the 3/4 through 1-1/4 inch trade sizes in lengths six feet or less per NEC Article 250.118(7). Larger sizes require separate grounding conductor.
- Installations in hazardous (classified) locations:
 - Class I Div. 2: Article 501.10 (B)(2) & 501.30 (B)
 - Class II Div. 1: Article 502.1 (A)(2) & 502.30 (B) Div. 2: 502.10 (B)(2)
 - Class III Div. 1: Article 503.10 (A)(2) & 503.30 (B) Div. 2: 503.10 (A)(2)
- Installed under raised floors in Data Processing Areas Articles 645.5 (2)
- Electric Signs and Outline Lighting over 1000 volts Articles 600.7/600.32(A)(1)
- Permitted for Service Entrance wiring to six feet Article 230.43
- Used as Feeders and Services at Marinas and Boatyards Article 553.7(B)
- Wiring on Building Article 225.10





All Products Proudly Made in the USA

Product Information

CERTIFICATIONS & COMPLIANCE

- Listed File # E29278. Conforms to **Underwriters Laboratories** Standard ANSI/UL-360 for Liquidtight Flexible Steel conduit.
- Certified File #LL18858. Conforms to CSA 22.2 No.56 for use per the Canadian Electrical Code C22.1 Section 12-1300. FT1



WEEE and RoHS Compliant

C € BS EN IEC 61386 Classification Code 444240650414 CE

Declaration

ARRA: For ARRA Certification Letter, please click here

STANDARD COLORS

Machine Tool Gray and Black. Other colors available upon request.


- Conductor Enclosures Adjacent to Motors over 1000 V Article 430.223
- Underground Service, Feeder, Branch Circuit, and Recreational Vehicle Site Feeder Circuit Conductors Article 551.80
- Elevators and Hoistways Article 620.21
- Pools and Fountains Article 680
- Bodies of water. Article 682
- Fire Pumps. Article 695

Markets:


Aerospace, Cell Towers, Construction, Data Centers, Defense, Fixture / AC Whips, Food Processing, Healthcare, Machine Tool (OEM), Mining, Oil & Gas Refineries, Pharmaceuticals, Power Plants, Rail/Transit, Renewable Energy, Security, Ship Building, Steel Mills, Telecommunications, Utilities, Wastewater Treatment

WORKING TEMPERATURES


-30°C to 80°C Dry / 60°C Wet / 70°C Oil



Squarelock with Filler: sizes 3/8" - 1-1/14"



Interlock sizes: 1-1/2" - 4"



Product Table

	US Trade Size	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"	3 1/2"	4"
	ISO (MM)	16	20	25	32	40	50	63	70	80	90	100
	CSA (MM)	12	16	21	27	35	41	53	63	78	91	103
	Туре	LA-10	LA-11	LA-12	LA-13	LA-14	LA-15	LA-16	LA-17	LA-18	LA-350	LA-19
Internal Diameter	Min (IN.)	0.484	0.622	0.820	1.041	1.380	1.575	2.020	2.480	3.070	3.500	4.000
	Max (IN.)	0.504	0.642	0.840	1.066	1.410	1.600	2.045	2.505	3.100	3.540	4.040
Outer Diameter	Min (IN.)	0.690	0.820	1.030	1.290	1.630	1.865	2.340	2.840	3.460	3.960	4.460
	Max (IN.)	0.710	0.840	1.050	1.315	1.660	1.900	2.375	2.875	3.500	4.000	4.500
Inside Bend Radius	Static (IN.)	2.0	3.0	4.2	5.5	7.0	4.5	6.0	8.0	10.0	11.0	12.0
	Dynamic (IN.)	4.0	5.0	6.0	12.0	15.0	17.0	22.0	30.0	36.0	43.0	52.0
Weight	Lbs. per 100 Ft	29	32	53	82	102	124	145	192	252	308	350
Standard Length	Carton (Ft.)	100	100	100	100	50	50	50	25	25	25	25
	Part # (Gray)	20101	21101	22101	23102	24102	25102	26102	27102	28102	28502	29102
	Part # (Black)	20801	21801	22801	23802	24802	25802	26802	27802	28802		29502
	Reel (Ft.)	500	500	500	400	200	150	100	275	175	175	100
	Part # (Gray)	20103	21103	22104	23104	24104	25104	26104	27105	28105	28505	29105
	Part # (Black)	20803	21803	22804	23804	24804	25804	26804	27805	28805		29505
	Reel (Ft.)	1000	1000	1000								
	Part # (Gray)	20104	21104	22110								
	Part # (Black)	20804	21804	22810								

related products



Type CBLA

Computer Blue LA (CBLA) is a liquidtight flexible steel conduit commonly used for computer room installations. The blue jacket color easily identifies circuitry for computer power wiring. It is listed by Underwriters Laboratories Inc. and certified by Canadian Standards Association.

see product detail»





Type ZHLA

Non-halogen, low smoke and low flame spread make Type ZHLA a proven choice for applications where limiting toxic materials of combustion are an important issue. Since ZHLA is also UL listed and CSA Certified, it is ideal for field installation in confined, public areas such as subways, tunnels, etc.

see product detail»

Type ATLA

A liquidtight flexible steel conduit designed specifically for extreme hot or cold environments. The flexible inner core is identical to that found in Type LA. The specially formulated PVC jacket remains flexible at low temperatures and resists aging at elevated temperatures. It is listed by Underwriters Laboratories Inc. and certified by Canadian Standards Association

see product detail»