SUNNY BOY 3.0-US / 3.8-US / 5.0-US / 6.0-US / 7.0-US / 7.7-US





Value-Added Improvements

- Superior integration with SMA's MLPE Power+ Solution
- World's first Secure Power Supply* now offers up to 2,000 W
- Full grid management capabilities ensure a utility-compliant solution for any market

Reduced Labor

- New Installation Assistant with direct access via smartphone minimizes time in the field
- Advanced communication interface with fewer components creates 50% faster setup and commissioning

Unmatched Flexibility

- SMA's proprietary OptiTracTM
 Global Peak technology mitigates
 shade with ease
- Multiple independent MPPTs accommodate hundreds of stringing possibilities

Trouble-Free Servicing

- Two-part enclosure concept allows for simple, expedited servicing
- Equipped with SMA Smart Connected, a proactive service solution that is integrated into Sunny Portal

SUNNY BOY 3.0-US / 3.8-US / 5.0-US / 6.0-US / 7.0-US / 7.7-US

Reduce costs across your entire residential business model

The residential PV market is changing rapidly. Your bottom line matters more than ever—so we've designed a superior residential solution to help you decrease costs at every stage of your business operations. The Sunny Boy 3.0-US/3.8-US/5.0-US/6.0-US/7.0-US/7.7-US join the SMA lineup of field-proven solar technology backed by the world's #1 service team, along with a wealth of improvements. Simple design, improved stocking and ordering, value-driven sales support and streamlined installation are just some of the ways that SMA helps your business operate more efficiently. And, Sunny Boy's superior integration with the innovative Power+ Solution means installers have even more flexibility in addressing their toughest challenges. Finally, SMA Smart Connected will automatically detect errors and initiate the repair and replacement process so that installers can reduce service calls and save time and money.

Technical data	Sunny Boy 3.0-US		Sunny Boy 3.8-US		Sunny Boy 5.0-US				
	208 V	240 V	208 V	240 V	208 V	240 V			
Input (DC)									
Max. PV power	4800	O Wp		0 Wp	800	0 Wp			
Max. DC voltage				600 V					
Rated MPP voltage range	155 -	480 V	195 - 480 V		220 - 480 V				
MPPT operating voltage range	100 - 550 V								
Min. DC voltage / start voltage	100 V / 125 V								
Max. operating input current per MPPT	10 A								
Max. short circuit current per MPPT	18 A								
Number of MPPT tracker / string per MPPT tracker	2/1				3 / 1				
Output (AC)									
AC nominal power	3000 W	3000 W	3330 W	3800 W	5000 W	5000 W			
Max. AC apparent power	3000 VA	3000 VA	3330 VA	3800 VA	5000 VA	5000 VA			
Nominal voltage / adjustable	208 V / ●	240 V / ●	208 V / ●	240 V / ●	208 V / ●	240 V / ●			
AC voltage range	183 - 229 V	211 - 264 V	183 - 229 V	211 - 264 V	183 - 229 V	211 - 264			
AC grid frequency			60 Hz ,	/ 50 Hz					
Max. output current	14.5 A	12.5 A	16.0 A	16.0 A	24.0 A	24.0 A			
Power factor (cos φ)				1					
Output phases / line connections	1/2								
Harmonics	< 4 %								
Efficiency				, ,-					
Max. efficiency	97.2 %	97.6 %	97.2 %	97.5 %	97.2 %	97.5 %			
CEC efficiency	96 %	96.5 %	96.5 %	96.5 %	96.5 %	97 %			
Protection devices	70 70	70.0 70	70.0 70	70.0 70	70.0 70	// /0			
DC disconnect device									
DC reverse polarity protection									
Ground fault monitoring / Grid monitoring									
AC short circuit protection				7					
All-pole sensitive residual current monitoring unit (RCMU)				_					
				-					
Arc fault circuit interrupter (AFCI) Protection class / overvoltage category	I / IV								
General data			1/	IV					
			525 720 100	(011 005 70)					
Dimensions (W / H / D) in mm (in) Packaging dimensions (W / H / D) in mm (in)	535 x 730 x 198 (21.1 x 28.5 x 7.8)								
Weight / packaging weight	600 x 800 x 300 (23.6 x 31.5 x 11.8) 26 kg (57 lb) / 30 kg (66 lb)								
Temperature range: operating / non-operating	-25°C+60°C / -40°C+60°C								
Environmental protection rating	-25°C+60°C / -40°C+60°C NEMA 3R								
Noise emission (typical)									
.,,,	39 dB(A) < 5 W								
Internal power consumption at night	< 5 W Transformerless / Convection								
Topology / Cooling concept			rransionnenes	is / Convection					
Features				2					
Ethernet ports				2					
Secure Power Supply	•*								
Display (2 x 16 characters)	•								
WLAN / Sensor module / External WLAN antenna	•/0/0								
Warranty: 10 / 15 / 20 years	111 1741 111 1741	CA :	,	0/0 00 JEEE1 5 47 TOO I)	CANIZOCANO			
Certificates and approvals			107.1-1, HECO SR	9B, IEEE1547, FCC F D-UL-1741-SA-V1.1	· ·	,			
Standard features O Optional features – Not available				·					
Type designation	SB3.0-1	SP-US-40	SB3.8-1	SP-US-40	SB5.0-1	SP-US-40			


Accessories



Sensor module MD.SEN-US-40







Technical data	Sunny Boy 6.0-US		Sunny Boy 7.0-US		Sunny Boy 7.7-US				
	208 V	240 V	208 V	240 V	208 V	240 V			
nput (DC)									
Max. PV power	9600 Wp 11200 Wp 12320 Wp								
Max. DC Voltage			600 V						
Rated MPP Voltage range	220 -	- 480 V	245 - 480 V		270 - 480 V				
MPPT operating voltage range	100 - 550 V								
Min. DC voltage / start voltage	100 V / 125 V								
Max. operating input current per MPPT	10 A								
Max. short circuit current per MPPT	18 A								
Number of MPPT tracker / string per MPPT tracker	3/1								
Output (AC)									
AC nominal power	5200 W	6000 W	6660 W	7000 W	6660 W	7680 W			
Max. AC apparent power	5200 VA	6000 VA	6660 VA	7000 VA	6660 VA	7680 VA			
Nominal voltage / adjustable	208 V / •	240 V / ●	208 V / ●	240 V / ●	208 V / ●	240 V / •			
AC voltage range	183 - 229 V	211 - 264 V	183 - 229 V	211 - 264 V	183 - 229 V	211 - 264			
AC grid frequency	60 Hz / 50 Hz								
Max. output current	25.0 A	25.0 A	32.0 A	29.2 A	32.0 A	32.0 A			
Power factor (cos φ)				1					
Output phases / line connections	1/2								
Harmonics	< 4 %								
Efficiency									
Max. efficiency	97.2 %	97.6 %	97.1 %	97.5 %	97.1 %	97.5 %			
CEC efficiency	96.5 %	97 %	96.5 %	97 %	96.5 %	97 %			
Protection devices		,, ,,							
DC disconnect device				•					
OC reverse polarity protection				•					
Ground fault monitoring / Grid monitoring				•					
AC short circuit protection				•					
All-pole sensitive residual current monitoring unit (RCMU)				•					
Arc fault circuit interrupter (AFCI)				•					
Protection class / overvoltage category	I / IV								
General data			' /						
Dimensions (W / H / D) in mm (in)			535 v 730 v 108	(21 1 ~ 28 5 ~ 7 8)					
Packaging Dimensions (W / H / D) in mm (in)	535 x 730 x 198 (21.1 x 28.5 x 7.8) 600 x 800 x 300 (23.6 x 31.5 x 11.8)								
Weight / packaging weight	26 kg (57 lb) / 30 kg (66 lb)								
emperature range: operating / non-operating	-25°C+60°C / -40°C+60°C								
Environmental protection rating	-23 C+60 C / -40 C+60 C								
Noise emission (typical)	39 dB(A) 45 dB(A)								
171	37	db(A)	43 db(A)						
nternal power consumption at night	T	/ C	Transformerless / Fan						
opology / Cooling concept	runstormerle	ss / Convection		iranstorme	eness / run				
eatures				2					
thernet ports				2 • *					
Secure Power Supply				Ť					
Display (2 x 16 characters)									
WLAN / Sensor module / External WLAN antenna	•/0/0								
Warranty: 10 / 15 / 20 years	III 1741 III 174	1 SA incl Dulo 21 DS		0/0 or leee1547 ecc.i	Part 15 (Class A 9 D)	CANI/CSA VO			
Certificates and approvals		1 SA incl. Rule 21 RS	107.1-1, HECO SF	RD-UL-1741-SA-V1.1					
·	e Data at nominal conditions NOTE: US inverters ship with gray lids. * Not compatible with the Power+ Solution Shutdown funct SB6.0-1SP-US-40 SB7.7-1SP-US-40								
ype designation	SB6.0-1SP-US-40 SB7.0-1SP-US-40 SB7.7-1					5P-US-40			

POWER+ SOLUTION

The SMA Power+ Solution combines legendary SMA inverter performance and intelligent DC module-level electronics

in one cost-effective, comprehensive package. This means that you can achieve maximum solar power production for your customers while also realizing significant installation savings.

NEW! Advanced communication interface allows for 50% faster setup and commissioning thanks to reduced components and a simplified process.

Visit www.SMA-America.com for more information.









SIMPLE, FLEXIBLE DESIGN

Speed the completion of customer proposals and maximize the efficiency of your design team with the Sunny Boy-US series, which provides a new level of flexibility in system design by offering:

- » Hundreds of stringing configurations and multiple independent MPPTs
- » SMA's proprietary OptiTrac™ Global Peak shade mitigation technology
- » Diverse application options including on- and off-grid compatibility



VALUE-DRIVEN SALES ENABLEMENT

SMA wants to enable your sales team by arming them with an abundance of feature/benefit support. Show your customers the value of the Sunny Boy-US series by utilizing:

- » Secure Power Supply, now with 2,000 W of opportunity power in the event of a grid outage, as an increased value-add or upsell opportunity
- » SMA's 35 year history and status as the #1 global inverter manufacturer instills homeowners with peace of mind and the long-term security they demand from a PV investment
- » An economical solution for shade mitigation and the challenges of complex roofs



IMPROVED STOCKING AND ORDERING

Ensure that your back office business operations run smoothly and succinctly while mitigating potential errors. The Sunny Boy-US series can help achieve cost savings in these areas by providing:

- » An integrated DC disconnect that simplifies equipment stocking and allows for a single inverter part number
- » All communications integrated into the inverter, eliminating the need to order additional equipment



STREAMLINED INSTALLATION AND COMMISSIONING

Expedite your operations in the field by taking advantage of the new Sunny Boy's installer-friendly feature set including:

- » Direct access via smartphone and utilization of SMA's Installation Assistant, which minimizes time/labor spent in the field and speeds the path to commissioning
- » Simple commissioning and monitoring setup in a single online portal
- » New! Advanced communication interface with fewer components allows for 50% faster commissioning



SUPERIOR SERVICE

SMA understands the factors that contribute to lifetime PV ownership cost, that's why the Sunny Boy-US series was designed for maximum reliability and backstopped by an unmatched service offering. Benefit from:

- » SMA Smart Connected, a proactive service solution integrated into Sunny Portal that automatically detects errors and initiates the repair and replacement process
- » The #1 service team in the PV industry, as recognized by IMS research, with experience servicing an installed base of more than 55 GW