

LED Omnidirectional A19 and A21 SPEC SHEET



True Omnidirectional Light Distribution

Topaz LED Omnidirectional A19 and A21 lamps are ideal for both residential and commercial settings including down lights, wall sconces, ceiling fans, table and floor lamps. Dimmable down to 10% for additional energy savings and ambiance control.

FEATURES

- 300° beam spread
- 85% energy savings compared to incandescent lamps
- Suitable for use in totally enclosed luminaires
- Long life – up to 10X longer than traditional incandescents
- RoHS compliant and mercury free
- Plastic lens material provides shatter protection

APPLICATIONS

- Fan lights, decorative, recessed, task lighting
- Residential, hospitality, retail, restaurants, commercial





Job Name/Title: _____ Catalog Number _____
Contractor: _____ Notes: _____

LED Omnidirectional A19 and A21 SPEC SHEET

GENERAL SPECIFICATIONS

Input Voltage: 120V
Average Rated Life: 25,000 Hours
CRI: 80
THD: <15%
Beam Angle: 220°
Ambient temp: -4°F to 104°F
PK-QTY: 1/6/24

SPECIFICATIONS / ORDER INFO

Item #	Order Code	UPC Code	Shape	Watts	Equivalent Wattage	Base	CCT (Kelvin)	Avg. Lumens	MOL In.	MOD In.	Energy Star	Dimmable
LA19/5/27K/D-46	77004	751338002708	A19	5	40W A19	E26	2700	450	4.35"	2.37"	Y	Y
LA19/5/30K/D-46	77005	751338002777	A19	5	40W A19	E26	3000	450	4.35"	2.37"	Y	Y
LA19/5/40K/D-46	77006	751338002784	A19	5	40W A19	E26	4000	450	4.35"	2.37"	Y	Y
LA19/5/50K/D-46	77007	751338002791	A19	5	40W A19	E26	5000	450	4.35"	2.37"	Y	Y
LA19/9/27K/D-46	77008	751338002807	A19	9.5	60W A19	E26	2700	800	4.35"	2.37"	-	Y
LA19/9/30K/D-46	77009	751338002814	A19	9.5	60W A19	E26	3000	800	4.35"	2.37"	Y	Y
LA19/9/40K/D-46	77010	751338002821	A19	9.5	60W A19	E26	4000	800	4.35"	2.37"	Y	Y
LA19/9/50K/D-46	77011	751338002838	A19	9.5	60W A19	E26	5000	800	4.35"	2.37"	Y	Y
LA19/12/27K/D-46	77012	751338002845	A19	11.5	75W A19	E26	2700	1,100	4.65"	2.37"	Y	Y
LA19/12/30K/D-46	77013	751338002852	A19	11.5	75W A19	E26	3000	1,100	4.65"	2.37"	Y	Y
LA19/12/40K/D-46	77014	751338002869	A19	11.5	75W A19	E26	4000	1,100	4.65"	2.37"	Y	Y
LA19/12/50K/D-46	77015	751338002876	A19	11.5	75W A19	E26	5000	1,100	4.65"	2.37"	Y	Y
LA21/16/27K/D-46	77018	751338002883	A21	15.5	100W A21	E26	2700	1,600	5.55"	2.65"	Y	Y
LA21/16/30K/D-46	77019	751338002890	A21	15.5	100W A21	E26	3000	1,600	5.55"	2.65"	Y	Y
LA21/16/40K/D-46	77020	751338002906	A21	15.5	100W A21	E26	4000	1,600	5.55"	2.65"	Y	Y
LA21/16/50K/D-46	77021	751338002913	A21	15.5	100W A21	E26	5000	1,600	5.55"	2.65"	Y	Y
LA19/9/27K/GU24D-46	71024	751338003378	A19	9.5	60W A19	GU24	2700	800	4.55"	2.37"	-	Y
LA19/9/30K/GU24D-46	71025	751338003385	A19	9.5	60W A19	GU24	3000	800	4.55"	2.37"	-	Y
LA19/9/40K/GU24D-46	71026	751338003392	A19	9.5	60W A19	GU24	4000	800	4.55"	2.37"	-	Y
LA19/12/30K/GU24D-46	74152	751338016286	A19	11.5	75W A19	GU24	3000	1,100	4.55"	2.37"	-	Y

NOMENCLATURE

Example: LA19/5/27K/D

LA19=LED A19 Shape / 5=5 Watt / 27K=2700K / D=Dimmable

ENERGY SAVINGS

	LED Watts	Incandescent Watts	Energy Saving, Watts	Yearly Saving, Fixture	5 Year Cost Savings
Based on 5 hours/day and .11¢/kwhr					
LA19/5/XXK/D	5	40	35	\$7.03	\$35.13
LA19/9/XXK/D	9.5	60	50.5	\$10.14	\$50.69
LA19/12/XXK/D	11.5	75	63.5	\$12.75	\$63.74
LA21/16/XXK/D	15.5	100	84.5	\$16.96	\$84.82

Suitable for enclosed fixtures. This device is not intended for use with emergency exits.

This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. Specifications subject to change without notice.

FIVE (5) YEAR LIMITED WARRANTY: TOPAZ LIGHTING CORP. warrants to the original purchaser that all TOPAZ LED lamps shall be free from defects of material and workmanship for a period of five (5) years from the date of purchase. Based on 12 hours of use per day. TOPAZ LIGHTING CORP. will, at its option, repair or replace without charge a defective LED lamp that has not been misused, carelessly handled or improperly installed. Repair or replacement, as stated above, shall constitute the purchaser's exclusive warranty, which does not extend to transportation, installation, labor or any other consequential charges. www.topaz-usa.com

Specifications subject to change without notice.