

# ETP™ 7000S Series Steel EMT Compression Connectors

NEC/CEC:  
Listed for Ordinary Locations

## Application

- To ground and secure EMT raceways to boxes and enclosures.

## Features

- Male hub threads — NPS.
- Available with insulated throat.
- Concretetight.
- Insulated throat connector rated +90 °C (+194 °F).

## Materials/Finish

- Body and nut: steel
- Steel/zinc plated

## NEC/CEC Certifications and Compliances

- UL Standard: 514B
- UL Listed: E14815, E-14814
- cUL Listed: E14815
- CSA Standard: C22.2 No. 18.3
- NEMA: FB-1



7050S –7400ST

| Trade Size<br>(Inches) | Dimensions in Millimeters (Inches) |                     |                  |  | Weight per 100<br>kg (lb) | Catalog<br>Number | Insulated Throat<br>Catalog Number |
|------------------------|------------------------------------|---------------------|------------------|--|---------------------------|-------------------|------------------------------------|
|                        | Body<br>Length                     | Maximum<br>Diameter | Thread<br>Length |  |                           |                   |                                    |
| 1/2                    | 28.7 (1.13)                        | 26.9 (1.06)         | 9.7 (0.38)       |  | 6.80 (15.00)              | 7050S             | 7050ST                             |
| 3/4                    | 26.2 (1.03)                        | 31.8 (1.25)         | 11.2 (0.44)      |  | 9.53 (21.00)              | 7075S             | 7075ST                             |
| 1                      | 31.8 (1.25)                        | 39.6 (1.56)         | 11.2 (0.44)      |  | 14.51 (32.00)             | 7100S             | 7100ST                             |
| 1-1/4                  | 46.0 (1.81)                        | 50.8 (2.00)         | 14.2 (0.56)      |  | 32.66 (72.00)             | 7125S             | 7125ST                             |
| 1-1/2                  | 50.8 (2.00)                        | 55.6 (2.19)         | 14.2 (0.56)      |  | 38.56 (85.00)             | 7150S             | 7150ST                             |
| 2                      | 57.2 (2.25)                        | 68.3 (2.69)         | 17.5 (0.69)      |  | 56.25 (124.00)            | 7200S             | 7200ST                             |
| 2 - 1/2 ①              | 60.5 (2.38)                        | 84.8 (3.34)         | 22.4 (0.88)      |  | 72.57 (160.00)            | 7250S             | 7250ST                             |
| 3 ①                    | 73.2 (2.88)                        | 101.6 (4.00)        | 22.4 (0.88)      |  | 120.20 (265.00)           | 7300S             | 7300ST                             |
| 3 - 1/2 ①              | 76.2 (3.00)                        | 114.3 (4.50)        | 25.4 (1.00)      |  | 192.78 (425.00)           | 7350S             | 7350ST                             |
| 4 ①                    | 81.0 (3.19)                        | 128.5 (5.06)        | 25.4 (1.00)      |  | 272.16 (600.00)           | 7400S             | 7400ST                             |

① Rated for steel EMT, aluminum and steel RMC, and steel IMC.

# ETP™ 7000US Series Steel EMT Compression Connectors

NEC/CEC:  
Listed for Ordinary Locations

## Application

- To ground and secure EMT raceways to boxes and enclosures.

## Features

- Made in the U.S.A.
- Male hub threads — NPS.
- Available with insulated throat.
- Concretetight.
- Insulated throat temperature rated +90 °C (+194 °F).

## Materials/Finish

- Steel/zinc plated 1/2" thru 2"
- Malleable Iron 2-1/2" thru 4"

## NEC/CEC Certifications and Compliances

- UL Standard: 514B
- UL Listed: E-14895, E14815
- CSA Standard: C22.2 No. 18.3
- cUL Listed: E14815
- CSA Certified: 028507
- NEMA: FB-1



7050US –7200US



7250US –7400US

| Trade Size<br>(Inches) | Dimensions in Millimeters (Inches) |                     |                  | Catalog<br>Number | Insulated Throat<br>Catalog Number |
|------------------------|------------------------------------|---------------------|------------------|-------------------|------------------------------------|
|                        | Body<br>Length                     | Maximum<br>Diameter | Thread<br>Length |                   |                                    |
| 1/2                    | 26.9 (1.06)                        | 24.6 (0.97)         | 9.7 (0.38)       | 7050US            | 7050UST                            |
| 3/4                    | 28.7 (1.13)                        | 31.0 (1.22)         | 10.4 (0.41)      | 7075US            | 7075UST                            |
| 1                      | 31.8 (1.25)                        | 38.1 (1.50)         | 11.2 (0.44)      | 7100US            | 7100UST                            |
| 1-1/4                  | 36.6 (1.44)                        | 48.5 (1.91)         | 12.7 (0.50)      | 7125US            | 7125UST                            |
| 1-1/2                  | 39.6 (1.56)                        | 54.9 (2.16)         | 13.5 (0.53)      | 7150US            | 7150UST                            |
| 2                      | 42.9 (1.69)                        | 68.3 (2.69)         | 15.0 (0.59)      | 7200US            | 7200UST                            |
| 2 - 1/2                | 103.1 (4.06)                       | 104.9 (4.13)        | 31.8 (1.25)      | 7250US            | 7250UST                            |
| 3                      | 104.9 (4.13)                       | 119.1 (4.69)        | 35.1 (1.38)      | 7300US            | 7300UST                            |
| 3 - 1/2                | 108.0 (4.25)                       | 135.6 (5.34)        | 35.8 (1.41)      | 7350US            | 7350UST                            |
| 4                      | 114.3 (4.50)                       | 149.4 (5.88)        | 38.1 (1.50)      | 7400US            | 7400UST                            |