

Traditional style. Remarkable energy savings.

The WPSLED luminaire provides traditional architectural style with high performance energy efficient illumination resulting in significant energy savings. With effective thermal management, the WPSLED luminaire provides glare free, uniform illumination while providing a safe and comfortable visual experience for pathway illumination, building entrances, vehicle ramps, schools, tunnels, stairways and loading docks.



Superior illumination

The WPSLED luminaire offers a 3,382 lumen package. Offered in brilliant white 5000K and neutral 4000K CCT.

Significant energy savings

Replaces 100 watt HID fixtures translating to over 87 percent in energy savings over traditional metal halide fixtures, while taking advantage of significant utility rebates.

Construction

- Rugged, die-cast aluminum housing
- Hinged, removable door for ease of maintenance
- Three 1/2" threaded conduit entry points for thru-branch wiring
- IP66 Rated
- UL/cUL wet location rated

Optical

- Replaces 100W metal halide luminaires
- Lumen package 3,282 nominal lumens
- Impact resistant borosilicate refractive glass lens
- Greater than 94 percent lumen maintenance at 50,000 hours
- Available in 4000K CCT, 70 CRI and 5000K CCT, 70 CRI
- DesignLights Consortium® Qualified*

Electrical

- 120-277V 50/60Hz, 347V/60Hz
- -40°C to 40°C ambient operating temperature range

Controls

- Button photocontrol (120-277V)

Accessories

- Galvanized coated steel wire guard
- Wall pack visor

Mounting

- J-box or conduit installation

Warranty

- Five-year warranty

Stock Ordering Information

Stock Number	Description	UPC Code	HID Replacement
WPSLED-30-GL-UNV	Wal-Pak LED, Borosilicate Glass Door, 3,382 Lumens, 4000K, 27W, 120-277V	080083776368	100W
WPSLED-30-GL-UNV-7050	Wal-Pak LED, Borosilicate Glass Door, 3,435 Lumens, 5000K, 27W, 120-277V	080083776443	100W
WPSLED-30-GL-UNV-PC	Wal-Pak LED, Borosilicate Glass Door, 3,382 Lumens, 4000K, 27W, PC, 120-277V	080083776528	100W
WPSLED-30-GL-347	Wal-Pak LED, Borosilicate Glass Door, 3,382 Lumens, 4000K, 27W, 347V	080083776641	100W
WPSLED-30-GL-347-7050	Wal-Pak LED, Borosilicate Glass Door, 3,435 Lumens, 5000K, 27W, 347V	080083776726	100W
WPSLED-30-GL-347-PC	Wal-Pak LED, Borosilicate Glass Door, 3,382 Lumens, 4000K, 27W, PC, 347V	080083776801	100W

* Refer to www.designlights.org for details.