

Straps for Coaxial Cable

- Our UV stabilized black straps are recommended for extended outdoor use. UV stabilized white, ivory, tan, and gray straps are also available on special order.
- Our 1" nails are heat treated for use in wood, mortar joints, or 'soft' masonry. Longer 1-3/16" heat treated nails are available on special order.
- Our CC-1021 has a special 5/8" nail designed exclusively for use in masonry.
- To prevent cable damage from an accidental hammer blow, we offer straps with a #6 x 1" Phillips Head self-tapping screw. If used with a plastic screw anchor, this strap can also be used on masonry.
- Our CC-1006 strap has a #8 x 3/4" Type AB Tapping Screw for attaching #14 and #12 ground wire. Straps with a #8 x 1" Slotted/Phillips Hex Head Type AB Tapping Screw are also available. Type AB screws will cut threads in a pre-drilled hole in concrete, block, or any masonry material.
- A 'snap on' feature for straps with the #8 Tapping Screw speeds installation.

CAT. NO.	MAXIMUM CABLE SIZE	NAIL/SCREW	PACKAGE AND QUANTITY	STD. CARTON QUANTITY	APPROX. SHIPPING WT. PER CARTON
CC-1005	#12 Ground Wire .140" Dia.	1" x .080 Dia. Hardened Nail	Box of 100	1000	3 lbs.
CC-1006	#14 and #12 Ground Wire .110" - .145" Dia.	#8 x 3/4" Slotted/Phillips Hex Head Type AB Tapping Screw	Box of 50	500	4 lbs.
CC-1010	RG59 .242" Dia.	1" x .080 Dia. Hardened Nail	Box of 100	1000	3 lbs.
CC-1012	RG59 .242" Dia.	#6 x 1" Phillips Head Self-Tapping Screw	Box of 100	1000	7 lbs.
CC-1016	RG59 .242" Dia.	#8 x 1" Slotted/Phillips Hex Head Type AB Tapping Screw	Box of 100	1000	9 lbs.
CC-2010	RG59 Dual .250" x .500"	1" x .080 Dia. Hardened Nail	Box of 100	1000	5 lbs.
CC-1020	RG6 .275" Dia.	1" x .080 Dia. Hardened Nail	Box of 100	1000	3 lbs.
CC-1021	RG6 .275" Dia.	.072 x 5/8" Hardened Nail	Box of 100	1000	3 lbs.
CC-1022	RG6 .275" Dia.	#6 x 1" Phillips Head Self-Tapping Screw	Box of 100	1000	7 lbs.
CC-1026	RG6 .275" Dia.	#8 x 1" Slotted/Phillips Hex Head Type AB Tapping Screw	Box of 100	1000	9 lbs.

