

Outdoor Wall Lantern

- 8037-02** Polished Solid Brass
8037-12 Black Finish Solid Brass
8037-15 White Finish Solid Brass
8037-17 Verde Finish Solid Brass
8037-71 Antique Bronze Finish Solid Brass
 Clear Curved Beveled Glass Bound in Solid Brass

Size: Width: 7" Height: 12 1/4" Extension: 7"
 Height from Center of Outlet Box: 6 1/8"

Wattage: One (M) 100w max.
 Clear Bulb Recommended.

8037-02



8037-12



8037-17



8037-71



8037-15



8040-12



8040-02



8040-15



8040-17



8040-71



Outdoor Wall Lantern

- 8040-02** Polished Solid Brass
8040-12 Black Finish Solid Brass
8040-15 White Finish Solid Brass
8040-17 Verde Finish Solid Brass
8040-71 Antique Bronze Finish Solid Brass
 Clear Curved Beveled Glass Bound in Solid Brass

Size: Width: 12 1/2" Height: 22 1/2" Extension: 11 5/8"
 Height from Center of Outlet Box: 9 1/4"

Wattage: Three (C) 40w max.
 Clear Bulb Recommended.

8039-02



8039-12




8039-15



8039-17



8039-71



Outdoor Wall Lantern







- 8039-02** Polished Solid Brass
8039-12 Black Finish Solid Brass
8039-15 White Finish Solid Brass
8039-17 Verde Finish Solid Brass
8039-71 Antique Bronze Finish Solid Brass
 Clear Curved Beveled Glass Bound in Solid Brass

Size: Width: 10" Height: 20" Extension: 9 3/4"
 Height from Center of Outlet Box: 8 3/4"

Wattage: Two (C) 40w max.
 Clear Bulb Recommended.



LIGHT BULB SELECTION & REFERENCE GUIDE

	Bulb Type	Item Number		Bulb Type	Base Type	Watts Rated	Watts Consumed	Rated Life (Hours)	Approx Light (Lumen)	Approx Color (Temp °K)	CRI	
24 Volt		9720-32	Clear	Xenon	T3	Rigid Loop	5	4.2	16,000	33	2,550	
		9720-33	Frosted	Xenon	T3	Rigid Loop	5	4.2	16,000	33	2,550	
		9721-32	Clear	Xenon	T3	Rigid Loop	10	8.4	12,000	83	2,650	
		9721-33	Frosted	Xenon	T3	Rigid Loop	10	8.4	12,000	83	2,650	
		9775		Xenon	T5	Wedge	18	16.2	2,000	210	2,800	
120 Volt	BI-PIN HALOGEN											
		9734-32	Halogen		T4	G-8	35	-	2,500	650	2,900	-
	MINI CAN											
		9759	Xenon		T3	E-11	20	-	2,000	200	2,700	-
		9760	Xenon		T3	E-11	40	-	2,000	560	2,800	-
		9761	Xenon		T3	E-11	60	-	2,000	960	2,800	-
		9779	Halogen		T3	E-11	75	-	1,500	1,120	2,850	-
		9780	Halogen		T4	E-11	150	-	1,500	2,400	2,850	-
		9781	Halogen		T4	E-11	250	-	2,000	4,500	2,900	-
	COMPACT FLUORESCENT											
		9744			Twin Tube	G23	5	-	10,000	250	2,700	82
		9745			Twin Tube	G23	7	-	10,000	400	2,700	82
		9746			Twin Tube	G23	9	-	10,000	600	2,700	82
		9747			Twin Tube	GX23	13	-	10,000	900	2,700	82
		9757	Instant Start		Twin Tube	GX23	13	-	12,500	825	2,700	82
9706				Twin Tube	L2G11	36	-	12,000	2,900	4,100	82	
	9748			Quad Tube	GX23-2	13	-	10,000	860	2,700	82	
	9749			Quad Tube	GX32 D-2	22	-	10,000	1200	2,700	82	
	9763	Instant Start		Quad Tube	GX23	13	-	10,000	860	2,700	84	
	9764			Quad Tube	G24 D-2	18	-	10,000	1200	2,700	84	

Note: Light bulbs are not included with lighting fixtures unless otherwise specified.

All Sea Gull Lighting fixtures are engineered to meet or exceed the standards set by the National Electrical code and are listed by Underwriters Laboratories, Inc. Each product is tested in our state-of-the-art facilities. At this time, there is no American National Safety Standard for light bulbs. Maximum light bulb wattages are specified in our catalog for all lighting products. Heat emitted from various manufacturers' and distributors' light bulbs may vary significantly and operate beyond acceptable limits. Sea Gull Lighting is not responsible for this occurrence unless the Sea Gull Lighting supplied brand light bulb is used. Our random testing has shown the General Electric, Osram/Sylvania and Philips, Westinghouse brand light bulbs operate within acceptable temperature variations.

